




THIS DRAWING IS UNPUBLISHED.
RELEASED FOR PUBLICATION
20
COPYRIGHT 20 BY - ALL RIGHTS RESERVED.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	B	REVISED PER ECO-17-005660	120CT2017	B. J	S. Y

- NOTES:
- 5 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI
 - 6 CONNECTOR WITH BLACK HOUSING

LOW HALOGEN


THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED:
mm	
	0 PLC ±0.1
	1 PLC ±0.05
	2 PLC ±0.01
	3 PLC ±0.01
	4 PLC ±0.01
	ANGLES ±0.1
MATERIAL	FINISH

DWN	16SEP04
CHK	FLORENCE TAN
APVD	ERIC TNG
PRODUCT SPEC	SE IFONG
APPLICATION SPEC	108-5390
WEIGHT	-
CUSTOMER DRAWING	

TE Connectivity			
NAME			
REC ASSY, 5H, 0.76 GOLD			
0.8FH, BTB CONNECTOR			
0.5 BOSS LENGTH			
SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A300779	C-5353999		-
SCALE	SHEET	OF	REV
4:1	1	2	B

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-



- NOTES;
- 1 MATERIAL: HOUSING: L.C.P. (HIGH TEMP. THERMOPLASTIC)
UL 94V-0, NATURAL.
CONTACT: BERYLIUM COPPER.
 - 2 FINISH: CONTACT AREA: 0.00076 MIN GOLD ON
0.0013 MIN ALL OVER NICKEL.
SOLDERING AREA: 0.002 MIN MATTE-TIN.
 - 3. POSITION SERIES: SEE TABLE.
 - 4. CONN STACK HEIGHT COMBINE OF PLUG "Y" H VS REC "X" H.
STACK HEIGHT = Y + X - 5

$\phi 1.2 \pm 0.03$ RECOMMENDED P.C. BOARD LAYOUT

LOW HALOGEN

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN FLORENCE TAN 16SEP04	TE Connectivity		
DIMENSIONS: mm		CHK ERIC TNG			
		APVD SEIFONG	NAME REC ASSY, 5H, 0.76 GOLD 0.8FH, BTB CONNECTOR 0.5 BOSS LENGTH		
		PRODUCT SPEC 108-5390	SIZE A300779		
MATERIAL		APPLICATION SPEC -	CAGE CODE C-5353999		
		FINISH -	DRAWING NO -		
		WEIGHT -	RESTRICTED TO -		
		CUSTOMER DRAWING	SCALE 4:1	SHEET 2 OF 2	REV B