





- NOTES:
1. MATERIALS AND FINISHES:
BODY - ZINC DIE CAST, NICKEL PLATING
CONTACT - PHOSPHOR BRONZE, GOLD PLATING (.000003 THICK)
@ CONTACT AREA ONLY, TIN PLATING AT TAIL, NICKEL PLATED OVERALL
INSULATOR - POLYPROPYLENE
ROUND PIN - BRASS, TIN PLATING
GROUNDNG TERMINAL - STEEL, TIN PLATING
2. ELECTRICAL:
A. IMPEDANCE: 75 OHM
B. FREQUENCY RANGE: DC - 1 GHz
C. DIELECTRIC WITHSTANDING VOLTAGE: 1500 VRMS, MIN.
3. MECHANICAL:
A. DURABILITY: 500 CYCLES MIN.
B. TEMPERATURE RANGE: -55° C TO 85° C
4. PACKAGING:
A. PACKAGED IN PACKING TRAYS
B. QUANTITY PER TRAY: 40



THIRD ANGLE PROJ.

REVISIONS

REV	DESCRIPTION	DATE	ECO	APPR
A	RELEASE TO MFG.	4/18/13	45442	EW



CUSTOMER OUTLINE DRAWING
ALL OTHER SHEETS ARE FOR INTERNAL USE ONLY

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN METRIC AND TOLERANCES ARE: <0.5mm ± 0.05mm 0.5 - 6mm ± 0.1mm 6 - 30mm ± 0.2mm 30 - 120mm ± 0.3mm ANGLES ±1°	MATERIAL -	DRAWN ERIC WANKOFF	DATE 01-Aug-12	TITLE 75 OHM BNC DUAL PORT R/A JACK		Amphenol RF www.amphenolrf.com	
		ENGINEER ERIC WANKOFF	DATE 01-Aug-12				
		REFERENCE EAR # 248	DATE 3/26/13	SCALE: 2.5:1.0 SHEET 2 OF 2		DRAWING NO. 31-70507	
		CONFIGURATION LEVEL: In Work	CAD FILE	DWG SIZE B		REV A	ITEM NO. 31-70507 PART NO. 31-70507