


Powerpole® Connectors

- PP75: up to 120 Amps



PP75 series Powerpole® housings can be used for wire-to-wire, wire-to-board, and wire-to-busbar applications. Wire sizes from #16 AWG (1.3 mm²) to #6 (13.3 mm²) offer power capabilities up to 120 amps per pole. Locking housings offer the capability to secure Powerpole® housings to each other and to mounting pads. Housings made from chemical resistant (CR) resin withstand industrial solvents better than standard housings.


- **Large Wire Range Accommodates up to #6 (10mm²) Wire**
Reducing bushings allow as small as #16 (1.5 mm²) wire to be used
- **Wire, PCB, and Busbar Contacts**
Allows one connection system to meet multiple needs
- **Mini-Powerclaw PCB Contacts Minimize PCB Footprint**
Removes the PP75 housing from the board side

PP75 ORDERING INFORMATION

PP75 Standard Housings

The second smallest Powerpole® housing can be used with wire contacts for up to 6 AWG [10mm²] as well as PCB and busbar contacts.


Description	Part Numbers	
Minimum Quantity	1,000	100
Red	5916G7-BK	5916G7
Green	5916G6-BK	5916G6
Black	5916G4-BK	5916G4
White	5916G5-BK	5916G5
Blue	5916-BK	5916
Yellow	5916G15-BK	5916G15
Orange	5916G14-BK	5916G14
Gray	5916G16-BK	5916G16



PP75 Chemical Resistant (CR) Housings

Has the same form and dimensions of the standard PP75 housing in a chemical resistant PBT/ PC blend housing. Suitable for use to -40°C.


Description	- Part Numbers -
Minimum Quantity	1,000
Red	P5916G7-BK
Black	P5916G4-BK
White	P5916G5-BK
Blue	P5916-BK



PP75 Locking Dovetail Housings

Offers dovetails for stacking housings that have a locking feature to prevent housings separating. Can mate to standard and chemical resistant housings, but cannot be stacked with them.


Description		Part Numbers	
Minimum Quantity	1,000	100
Red	75LOKRED-BK	75LOKRED	
Green	75LOKGRL-BK	75LOKGRL	
Black	75LOKBLK-BK	75LOKBLK	
White	75LOKWHT-BK	75LOKWHT	
Blue	75LOKBLU-BK	75LOKBLU	
Gray	75LOKGRA-BK	75LOKGRA	



PP75 Silver Plated Wire Contacts

Silver plated contacts offer the best electrical performance and durability up to 10,000 mating cycles. See reducing bushings in accessory section for smaller wires.


AWG	mm²	Mating Force	Loose Piece		Dimensions	
			-- Part Numbers --	1,000 100	- A -	inches mm
Minimum Quantity						
6	13.3	Low	1307-BK	1307	0.22	5.59
6	13.3	High	5900-BK	5900	0.22	5.59
8	8.4	High	5952-BK	5952	0.19	4.83
12 to 10	3.3 to 5.3	Low	5953-BK	5953	0.14	3.56
12 to 10	3.3 to 5.3	High	5915-BK	5915	0.14	3.56



PP75 Silver Plated Busbar Contacts

Provide a quick disconnect input or output busbar connection. Busbar contacts are for mating with wire contacts only. Part number 75BBS includes lock nuts. Locknuts must be ordered separately for B01956P4.



Type	Thread	Force	Mating			Part Numbers		
			1,000	20	10		
Minimum Quantity								
Busbar	#10-24	High	B01915P1	-	75BBS			
Lock Nut	#10-24	-	H1216P8	110G54	-			




55A Right Angle Standard Powerclaw PCB Contacts

Standard Powerclaw contacts are for use inside a PP75 housing and provide a color coded right angle connection to the PCB.

Description			--- Loose Piece Part Numbers --	
Minimum Quantity	500	100	
Tin Plated	PC5930T-BK	PC5930T		
Silver Plated	PC5930S-BK	PC5930S		



Second housing and contact in two pole version only.




See PCB contact drawing on website for further detail.

55A Right Angle Mini Powerclaw PCB Contacts

Right angle Mini Powerclaw contacts can be used on the PCB edge without a PP75 housing on the PCB side. A self polarizing design only allow PP75 wire housings to mate to PCB contacts one way.


Description		Loose Piece	
		Part Numbers	
Minimum Quantity ...		1,000	100
Tin Plated		PC5934T-BK	PC5934T
Silver Plated		PC5934S-BK	PC5934S



55A Vertical Mini Powerclaw PCB Contacts







Vertical Mini Powerclaw contacts save space by not requiring a PP75 housing on the PCB side. The guide housing is required for 2 pole applications to provide a polarized connection. (See PP75 accessories).

Description		Loose Piece	
		Part Numbers	
Minimum Quantity ...		1,500	100
Tin Plated		PC5933T-BK	PC5933T
Silver Plated		PC5933S-BK	PC5933S



See PCB contact drawing on website for further detail.

PP75 TEMPERATURE CHARTS |



NOTE: Temperature rise charts are based on a 25°C ambient temperature. Powerclaw charts are based on #8 AWG equivalent copper foil on board side, mated to #6 AWG conductor on wire side.

| PP75 SPECIFICATIONS |

Electrical		
Current Rating Amperes ¹	UL 1977	CSA
Wire to Wire (6 AWG)	120	70
Wire to PCB (6-AWG)	55	50
Wire to Busbar (6 AWG)	75	
Voltage Rating AC/DC		
UL 1977	600	
PCB Connector Recommended Voltage ³ per IEC 60950-1 Table 2L Pollution Degree ²		
Mini Vert. Contact Adjacent Poles	220	
Mini Horiz. Contact Adjacent Poles	200	
Standard Contact Adjacent Poles	635	
Dielectric Withstanding Voltage		
Volts AC	2,200	
Avg. Mated Contact Resistance Milliohms ¹		
Wire Contact with 1 1/4" of #6 AWG	0.200	
PCB Contact to Contact	0.500	
UL Hot Plug Current Rating Amperes - 250 cycles at 120V DC		
Wire- wire	50A	
PCB- wire (Vertical Mini Powerclaw)	40A	
Materials		
Housing		
Standard Plastic Resin	Polycarbonate	
Chem. Resistant Resin	Polycarbonate / PBT blend	
Contact Retention Spring	Stainless Steel	
Housing Flammability Rating		
UL94	V-0	
Contact		
Base	Copper Alloy	
Wire Plating	Silver	
PCB Plating	Sn or Ag over Ni	
Contact Termination Methods		
Crimp ⁴	Wire Contacts	
Hand Solder	Wire and PCB Contacts	
Solder Dip*	PCB Contacts	
Wave Solder*	PCB Contacts	
Wrench / Socket	Busbar Contacts	

Mechanical		
Wire Size Range	AWG	mm ²
Wire Contacts with Bushings	16 to 6	1.3 to 13.3
Max. Wire Insulation Diameter	in.	mm
	0.437	11.100
Operating Temperature ²	°F	°C
Standard	-4° to 221°	-20° to 105°
Chemical Resistant*	-40 to 221°	-40° to 105°
*Chemical resistant material not available for PCB guide housings		
Mating Cycles No Load by Plating		
Wire and PCB Contacts	Silver (Ag)	Tin (Sn)
	10,000	1,500
Avg. Mating / Unmating Force		
Wire to Wire Low Force Contacts	Lbf.	N
Wire to Wire High Force Contacts	5	22
Standard Powerclaw to Wire	7	31
Mini Powerclaw to Wire	7	31
	4	17
PCB Specifications		
Mounting Style	Plated Through Hole	
Max PCB Thickness- in. [mm]	Standard: 0.15 [0.381] Mini: 0.25 [0.635]	
Recommended Traces	#8 AWG Cross Section	
Min. Contact / Spring Retention Force		
Wire Housing	Lbf.	N
	50	222
Min. Creepage / Clearance Distance PCB in.		
Standard Powerclaw Adjacent Poles	0.260	6.6
Mini Vert. Powerclaw Adjacent Poles	0.087	2.2
Mini Horz. Powerclaw Adjacent Poles	0.079	2.0

Protection

Touch Safety with Wire Contacts
IEC 60529 IP10

¹ Based on: 105°C rated or better cable of the largest size, Properly calibrated APP® recommended tooling, and a 25°C ambient temperature. UL rating not to exceed the maximum operating temperature. CSA rating below a 30°C temperature rise.

² Limited by the thermal properties of the connector plastic housing.

³ Without use of spacers to increase creepage and clearance distances.

⁴ Use APP® recommended tooling only. Alternate tools may adversely affect the performance of our connectors along with UL and CSA recognition.



CSA Certified
File No. LR25154




Powerpole® PP75 Accessories |

Strain Relief Grommets

Use for strain relief in the back side of a PP75 housing. Wire gauge given for reference only, use grommet ID and wire OD to determine suitability in the end application.


Description	- Part Numbers -	Dimensions	
		- A -	inches mm
Minimum Quantity ...	100		
#6 AWG, Black	114411P2	0.35	8.89
#8 AWG, Black	114411P1	0.25	6.35
#10 - 12 AWG, Black	114411P3	0.17	4.32



Mounting Wing for Standard or CR Housings

Mounting wings can be used to secure dovetailed Powerpole® 75 series housings by passing fasteners through the wings in either a horizontal or vertical orientation. Useful for sheet metal panels, printed circuit boards, and many other mounting surfaces. Fasteners not included.


Description	----- Part Numbers -----
Minimum Quantity ...	1,000 100 ...
Blue, Round Hole	1399G20-BK 1399G20
Blue, Oval Hole	1399G7-BK 1399G7



Mounting Wing for Locking Housings

Mounting wings can be used to secure Powerpole® 75 series housings with locking dovetails by passing fasteners through the wings in either a horizontal or vertical orientation. Useful for sheet metal panels, printed circuit boards, and many other mounting surfaces. Fasteners not included.


Description	----- Part Numbers -----
Minimum Quantity ...	1,000 100 ...
Blue, Oval Hole	75LOKWNGBLU-BK 75LOKWNGBLU
Blue, Round Hole	75LOKWNGBLU-R-BK 75LOKWNGBLU-R



Surface Mount for Locking Housings

Use to secure Powerpole® 75 series housings with locking dovetails to a flat surface. Useful for sheet metal panels, printed circuit boards, and many other mounting surfaces. Fasteners not included.


Description	----- Part Numbers -----
Minimum Quantity ...	1,000 100 ...
Blue	75LOKSMTBLU-BK 75LOKSMTBLU



NEW Spacer

Use to separate housings under high power to minimize power capability derating due to heat rise. They are recommended for squaring off a block of Powerpole® 75 housings to enable mounting accessories or retaining pins to be used. Combining long and short spacers opposite each other in a mated block adds keying features, or use two short spacers to avoid interference.


Description	----- Part Numbers -----
Minimum Quantity...	1000 100 ...
Red, Short	Available Soon
Red, Long	Available Soon



Guide Housings for Vertical Mini Powerclaw Contacts

Prevents polarity being reversed when a two pole PP75 block is mated to vertical mini Powerclaw contacts. Fastening hardware not included.


Description	Part Numbers		
Minimum Quantity ...	1,000	100	...
Black Guide Housing	PC-HSG-PP-BK	PC-HSG-PP	



Mounting Clamp

Mounting clamps can be used for fastening a block of Powerpole® 75 series housings to a panel. Connector blocks must be a complete square for the clamps to work properly. Fastening hardware not included.

Description	-- Part Numbers --
Minimum Quantity ...	50 sets of 2 ...
2 or 4 Pole	1463G1
3 or 6 Pole	1463G2




Retaining Pins

Retaining pins are used to keep stacked Powerpole® 75 series housings from separating.

Retaining pins are inserted in the circular opening between two housings stacked side by side.

Dimension B is +/- 0.015 in or 0.38 mm.



Description	Part Numbers	Dimensions					
		- A -		- B -			
		inches	mm	inches	mm		
Minimum Quantity ...	1,000 100						
1 Block High	111812P7 110G19	0.196 / 0.207	4.98 / 5.26	0.560	14.220		
2 Block High	111812P6 110G18	0.196 / 0.207	4.98 / 5.26	1.000	25.400		



PCB Mounting Staples

Reduce strain on solder joints during mating and unmating. Staples bend over the underside of the PCB board to lock the housings in place. Staples are an interference fit with housings.


Part Numbers	Number of Stacked Powerpoles® H x W
PCSTAPLE-1	100 1 x 1
PCSTAPLE-2	1 x 2



Reducing Bushings

Use with contact part number 5900-BK or 1307-BK to allow a smaller wire to be used with the connector. Electrical capability is derated with smaller wire.

Contact Barrel Size	Wire Size	Part Numbers	Dimensions						
			- ID -	- Length -					
			inches	mm	Inches	mm			
Minimum Quantity ...		3,000 1,000 100							
#6 AWG [13.3 mm ²]	#8 AWG [8.4 mm ²]		-	5912-BK	5912	0.18	4.57	0.45	11.43
#6 AWG [13.3 mm ²]	#12- 10 AWG [3.3- 5.3 mm ²]	5910-BK	-	5910	0.14	3.56	0.47	11.94	
#6 AWG [13.3 mm ²]	#16- 14 AWG [1.3- 2.1 mm ²]	5913-BK	-	5913	0.09	2.29	0.47	11.94	



For environmentally sealed connector shells to hold Powerpole® 15-180 connectors, see APP®'s SPEC Pak® product series on our website, www.andersonpower.com



Powerpole® - Tooling Information

Wire Size		Loose Piece Part Numbers		Loose Piece Contact Crimp Tool					Reeled Part Numbers		Reeled Contact Crimp Tools		
AWG	mm ²	Tin Plating	Silver Plating	Hand Tool or	Pneumatic Bench Tool	+ Die	+ Locator	Number of Crimps	Tin Plating	Silver Plating	ATS Applicator	ATS Press	Air Feed Kit*
PP15 / 45 Flat Wiping Power & Ground													
16 / 20	1.3 / 0.52	N/A	1332	1309G2 or 1309G8	1367G1 N/A N/A N/A N/A N/A N/A	1388G6 1387G1 1388G7 1388G3 1389G4 1387G1 1303G12 1387G2	Single Single Single Single Single Single Single Single	N/A 262G1 200G2L 269G2 261G1 261G2 269G1 269G3 200G1L	N/A 262G2 200G4L N/A 261G4 261G3 N/A 200G3L	N/A 1385519-1 TBD 1385519-1 1385520-1 1385458-1 1385520-1 1385458-1	N/A 1385519-1 TBD 1385519-1 1385520-1 1385458-1 1385520-1 1385458-1	N/A 1385519-1 TBD 1385519-1 1385520-1 1385458-1 1385520-1 1385458-1	
12 / 16	3.3 / 1.3	N/A	1331										
16 / 20	1.3 / 0.52	262G1-LPBK	262G2-LPBK										
16 / 20	1.5 / 0.52	200G2L-LPBK	200G4L-LPBK										
16 / 20	1.3 / 0.52	269G2-LPBK	N/A										
12 / 16	3.3 / 1.3	261G1-LPBK	261G4-LPBK										
10 / 14	5.3 / 2.1	261G2-LPBK	261G3-LPBK										
12 / 16	3.3 / 1.3	269G1-LPBK	N/A										
10 / 14	5.3 / 2.1	269G3-LPBK	N/A										
10 / 14	6.0 / 2.1	200G1L-LPBK	200G3L-LPBK										
10 / 14	6.0 / 2.1	201G1H-LPBK	201G3H-LPBK										
10 / 14	6.0 / 2.1	1830G1-LPBK	1830G2-LPBK										
PP75													
#6	13.3	N/A	1307	1309G4	1387G1	1388G6 1388G7 1388G3 1388G4	1389G6 1389G7 1389G4 1389G3	Single Single Single Single	265G5 265G6	N/A N/A	1385523-1 1385522-1	2-565435-2 1725900-2 1424266-1 or [3-54500-1]	692655-1 1424266-1 or [354578-1]
#8	8.4		5900										
#10 / 12	5.3 / 3.3		5952										
			5953										
			5915										
PP120													
1/0	53.5	N/A	1323G2	1368	1387G1	1388G3 1388G4	1389G3 1389G4	Single Single	N/A	N/A	N/A	N/A	N/A
#1	42.4		1323G1										
#2	33.6		1319										
#4	21.2		1319G4										
#6	13.3		1319G6										
PP180													
3/0	85	N/A	1328G2	1368	1387G2	1303G12 1303G13	1304G32 1304G32	Double Double	N/A	N/A	N/A	N/A	N/A
2/0	53.5		1328G1										
1/0	53.5		1382										
#1	42.4		1347										
#2	33.6		1383										
#4	21.1		1384										
#6	13.3		1348										

* All ATS applicators for APP® contacts are air feed style, (except 1385870) and require the press to have an air feed kit installed.
 NOTE: See website for the most current information.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Anderson Power Products:

[75LOKBLK-BK](#) [75LOKSMTBLU-BK](#) [75LOKWNGBLU-BK](#) [75LOKGRL-BK](#) [75LOKWNGBLU-R-BK](#) [75LOKRED-BK](#)
[75LOKYEL-BK](#) [75LOKBLU-BK](#)