

10 9 8 7 6 5 4 3 2 1

NOTES:


- 1.) MATERIAL -
INSULATOR - LCP, UL 94V-0, COLOR BLACK
CONTACTS - PHOSPHOR BRONZE
- 2.) SEE SHT. 5 & 6 FOR CHART DIMENSIONS AND EDP NO.'S
- 3.) RECOMMENDED MATING PIN LENGTH:
LOWER ROW - .200" MIN., .285" MAX.
UPPER ROW - .200" MIN.
- 4.) REFER TO PRODUCT SPECIFICATION PS-71973-9999 FOR PERFORMANCE DATA
- 5.) MANUFACTURED DATE CODE - YEAR, WEEK.
- 6.) PACKAGING: FOR THIS PRODUCT IN TUBES SEE SHT. 6 & 7
FOR THIS PRODUCT IN TRAYS SEE SHT. 8 & 9

FINISHES


- 15 GOLD .000015 MINIMUM GOLD PLATE IN SELECT AREA OVER
.000050 MINIMUM NICKEL UNDERPLATE OVER-ALL WITH
.000075 MINIMUM TIN PLATE IN SELECT AREA.
- 30 GOLD .000030 MINIMUM GOLD PLATE IN SELECT AREA OVER
.000050 MINIMUM NICKEL UNDERPLATE OVER-ALL WITH
.000075 MINIMUM TIN PLATE IN SELECT AREA.
- 50 GOLD .000050 MINIMUM GOLD PLATE IN SELECT AREA OVER
.000050 MINIMUM NICKEL UNDERPLATE OVER-ALL WITH
.000100 MINIMUM TIN PLATE IN SELECT AREA.

.105
(2.67)


POINT OF
CONTACT



SECTION C-C



4 DIGIT DATE CODE
SEE NOTE 5





- ⊕ Ø.015(5) TAIL TO TAIL
⊕ Ø.020(5) X(5) Y(5) TAIL TO INSULATOR

OPTION "A" ASSEMBLY
STANDARD HOUSING

NOTE FOR LEAD FREE CONVERSION:

THE PRIMARY SHIPPING CARTON WILL BE
LABELED "COMPLIANT TO RoHS DIRECTIVE
2002/95/EC AND ELV ANNEX II OF
DIRECTIVE 2000/53/EC". CARTONS WITHOUT
THIS LABEL MAY CONTAIN PRODUCT WITH
LEAD.




OPTION "B" ASSEMBLY
STD. HOUSING W/MOUNTING EARS

SCALE 4:1

REFER TO OPT. A FOR ALL OTHER INFORMATION


OPTION "J" ASSEMBLY

OPTION "J" IS THE SAME AS OPTION "B" EXCEPT
DATE CODE IS NOT STAMPED ON HOUSING.




RECOMMENDED P.C.B.
LAYOUT

ADD OPTION K & L EC NO: S2010-0534 DRWN:KANG 2009/12/30 CHKD:ATSEE 2010/01/08 APPR:MLONG 2010/01/14	QUALITY SYMBOLS	DESCRIPTION	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE		SCALE	DESIGN UNITS	THIRD ANGLE PROJECTION			
					IN/MM		NTS	INCH				
				mm	INCH	DRAWN BY	DATE	TITLE EARLY ENTRY R/A RECPT .120"PC TAIL W/O LOWER ROW PINSTOP-.100" GRID				
			4 PLACES	± ---	± ---	DJB	1991/10/21					
			3 PLACES	± ---	± .010	CHECKED BY	DATE	MOLEX MOLEX INCORPORATED				
			2 PLACES	± 0.25	± ---	DJB	1991/10/21					
			1 PLACE	± ---	± ---	APPROVED BY	DATE	DOCUMENT NO. SDA-71973-****				
			ANGULAR ±1/2°		MLONG	2010/01/14						
			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		MATERIAL NO. SEE TABLE		SHEET NO. 1 OF 26					
					SIZE A3							THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION



4 DIGIT DATE CODE
SEE NOTE 5



OPTION "C" ASSEMBLY
STANDARD HOUSING

NOTE FOR LEAD FREE CONVERSION:
THE PRIMARY SHIPPING CARTON WILL BE
LABELED "COMPLIANT TO RoHS DIRECTIVE
2002/95/EC AND ELV ANNEX II OF
DIRECTIVE 2000/53/EC". CARTONS WITHOUT
THIS LABEL MAY CONTAIN PRODUCT WITH
LEAD.


tb_frame_A3_P_AM_T
Rev. F 2009/06/18

NOTES:



- 1.) MATERIAL-
INSULATOR - LCP, UL 94V-0, COLOR BLACK
CONTACTS - PHOSPHOR BRONZE
- 2.) SEE SHT. 9 & 10 FOR CHART DIMENSIONS AND EDP NO.'S
- 3.) RECOMMENDED MATING PIN LENGTH:
LOWER ROW - .200" MIN., .285" MAX.
UPPER ROW - .200" MIN.
- 4.) REFER TO PRODUCT SPECIFICATION PS-71973-9999 FOR
PERFORMANCE DATA
- 5.) MANUFACTURED DATE CODE - YEAR, WEEK.
- 6.) PACKAGING: FOR THIS PRODUCT IN TUBES SEE SHT. 10 & 11
FOR THIS PRODUCT IN TRAYS SEE SHT. 12 & 13

FINISHES

- | | |
|---------|--|
| 15 GOLD | .000015 MINIMUM GOLD PLATE IN SELECT AREA OVER
.000050 MINIMUM NICKEL UNDERPLATE OVER-ALL WITH
.000075 MINIMUM TIN PLATE IN SELECT AREA. |
| 30 GOLD | .000030 MINIMUM GOLD PLATE IN SELECT AREA OVER
.000050 MINIMUM NICKEL UNDERPLATE OVER-ALL WITH
.000075 MINIMUM TIN PLATE IN SELECT AREA. |
| 50 GOLD | .000050 MINIMUM GOLD PLATE IN SELECT AREA OVER
.000050 MINIMUM NICKEL UNDERPLATE OVER-ALL WITH
.000100 MINIMUM TIN PLATE IN SELECT AREA. |




SECTION C-C



OPTION "D" ASSEMBLY
STD. HOUSING W/MOUNTING EARS
SCALE 4:1

REFER TO OPT. C FOR ALL OTHER INFORMATION



RECOMMENDED P.C.B. LAYOUT

ADD OPTION K & L		QUALITY SYMBOLS		GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE		SCALE		DESIGN UNITS		THIRD ANGLE PROJECTION	
EC NO: S2010-0534		F _A =0		mm		IN/MM		NTS		INCH			
2009/12/30	DRWN:SKANG	F _B =0		INCH		DRAWN BY		DATE		TITLE			
2010/01/08	CHKD:ATSEE	F _P =0		4 PLACES ± --- ± ---		DATE		1991/10/21		EARLY ENTRY R/A RECPT			
2010/01/14	APPR:MLONG			3 PLACES ± --- ± .010		CHECKED BY		DATE		.120"PC TAIL W/O LOWER			
				2 PLACES ± 0.25 ± ---		DATE		1991/10/21		ROW PINSTOP-.100" GRID			
				1 PLACE ± --- ± ---		APPROVED BY		DATE		MOLEX INCORPORATED			
				ANGULAR ± 1/2°		MLONG		2010/01/14		SDA-71973-****			
				DRAFT WHERE APPLICABLE		MATERIAL NO.		DOCUMENT NO.		SHEET NO.			
				MUST REMAIN		SEE TABLE				2 OF 26			
				WITHIN DIMENSIONS		SIZE							
						A3							

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX
INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION



10 9 8 7 6 5 4 3 2 1

NOTES:

- 1.) MATERIAL -
INSULATOR - LCP, UL 94V-0, COLOR BLACK
CONTACTS - PHOSPHOR BRONZE
- 2.) SEE SHT. 13 & 14 FOR CHART DIMENSIONS AND EDP NO.'S
- 3.) RECOMMENDED MATING PIN LENGTH:
LOWER ROW - .200" MIN., .250" MAX.
UPPER ROW - .200" MIN.
- 4.) REFER TO PRODUCT SPECIFICATION PS-71973-9999 FOR PERFORMANCE DATA
- 5.) MANUFACTURED DATE CODE - YEAR, WEEK.
- 6.) PACKAGING: FOR THIS PRODUCT IN TUBES SEE SHT. 14 & 15
FOR THIS PRODUCT IN TRAYS SEE SHT. 16 & 17

FINISHES


- 15 GOLD .000015 MINIMUM GOLD PLATE IN SELECT AREA OVER
.000050 MINIMUM NICKEL UNDERPLATE OVER-ALL WITH
.000075 MINIMUM TIN PLATE IN SELECT AREA.
- 30 GOLD .000030 MINIMUM GOLD PLATE IN SELECT AREA OVER
.000050 MINIMUM NICKEL UNDERPLATE OVER-ALL WITH
.000075 MINIMUM TIN PLATE IN SELECT AREA.
- 50 GOLD .000050 MINIMUM GOLD PLATE IN SELECT AREA OVER
.000050 MINIMUM NICKEL UNDERPLATE OVER-ALL WITH
.000100 MINIMUM TIN PLATE IN SELECT AREA.





OPTION "E" ASSEMBLY
STANDARD HOUSING

NOTE FOR LEAD FREE CONVERSION:

THE PRIMARY SHIPPING CARTON WILL BE
LABELED "COMPLIANT TO ROHS DIRECTIVE
2002/95/EC AND ELV ANNEX II OF
DIRECTIVE 2000/53/EC". CARTONS WITHOUT
THIS LABEL MAY CONTAIN PRODUCT WITH
LEAD.




SECTION C-C



OPTION "F" ASSEMBLY
STD. HOUSING W/MOUNTING EARS
AND LOWER ROW PINSTOP
SCALE 4:1


REFER TO OPT. E FOR ALL OTHER INFORMATION




RECOMMENDED P.C.B. LAYOUT

GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE		SCALE		DESIGN UNITS		THIRD ANGLE PROJECTION	
		IN/MM		NTS		INCH			
		mm	INCH	DRAWN BY	DATE	TITLE			
4 PLACES		± .005	± .002	DJB	1991/10/21	EARLY ENTRY R/A RECPT .120"PC TAIL W/O LOWER ROW PINSTOP-.100" GRID MOLEX INCORPORATED		SHEET NO. 3 OF 26	
3 PLACES		± .010	± .005	CHECKED BY	DATE				
2 PLACES		± .025	± .010	DJB	1991/10/21				
1 PLACE		± .050	± .020	APPROVED BY	DATE				
ANGULAR ± 1/2°				MLONG	2010/01/14	DOCUMENT NO.			
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE TABLE		MATERIAL NO.		SDA-71973-****			
		SIZE A3		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION					

10 9 8 7 6 5 4 3 2 1



4 DIGIT DATE CODE
SEE NOTE 5



⊕ Ø.015(5) TAIL TO TAIL
⊕ Ø.020(5) X(5) Y(5) TAIL TO INSULATOR

OPTION "G" ASSEMBLY STANDARD HOUSING


NOTE FOR LEAD FREE CONVERSION:

THE PRIMARY SHIPPING CARTON WILL BE LABELED "COMPLIANT TO RoHS DIRECTIVE 2002/95/EC AND ELV ANNEX II OF DIRECTIVE 2000/53/EC". CARTONS WITHOUT THIS LABEL MAY CONTAIN PRODUCT WITH LEAD.



- NOTES:**
- 1.) MATERIAL -
INSULATOR - LCP, UL 94V-0, COLOR BLACK
CONTACTS - PHOSPHOR BRONZE
 - 2.) SEE SHT. 17 & 18 FOR CHART DIMENSIONS AND EDP NO.'S
 - 3.) RECOMMENDED MATING PIN LENGTH:
LOWER ROW - .200" MIN., .250" MAX.
UPPER ROW - .200" MIN.
 - 4.) REFER TO PRODUCT SPECIFICATION PS-71973-9999 FOR PERFORMANCE DATA
 - 5.) MANUFACTURED DATE CODE - YEAR, WEEK.
 - 6.) PACKAGING: FOR THIS PRODUCT IN TUBES SEE SHT. 18 & 19
FOR THIS PRODUCT IN TRAYS SEE SHT. 20 & 21

FINISHES

- 15 GOLD .000015 MINIMUM GOLD PLATE IN SELECT AREA OVER
.000050 MINIMUM NICKEL UNDERPLATE OVER-ALL WITH
.000075 MINIMUM TIN PLATE IN SELECT AREA.
- 30 GOLD .000030 MINIMUM GOLD PLATE IN SELECT AREA OVER
.000050 MINIMUM NICKEL UNDERPLATE OVER-ALL WITH
.000075 MINIMUM TIN PLATE IN SELECT AREA.
- 50 GOLD .000050 MINIMUM GOLD PLATE IN SELECT AREA OVER
.000050 MINIMUM NICKEL UNDERPLATE OVER-ALL WITH
.000100 MINIMUM TIN PLATE IN SELECT AREA.




SECTION C-C



OPTION "H" ASSEMBLY STD. HOUSING W/MOUNTING EARS AND LOWER PINSTOP SCALE 4:1



REFER TO OPT. G FOR ALL OTHER INFORMATION



RECOMMENDED P.C.B. LAYOUT

ADD OPTION K & L EC NO: S2010-0534 2009/12/30 DRWN:SKANG CHKD:ATSEE 2010/01/08 APPR:MLONG 2010/01/14			QUALITY SYMBOLS FA=0 FE=0 FP=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE IN/MM		SCALE NTS	DESIGN UNITS INCH	THIRD ANGLE PROJECTION
				mm	INCH	DRAWN BY DJB	DATE 1991/10/21	TITLE EARLY ENTRY R/A RECPT .120"PC TAIL W/O LOWER ROW PINSTOP-.100" GRID MOLEX INCORPORATED		
				4 PLACES ± --- ± ---	3 PLACES ± --- ± .010	CHECKED BY DJB	DATE 1991/10/21			
				2 PLACES ± 0.25 ± ---	1 PLACE ± --- ± ---	APPROVED BY MLONG	DATE 2010/01/14			
K		REV	ANGULAR ±1/2°		MATERIAL NO. SEE TABLE		DOCUMENT NO. SDA-71973-****		SHEET NO. 4 OF 26	
			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SIZE A3		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION			


10 9 8 7 6 5 4 3 2 1



RECOMMENDED P.C.B.
LAYOUT

SCALE 4:1

SECTION D-D



NOTES:


- 1.) MATERIAL -
INSULATOR - LCP, UL 94V-0, COLOR BLACK
CONTACTS - PHOSPHOR BRONZE
- 2.) SEE SHT. 22 FOR CHART DIMENSIONS AND ITEM NO.'S
- 3.) RECOMMENDED MATING PIN LENGTH:
LOWER ROW - .200" MINIMUM, .285" MAX.
UPPER ROW - .200" MINIMUM
- 4.) REFER TO PRODUCT SPECIFICATION PS-71973-9999 FOR PERFORMANCE DATA
- 5.) MANUFACTURED DATE CODE - YEAR, WEEK.
- 6.) PACKAGING: FOR THIS PRODUCT IN TUBES SEE SHT. 22

FINISHES PER ES-88-(***)

- 15 GOLD .000015 MINIMUM GOLD PLATE IN SELECT AREA OVER
.000050 MINIMUM NICKEL UNDERPLATE OVER-ALL WITH
.000075 MINIMUM TIN PLATE IN SELECT AREA.
- 30 GOLD .000030 MINIMUM GOLD PLATE IN SELECT AREA OVER
.000050 MINIMUM NICKEL UNDERPLATE OVER-ALL WITH
.000075 MINIMUM TIN PLATE IN SELECT AREA.
- 50 GOLD .000050 MINIMUM GOLD PLATE IN SELECT AREA OVER
.000050 MINIMUM NICKEL UNDERPLATE OVER-ALL WITH
.000100 MINIMUM TIN PLATE IN SELECT AREA.

NOTE FOR LEAD FREE CONVERSION:

THE PRIMARY SHIPPING CARTON WILL BE
LABELED "COMPLIANT TO RoHS DIRECTIVE
2002/95/EC AND ELV ANNEX II OF
DIRECTIVE 2000/53/EC". CARTONS WITHOUT
THIS LABEL MAY CONTAIN PRODUCT WITH
LEAD.



.028±.002
(0.71±0.05)
Ø .015 TAIL TO TAIL
Ø .020 X S Y TAIL TO INSULATOR
(SEE NOTE 7)

OPTION "I" ASSEMBLY

STANDARD HOUSING W/ PEGS AND MOUNTING EARS

ADD OPTION K & L	
EC NO: S2010-0534	2009/12/30
DRWN:SKANG	2010/01/08
CHKD:ATSEE	2010/01/14
APPR:MLONG	2010/01/14
DESCRIPTION	REV
QUALITY SYMBOLS	REV
F _A =0	
F _C =0	
F _P =0	

GENERAL TOLERANCES (UNLESS SPECIFIED)	
mm	INCH
4 PLACES ± ---	± ---
3 PLACES ± ---	± .010
2 PLACES ± 0.25	± ---
1 PLACE ± ---	± ---
ANGULAR ± 1/2°	
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS	

DIMENSION STYLE IN/MM	
DRAWN BY	DATE
DJB	1991/10/21
CHECKED BY	DATE
DJB	1991/10/21
APPROVED BY	DATE
MLONG	2010/01/14
MATERIAL NO.	
SEE TABLE	
SIZE	A3

SCALE	DESIGN UNITS	THIRD ANGLE PROJECTION
NTS	INCH	
EARLY ENTRY R/A RECPT .120"PC TAIL W/O LOWER ROW PINSTOP-.100" GRID		
MOLEX INCORPORATED		
DOCUMENT NO.		SHEET NO.
SDA-71973-****		5 OF 26
THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION		


9 8 7 6 5 4 3 2 1

FINISHES



- 15 GOLD .000015 MINIMUM GOLD PLATE IN SELECT AREA OVER
.000050 MINIMUM NICKEL UNDERPLATE OVER-ALL WITH
.000075 MINIMUM TIN PLATE IN SELECT AREA.
- 30 GOLD .000030 MINIMUM GOLD PLATE IN SELECT AREA OVER
.000050 MINIMUM NICKEL UNDERPLATE OVER-ALL WITH
.000075 MINIMUM TIN PLATE IN SELECT AREA.
- 50 GOLD .000050 MINIMUM GOLD PLATE IN SELECT AREA OVER
.000050 MINIMUM NICKEL UNDERPLATE OVER-ALL WITH
.000100 MINIMUM TIN PLATE IN SELECT AREA.

NOTES:

- 1.) MATERIAL-
INSULATOR - LCP, UL 94V-0, COLOR BLACK
CONTACTS - PHOSPHOR BRONZE
- 2.) SEE SHT.25 FOR CHART DIMENSIONS AND ITEM NO.'S
- 3.) RECOMMENDED MATING PIN LENGTH:
LOWER ROW - .200" MINIMUM, .285" MAX.
UPPER ROW - .200" MINIMUM
- 4.) REFER TO PRODUCT SPECIFICATION PS-71973-9999 FOR PERFORMANCE DATA
- 5.) MANUFACTURED DATE CODE - YEAR, WEEK.
- 6.) PACKAGING: FOR THIS PRODUCT IN TUBES SEE SHT.25



SECTION D-D




RECOMMENDED P.C.B.
LAYOUT

OPTION "K" ASSEMBLY
STANDARD HOUSING W/ PEGS

TAIL TO TAIL
TAIL TO INSULATOR
(SEE NOTE 8)

REV	DESCRIPTION	QUALITY SYMBOLS		GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE		SCALE	DESIGN UNITS	THIRD ANGLE PROJECTION
		mm	INCH	mm	INCH	IN/MM	NTS			
K	ADD OPTION K & L EC NO: S2010-0534 DRWN:SKANG 2009/12/30 CHKD:ATSEE 2010/01/08 APPR:MLONG 2010/01/14	F _A =0 F _C =0 F _P =0	4 PLACES 3 PLACES 2 PLACES 1 PLACE	± --- ± --- ± 0.25 ± ---	± --- ± .010 ± --- ± ---	DRAWN BY DJB CHECKED BY DJB APPROVED BY MLONG	DATE 1991/10/21 1991/10/21 2010/01/14	TITLE EARLY ENTRY R/A RECPT .120"PC TAIL W/O LOWER ROW PINSTOP-.100" GRID MOLEX INCORPORATED	DOCUMENT NO. SDA-71973-****	SHEET NO. 6 OF 26

10 9 8 7 6 5 4 3 2 1



FINISHES


15 GOLD .000015 MINIMUM GOLD PLATE IN SELECT AREA OVER
.000050 MINIMUM NICKEL UNDERPLATE OVER-ALL WITH
.000075 MINIMUM TIN PLATE IN SELECT AREA.

30 GOLD .000030 MINIMUM GOLD PLATE IN SELECT AREA OVER
.000050 MINIMUM NICKEL UNDERPLATE OVER-ALL WITH
.000075 MINIMUM TIN PLATE IN SELECT AREA.



50 GOLD .000050 MINIMUM GOLD PLATE IN SELECT AREA OVER
.000050 MINIMUM NICKEL UNDERPLATE OVER-ALL WITH
.000100 MINIMUM TIN PLATE IN SELECT AREA.

NOTES:

- 1.) MATERIAL-
INSULATOR - LCP, UL 94V-0, COLOR BLACK
CONTACTS - PHOSPHOR BRONZE
- 2.) SEE SHT. 22 FOR CHART DIMENSIONS AND ITEM NO.'S
- 3.) RECOMMENDED MATING PIN LENGTH:
LOWER ROW - .200" MINIMUM, .250" MAX.
UPPER ROW - .200" MINIMUM
- 4.) REFER TO PRODUCT SPECIFICATION PS-71973-9999 FOR
PERFORMANCE DATA
- 5.) MANUFACTURED DATE CODE - YEAR, WEEK.
- 6.) PACKAGING: FOR THIS PRODUCT IN TUBES SEE SHT. 26



SECTION D-D



RECOMMENDED P.C.B.
LAYOUT

OPTION "L" ASSEMBLY
STANDARD HOUSING W/ PEGS

±.015 TAIL TO TAIL
±.020 X S Y TAIL TO INSULATOR
(SEE NOTE 8)

ADD OPTION K & L EC NO: S2010-0534 DRWN:SKANG 2009/12/30 CHKD:ATSEE 2010/01/08 APPR:MLONG 2010/01/14 K	QUALITY SYMBOLS FA=0 FC=0 FP=0	DESCRIPTION REV	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE IN/MM		SCALE NTS	DESIGN UNITS INCH	THIRD ANGLE PROJECTION	
				mm	INCH	DRAWN BY DJB	DATE 1991/10/21	TITLE EARLY ENTRY R/A RECPT .120"PC TAIL W/O LOWER ROW PINSTOP-.100" GRID		
			4 PLACES	± ---	± ---	CHECKED BY DJB	DATE 1991/10/21			
			3 PLACES	± ---	± .010	APPROVED BY MLONG		DATE 2010/01/14		MOLEX MOLEX INCORPORATED
			2 PLACES	± 0.25	± ---					
	1 PLACE	± ---	± ---	ANGULAR ±1/2°		MATERIAL NO. SEE TABLE	DOCUMENT NO. SDA-71973-****	SHEET NO. 7 OF 26		
	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			SIZE A3		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION				

10		9		8		7		6		5		4		3		2		1											
NO. OF CKTS		OPTION A ASSEMBLY PACKAGED IN TUBES PER PK-70873-0138 (SEE SHEET I FOR FINISH SPECIFICATIONS)						DIMENSION				NO. OF CKTS		OPTION A ASSEMBLY PACKAGED IN TUBES PER PK-70873-0138 (SEE SHEET I FOR FINISH SPECIFICATIONS)						DIMENSION									
PER ROW	TOTAL			15 GOLD		30 GOLD		50 GOLD		A	B					15 GOLD		30 GOLD		50 GOLD		A	B						
4	8				71973-0204	71973-0304	71973-0404	.300 (7.62)	.395 (10.03)								71973-0233	71973-0333	71973-0433	3.200 (81.28)	3.295 (83.69)								
5	10				71973-0205	71973-0305	71973-0405	.400 (10.16)	.495 (12.57)								71973-0234	71973-0334	71973-0434	3.300 (83.82)	3.395 (86.23)								
6	12				71973-0206	71973-0306	71973-0406	.500 (12.70)	.595 (15.11)								71973-0235	71973-0335	71973-0435	3.400 (86.36)	3.495 (88.77)								
7	14				71973-0207	71973-0307	71973-0407	.600 (15.24)	.695 (17.65)								71973-0236	71973-0336	71973-0436	3.500 (88.90)	3.595 (91.31)								
8	16				71973-0208	71973-0308	71973-0408	.700 (17.78)	.795 (20.19)																				
9	18				71973-0209	71973-0309	71973-0409	.800 (20.32)	.895 (22.73)																				
10	20				71973-0210	71973-0310	71973-0410	.900 (22.86)	.995 (25.27)																				
11	22				71973-0211	71973-0311	71973-0411	1.000 (25.40)	1.095 (27.81)																				
12	24				71973-0212	71973-0312	71973-0412	1.100 (27.94)	1.195 (30.35)																				
13	26				71973-0213	71973-0313	71973-0413	1.200 (30.48)	1.295 (32.89)																				
14	28				71973-0214	71973-0314	71973-0414	1.300 (33.02)	1.395 (35.43)																				
15	30				71973-0215	71973-0315	71973-0415	1.400 (35.56)	1.495 (37.97)																				
16	32				71973-0216	71973-0316	71973-0416	1.500 (38.10)	1.595 (40.51)																				
17	34				71973-0217	71973-0317	71973-0417	1.600 (40.64)	1.695 (43.05)																				
18	36				71973-0218	71973-0318	71973-0418	1.700 (43.18)	1.795 (45.59)																				
19	38				71973-0219	71973-0319	71973-0419	1.800 (45.72)	1.895 (48.13)																				
20	40				71973-0220	71973-0320	71973-0420	1.900 (48.26)	1.995 (50.67)																				
21	42				71973-0221	71973-0321	71973-0421	2.000 (50.80)	2.095 (53.21)																				
22	44				71973-0222	71973-0322	71973-0422	2.100 (53.34)	2.195 (55.75)																				
23	46				71973-0223	71973-0323	71973-0423	2.200 (55.88)	2.295 (58.29)																				
24	48				71973-0224	71973-0324	71973-0424	2.300 (58.42)	2.395 (60.83)																				
25	50				71973-0225	71973-0325	71973-0425	2.400 (60.96)	2.495 (63.37)																				
26	52				71973-0226	71973-0326	71973-0426	2.500 (63.50)	2.595 (65.91)																				
27	54				71973-0227	71973-0327	71973-0427	2.600 (66.04)	2.695 (68.45)																				
28	56				71973-0228	71973-0328	71973-0428	2.700 (68.58)	2.795 (70.99)																				
29	58				71973-0229	71973-0329	71973-0429	2.800 (71.12)	2.895 (73.53)																				
30	60				71973-0230	71973-0330	71973-0430	2.900 (73.66)	2.995 (76.07)																				
31	62				71973-0231	71973-0331	71973-0431	3.000 (76.20)	3.095 (78.61)																				
32	64				71973-0232	71973-0332	71973-0432	3.100 (78.74)	3.195 (81.15)																				
ADD OPTION K & L EC NO: S2010-0534 DRWN:SKANG 2009/12/30 CHKD:ATSEE 2010/01/08 APPR:MLONG 2010/01/14 K										QUALITY SYMBOLS F=0 F=0 F=0		GENERAL TOLERANCES (UNLESS SPECIFIED) mm INCH 4 PLACES ± --- ± --- 3 PLACES ± --- ± .010 2 PLACES ± 0.25 ± --- 1 PLACE ± --- ± --- ANGULAR ± 1/2°				DIMENSION STYLE IN/MM DRAWN BY DATE DJB 1991/10/21 CHECKED BY DATE DJB 1991/10/21 APPROVED BY DATE MLONG 2010/01/14 MATERIAL NO.				SCALE NTS		DESIGN UNITS INCH		THIRD ANGLE PROJECTION					
										DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				SEE TABLE				THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION				MOLEX MOLEX INCORPORATED				SHEET NO. 8 OF 26			
tb_frame_A3_P_AM.T Rev. F 2009/06/18										9		8		7		6		5		4		3		2		1			

tb_frame_A3_P_AM_T
Rev. F 2009/06/18

[illegible]

10		9		8		7		6		5		4		3		2		1					
NO. OF CKTS		OPTION D ASSEMBLY PACKAGED IN TUBES PER PK-70873-0139 (SEE SHEET I FOR FINISH SPECIFICATIONS)						DIMENSION				NO. OF CKTS		OPTION D ASSEMBLY PACKAGED IN TUBES PER PK-70873-0139 (SEE SHEET I FOR FINISH SPECIFICATIONS)						DIMENSION			
PER ROW	TOTAL			I5 GOLD	30 GOLD	50 GOLD	A	B		D	PER ROW	TOTAL			I5 GOLD	30 GOLD	50 GOLD	A	B		D		
4	8			X 71973-2604	X 71973-2704	X 71973-2804	.300 (7.62)	.395 (10.03)		.658 (16.71)	33	66			X 71973-2633	X 71973-2733	X 71973-2833	3.200 (81.28)	3.295 (83.69)		3.558 (90.37)		
5	10			X 71973-2605	X 71973-2705	X 71973-2805	.400 (10.16)	.495 (12.57)		.758 (19.25)	34	68			X 71973-2634	X 71973-2734	X 71973-2834	3.300 (83.82)	3.395 (86.23)		3.658 (92.91)		
6	12			X 71973-2606	X 71973-2706	X 71973-2806	.500 (12.70)	.595 (15.11)		.858 (21.79)	35	70			X 71973-2635	X 71973-2735	X 71973-2835	3.400 (86.36)	3.495 (88.77)		3.758 (95.45)		
7	14			X 71973-2607	X 71973-2707	X 71973-2807	.600 (15.24)	.695 (17.65)		.958 (24.33)	36	72			X 71973-2636	X 71973-2736	X 71973-2836	3.500 (88.90)	3.595 (91.31)		3.858 (97.99)		
8	16			X 71973-2608	X 71973-2708	X 71973-2808	.700 (17.78)	.795 (20.19)		1.058 (26.87)													
9	18			X 71973-2609	X 71973-2709	X 71973-2809	.800 (20.32)	.895 (22.73)		1.158 (29.41)													
10	20			X 71973-2610	X 71973-2710	X 71973-2810	.900 (22.86)	.995 (25.27)		1.258 (31.95)													
11	22			X 71973-2611	X 71973-2711	X 71973-2811	1.000 (25.40)	1.095 (27.81)		1.358 (34.49)													
12	24			X 71973-2612	X 71973-2712	X 71973-2812	1.100 (27.94)	1.195 (30.35)		1.458 (37.03)													
13	26			X 71973-2613	X 71973-2713	X 71973-2813	1.200 (30.48)	1.295 (32.89)		1.558 (39.57)													
14	28			X 71973-2614	X 71973-2714	X 71973-2814	1.300 (33.02)	1.395 (35.43)		1.658 (42.11)													
15	30			X 71973-2615	X 71973-2715	X 71973-2815	1.400 (35.56)	1.495 (37.97)		1.758 (44.65)													
16	32			X 71973-2616	X 71973-2716	X 71973-2816	1.500 (38.10)	1.595 (40.51)		1.858 (47.19)													
17	34			X 71973-2617	X 71973-2717	X 71973-2817	1.600 (40.64)	1.695 (43.05)		1.958 (49.73)													
18	36			X 71973-2618	X 71973-2718	X 71973-2818	1.700 (43.18)	1.795 (45.59)		2.058 (52.27)													
19	38			X 71973-2619	X 71973-2719	X 71973-2819	1.800 (45.72)	1.895 (48.13)		2.158 (54.81)													
20	40			X 71973-2620	X 71973-2720	X 71973-2820	1.900 (48.26)	1.995 (50.67)		2.258 (57.35)													
21	42			X 71973-2621	X 71973-2721	X 71973-2821	2.000 (50.80)	2.095 (53.21)		2.358 (59.89)													
22	44			X 71973-2622	X 71973-2722	X 71973-2822	2.100 (53.34)	2.195 (55.75)		2.458 (62.43)													
23	46			X 71973-2623	X 71973-2723	X 71973-2823	2.200 (55.88)	2.295 (58.29)		2.558 (64.97)													
24	48			X 71973-2624	X 71973-2724	X 71973-2824	2.300 (58.42)	2.395 (60.83)		2.658 (67.51)													
25	50			X 71973-2625	X 71973-2725	X 71973-2825	2.400 (60.96)	2.495 (63.37)		2.758 (70.05)													
26	52			X 71973-2626	X 71973-2726	X 71973-2826	2.500 (63.50)	2.595 (65.91)		2.858 (72.59)													
27	54			X 71973-2627	X 71973-2727	X 71973-2827	2.600 (66.04)	2.695 (68.45)		2.958 (75.13)													
28	56			X 71973-2628	X 71973-2728	X 71973-2828	2.700 (68.58)	2.795 (70.99)		3.058 (77.67)													
29	58			X 71973-2629	X 71973-2729	X 71973-2829	2.800 (71.12)	2.895 (73.53)		3.158 (80.21)													
30	60			X 71973-2630	X 71973-2730	X 71973-2830	2.900 (73.66)	2.995 (76.07)		3.258 (82.75)													
31	62			X 71973-2631	X 71973-2731	X 71973-2831	3.000 (76.20)	3.095 (78.61)		3.358 (85.29)													
32	64			X 71973-2632	X 71973-2732	X 71973-2832	3.100 (78.74)	3.195 (81.15)		3.458 (87.83)													
X INDICATES TOOLING IS NOT AVAILABLE							ADD OPTION K & L EC NO: S2010-0534 DRWN:SKANG 2009/12/30 CHKD:ATSEE 2010/01/08 APPR:MLONG 2010/01/14		QUALITY SYMBOLS FA=0 FG=0 FP=0		GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE IN/MM		SCALE NTS		DESIGN UNITS INCH		THIRD ANGLE PROJECTION				
													DRAWN BY DATE DJB 1991/10/21		TITLE EARLY ENTRY R/A RECPT .120"PC TAIL W/O LOWER ROW PINSTOP-.100" GRID								
													CHECKED BY DATE DJB 1991/10/21		MOLEX INCORPORATED								
													APPROVED BY DATE MLONG 2010/01/14		DOCUMENT NO. SDA-71973-****								
A							K		REV		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE TABLE		SHEET NO. 13 OF 26								
											SIZE A3		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION										
fb_frame_A3_P_AM.T Rev. F 2009/06/18		9		8		7		6		5		4		3		2		1					

tb_frame_A3_P_AM_T
Rev. F 2009/06/18

tb_frame_A3_P_AM_T
Rev. F 2009/06/18

10			9			8			7			6			5			4			3			2			1		
NO. OF CKTS		OPTION E ASSEMBLY PACKAGED IN TUBES PER PK-70873-0138 (SEE SHEET I FOR FINISH SPECIFICATIONS)						DIMENSION				NO. OF CKTS		OPTION E ASSEMBLY PACKAGED IN TUBES PER PK-70873-0138 (SEE SHEET I FOR FINISH SPECIFICATIONS)						DIMENSION									
PER ROW	TOTAL			15 GOLD		30 GOLD		50 GOLD		A	B			PER ROW	TOTAL			15 GOLD		30 GOLD		50 GOLD		A	B				
4	8			71973-3404	71973-3504	71973-3604	.300 (7.62)	.395 (10.03)					34	68			71973-3434	71973-3534	71973-3634	3.300 (83.82)	3.395 (86.23)								
5	10			71973-3405	71973-3505	71973-3605	.400 (10.16)	.495 (12.57)					35	70			71973-3435	71973-3535	71973-3635	3.400 (86.36)	3.495 (88.77)								
6	12			71973-3406	71973-3506	71973-3606	.500 (12.70)	.595 (15.11)					36	72			71973-3436	71973-3536	71973-3636	3.500 (88.90)	3.595 (91.31)								
7	14			71973-3407	71973-3507	71973-3607	.600 (15.24)	.695 (17.65)																					
8	16			71973-3408	71973-3508	71973-3608	.700 (17.78)	.795 (20.19)																					
9	18			71973-3409	71973-3509	71973-3609	.800 (20.32)	.895 (22.73)																					
10	20			71973-3410	71973-3510	71973-3610	.900 (22.86)	.995 (25.27)																					
11	22			71973-3411	71973-3511	71973-3611	1.000 (25.40)	1.095 (27.81)																					
12	24			71973-3412	71973-3512	71973-3612	1.100 (27.94)	1.195 (30.35)																					
13	26			71973-3413	71973-3513	71973-3613	1.200 (30.48)	1.295 (32.89)																					
14	28			71973-3414	71973-3514	71973-3614	1.300 (33.02)	1.395 (35.43)																					
15	30			71973-3415	71973-3515	71973-3615	1.400 (35.56)	1.495 (37.97)																					
16	32			71973-3416	71973-3516	71973-3616	1.500 (38.10)	1.595 (40.51)																					
17	34			71973-3417	71973-3517	71973-3617	1.600 (40.64)	1.695 (43.05)																					
18	36			71973-3418	71973-3518	71973-3618	1.700 (43.18)	1.795 (45.59)																					
19	38			71973-3419	71973-3519	71973-3619	1.800 (45.72)	1.895 (48.13)																					
20	40			71973-3420	71973-3520	71973-3620	1.900 (48.26)	1.995 (50.67)																					
21	42			71973-3421	71973-3521	71973-3621	2.000 (50.80)	2.095 (53.21)																					
22	44			71973-3422	71973-3522	71973-3622	2.100 (53.34)	2.195 (55.75)																					
23	46			71973-3423	71973-3523	71973-3623	2.200 (55.88)	2.295 (58.29)																					
24	48			71973-3424	71973-3524	71973-3624	2.300 (58.42)	2.395 (60.83)																					
25	50			71973-3425	71973-3525	71973-3625	2.400 (60.96)	2.495 (63.37)																					
26	52			71973-3426	71973-3526	71973-3626	2.500 (63.50)	2.595 (65.91)																					
27	54			71973-3427	71973-3527	71973-3627	2.600 (66.04)	2.695 (68.45)																					
28	56			71973-3428	71973-3528	71973-3628	2.700 (68.58)	2.795 (70.99)																					
29	58			71973-3429	71973-3529	71973-3629	2.800 (71.12)	2.895 (73.53)																					
30	60			71973-3430	71973-3530	71973-3630	2.900 (73.66)	2.995 (76.07)																					
31	62			71973-3431	71973-3531	71973-3631	3.000 (76.20)	3.095 (78.61)																					
32	64			71973-3432	71973-3532	71973-3632	3.100 (78.74)	3.195 (81.15)																					
33	66			71973-3433	71973-3533	71973-3633	3.200 (81.28)	3.295 (83.69)																					
*X INDICATES TOOLING IS NOT AVAILABLE										ADD OPTION K & L EC NO: S2010-0534 DRWN:SKANG 2009/12/30 CHKD:ATSEE 2010/01/08 APPR:MLONG 2010/01/14			QUALITY SYMBOLS F=0 F=0 F=0		GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE IN/MM		SCALE NTS		DESIGN UNITS INCH		THIRD ANGLE PROJECTION						
															mm		DATE		TITLE										
															INCH		DATE		EARLY ENTRY R/A RECPT .120"PC TAIL W/O LOWER ROW PINSTOP-.100" GRID										
															DATE		MOLEX INCORPORATED												
										DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		MATERIAL NO. SEE TABLE		DOCUMENT NO. SDA-71973-****		SHEET NO. 16 OF 26													
												SIZE A3		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION															
fb_frame_A3_P_AM_T Rev. F 2009/06/18			9			8			7			6			5			4			3			2			1		

tb_frame_A3_P_AM_T
Rev. F 2009/06/18

10		9		8		7		6		5		4		3		2		1													
F	NO. OF CKTS		OPTION E ASSEMBLY PACKAGED IN TRAYS PER PK-70873-0239 (SEE SHEET I FOR FINISH SPECIFICATIONS)						DIMENSION		NO. OF CKTS	OPTION E ASSEMBLY PACKAGED IN TRAYS PER PK-70873-0239 (SEE SHEET I FOR FINISH SPECIFICATIONS)						DIMENSION		F											
	PER ROW	TOTAL			15 GOLD	30 GOLD	50 GOLD	A	B				15 GOLD	30 GOLD	50 GOLD	A	B														
4	8				71973-8204	71973-8304	71973-8404	.300 (7.62)	.395 (10.03)					71973-8234	71973-8334	71973-8434	3.300 (83.82)	3.395 (86.23)													
5	10				71973-8205	71973-8305	71973-8405	.400 (10.16)	.495 (12.57)					71973-8235	71973-8335	71973-8435	3.400 (86.36)	3.495 (88.77)													
6	12				71973-8206	71973-8306	71973-8406	.500 (12.70)	.595 (15.11)					71973-8236	71973-8336	71973-8436	3.500 (88.90)	3.595 (91.31)													
7	14				71973-8207	71973-8307	71973-8407	.600 (15.24)	.695 (17.65)																						
8	16				71973-8208	71973-8308	71973-8408	.700 (17.78)	.795 (20.19)																						
9	18				71973-8209	71973-8309	71973-8409	.800 (20.32)	.895 (22.73)																						
10	20				71973-8210	71973-8310	71973-8410	.900 (22.86)	.995 (25.27)																						
11	22				71973-8211	71973-8311	71973-8411	1.000 (25.40)	1.095 (27.81)																						
12	24				71973-8212	71973-8312	71973-8412	1.100 (27.94)	1.195 (30.35)																						
13	26				71973-8213	71973-8313	71973-8413	1.200 (30.48)	1.295 (32.89)																						
14	28				71973-8214	71973-8314	71973-8414	1.300 (33.02)	1.395 (35.43)																						
15	30				71973-8215	71973-8315	71973-8415	1.400 (35.56)	1.495 (37.97)																						
16	32				71973-8216	71973-8316	71973-8416	1.500 (38.10)	1.595 (40.51)																						
17	34				71973-8217	71973-8317	71973-8417	1.600 (40.64)	1.695 (43.05)																						
18	36				71973-8218	71973-8318	71973-8418	1.700 (43.18)	1.795 (45.59)																						
19	38				71973-8219	71973-8319	71973-8419	1.800 (45.72)	1.895 (48.13)																						
20	40				71973-8220	71973-8320	71973-8420	1.900 (48.26)	1.995 (50.67)																						
21	42				71973-8221	71973-8321	71973-8421	2.000 (50.80)	2.095 (53.21)																						
22	44				71973-8222	71973-8322	71973-8422	2.100 (53.34)	2.195 (55.75)																						
23	46				71973-8223	71973-8323	71973-8423	2.200 (55.88)	2.295 (58.29)																						
24	48				71973-8224	71973-8324	71973-8424	2.300 (58.42)	2.395 (60.83)																						
25	50				71973-8225	71973-8325	71973-8425	2.400 (60.96)	2.495 (63.37)																						
26	52				71973-8226	71973-8326	71973-8426	2.500 (63.50)	2.595 (65.91)																						
27	54				71973-8227	71973-8327	71973-8427	2.600 (66.04)	2.695 (68.45)																						
28	56				71973-8228	71973-8328	71973-8428	2.700 (68.58)	2.795 (70.99)																						
29	58				71973-8229	71973-8329	71973-8429	2.800 (71.12)	2.895 (73.53)																						
30	60				71973-8230	71973-8330	71973-8430	2.900 (73.66)	2.995 (76.07)																						
31	62				71973-8231	71973-8331	71973-8431	3.000 (76.20)	3.095 (78.61)																						
32	64				71973-8232	71973-8332	71973-8432	3.100 (78.74)	3.195 (81.15)																						
33	66				71973-8233	71973-8333	71973-8433	3.200 (81.28)	3.295 (83.69)																						
X INDICATES TOOLING IS NOT AVAILABLE.																				ADD OPTION K & L EC NO: S2010-0534 DRWN:SKANG 2009/12/30 CHKD:ATSEE 2010/01/08 APPR:MLONG 2010/01/14		DESCRIPTION REV	QUALITY SYMBOLS F=0 F=0 F=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE IN/MM		SCALE NTS	DESIGN UNITS INCH	THIRD ANGLE PROJECTION	
																								mm INCH		DRAWN BY DATE DJB 1991/10/21		TITLE EARLY ENTRY R/A RECPT .120"PC TAIL W/O LOWER ROW PINSTOP-.100" GRID			
																								DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		APPROVED BY DATE MLONG 2010/01/14		MOLEX INCORPORATED			
SIZE A3		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION										DOCUMENT NO. SDA-71973-****		SHEET NO. 18 OF 26																	
tb_frame_A3_P_AM_T Rev. F 2009/06/18		9	8	7	6	5	4	3	2	1	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																				

	10		9		8		7		6		5		4		3		2		1			
F	NO. OF CKTS		OPTION F ASSEMBLY PACKAGED IN TRAYS PER PK-70873-0239 (SEE SHEET I FOR FINISH SPECIFICATIONS)				DIMENSION				NO. OF CKTS		OPTION F ASSEMBLY PACKAGED IN TRAYS PER PK-70873-0239 (SEE SHEET I FOR FINISH SPECIFICATIONS)				DIMENSION					
	PER ROW	TOTAL			15 GOLD	30 GOLD	50 GOLD	A	B		D	PER ROW	TOTAL			15 GOLD	30 GOLD	50 GOLD	A	B		D
	4	8			71973-8604	71973-8704	71973-8804	.300 (7.62)	.395 (10.03)		.658 (16.71)	34	68			71973-8634	71973-8734	71973-8834	3.300 (83.82)	3.395 (86.23)		3.658 (92.91)
	5	10			71973-8605	71973-8705	71973-8805	.400 (10.16)	.495 (12.57)		.758 (19.25)	35	70			71973-8635	71973-8735	71973-8835	3.400 (86.36)	3.495 (88.77)		3.758 (95.45)
	6	12			71973-8606	71973-8706	71973-8806	.500 (12.70)	.595 (15.11)		.858 (21.79)	36	72			71973-8636	71973-8736	71973-8836	3.500 (88.90)	3.595 (91.31)		3.858 (97.99)
	7	14			71973-8607	71973-8707	71973-8807	.600 (15.24)	.695 (17.65)		.958 (24.33)											
	8	16			71973-8608	71973-8708	71973-8808	.700 (17.78)	.795 (20.19)		1.058 (26.87)											
	9	18			71973-8609	71973-8709	71973-8809	.800 (20.32)	.895 (22.73)		1.158 (29.41)											
E	10	20			71973-8610	71973-8710	71973-8810	.900 (22.86)	.995 (25.27)		1.258 (31.95)											
	11	22			71973-8611	71973-8711	71973-8811	1.000 (25.40)	1.095 (27.81)		1.358 (34.49)											
	12	24			71973-8612	71973-8712	71973-8812	1.100 (27.94)	1.195 (30.35)		1.458 (37.03)											
	13	26			71973-8613	71973-8713	71973-8813	1.200 (30.48)	1.295 (32.89)		1.558 (39.57)											
	14	28			71973-8614	71973-8714	71973-8814	1.300 (33.02)	1.395 (35.43)		1.658 (42.11)											
	15	30			71973-8615	71973-8715	71973-8815	1.400 (35.56)	1.495 (37.97)		1.758 (44.65)											
	16	32			71973-8616	71973-8716	71973-8816	1.500 (38.10)	1.595 (40.51)		1.858 (47.19)											
D	17	34			71973-8617	71973-8717	71973-8817	1.600 (40.64)	1.695 (43.05)		1.958 (49.73)											
	18	36			71973-8618	71973-8718	71973-8818	1.700 (43.18)	1.795 (45.59)		2.058 (52.27)											
	19	38			71973-8619	71973-8719	71973-8819	1.800 (45.72)	1.895 (48.13)		2.158 (54.81)											
	20	40			71973-8620	71973-8720	71973-8820	1.900 (48.26)	1.995 (50.67)		2.258 (57.35)											
	21	42			71973-8621	71973-8721	71973-8821	2.000 (50.80)	2.095 (53.21)		2.358 (59.89)											
	22	44			71973-8622	71973-8722	71973-8822	2.100 (53.34)	2.195 (55.75)		2.458 (62.43)											
	23	46			71973-8623	71973-8723	71973-8823	2.200 (55.88)	2.295 (58.29)		2.558 (64.97)											
C	24	48			71973-8624	71973-8724	71973-8824	2.300 (58.42)	2.395 (60.83)		2.658 (67.51)											
	25	50			71973-8625	71973-8725	71973-8825	2.400 (60.96)	2.495 (63.37)		2.758 (70.05)											
	26	52			71973-8626	71973-8726	71973-8826	2.500 (63.50)	2.595 (65.91)		2.858 (72.59)											
	27	54			71973-8627	71973-8727	71973-8827	2.600 (66.04)	2.695 (68.45)		2.958 (75.13)											
	28	56			71973-8628	71973-8728	71973-8828	2.700 (68.58)	2.795 (70.99)		3.058 (77.67)											
	29	58			71973-8629	71973-8729	71973-8829	2.800 (71.12)	2.895 (73.53)		3.158 (80.21)											
	30	60			71973-8630	71973-8730	71973-8830	2.900 (73.66)	2.995 (76.07)		3.258 (82.75)											
B	31	62			71973-8631	71973-8731	71973-8831	3.000 (76.20)	3.095 (78.61)		3.358 (85.29)											
	32	64			71973-8632	71973-8732	71973-8832	3.100 (78.74)	3.195 (81.15)		3.458 (87.83)											
	33	66			71973-8633	71973-8733	71973-8833	3.200 (81.28)	3.295 (83.69)		3.558 (90.37)											
A			*X* INDICATES TOOLING IS NOT AVAILABLE.																			

10										9										7										6										5										4										3										2										1																																																											
NO. OF CKTS										OPTION G ASSEMBLY PACKAGED IN TUBES PER PK-70873-0138 (SEE SHEET I FOR FINISH SPECIFICATIONS)										DIMENSION										NO. OF CKTS										OPTION G ASSEMBLY PACKAGED IN TUBES PER PK-70873-0138 (SEE SHEET I FOR FINISH SPECIFICATIONS)										DIMENSION																																																																																									
PER ROW										TOTAL										A										B										PER ROW										TOTAL										A										B																																																																					
4										8										X 71973-5004										X 71973-5104										X 71973-5204										.300 (7.62)										.395 (10.03)										32										64										X 71973-5032										X 71973-5132										X 71973-5232										3.100 (78.74)										3.195 (81.15)									
5										10										X 71973-5005										X 71973-5105										X 71973-5205										.400 (10.16)										.495 (12.57)										33										66										X 71973-5033										X 71973-5133										X 71973-5233										3.200 (81.28)										3.295 (83.69)									
6										12										X 71973-5006										X 71973-5106										X 71973-5206										.500 (12.70)										.595 (15.11)										34										68										X 71973-5034										X 71973-5134										X 71973-5234										3.300 (83.82)										3.395 (86.23)									
7										14										X 71973-5007										X 71973-5107										X 71973-5207										.600 (15.24)										.695 (17.65)										35										70										X 71973-5035										X 71973-5135										X 71973-5235										3.400 (86.36)										3.495 (88.77)									
8										16										X 71973-5008										X 71973-5108										X 71973-5208										.700 (17.78)										.795 (20.19)										36										72										X 71973-5036										X 71973-5136										X 71973-5236										3.500 (88.90)										3.595 (91.31)									
9										18										X 71973-5009										X 71973-5109										X 71973-5209										.800 (20.32)										.895 (22.73)																																																																															
E										10										X 71973-5010										X 71973-5110										X 71973-5210										.900 (22.86)										.995 (25.27)																																																																															
										11										X 71973-5011										X 71973-5111										X 71973-5211										1.000 (25.40)										1.095 (27.81)																																																																															
										12										X 71973-5012										X 71973-5112										X 71973-5212										1.100 (27.94)										1.195 (30.35)																																																																															
										13										X 71973-5013										X 71973-5113										X 71973-5213										1.200 (30.48)										1.295 (32.89)																																																																															
										14										X 71973-5014										X 71973-5114										X 71973-5214										1.300 (33.02)										1.395 (35.43)																																																																															
										15										X 71973-5015										X 71973-5115										X 71973-5215										1.400 (35.56)										1.495 (37.97)																																																																															
D										16										X 71973-5016										X 71973-5116										X 71973-5216										1.500 (38.10)										1.595 (40.51)																																																																															
										17										X 71973-5017										X 71973-5117										X 71973-5217										1.600 (40.64)										1.695 (43.05)																																																																															
										18										X 71973-5018										X 71973-5118										X 71973-5218										1.700 (43.18)										1.795 (45.59)																																																																															
										19										X 71973-5019										X 71973-5119										X 71973-5219										1.800 (45.72)										1.895 (48.13)																																																																															
										20										X 71973-5020										X 71973-5120										X 71973-5220										1.900 (48.26)										1.995 (50.67)																																																																															
										21										X 71973-5021										X 71973-5121										X 71973-5221										2.000 (50.80)										2.095 (53.21)																																																																															
										22										X 71973-5022										X 71973-5122										X 71973-5222										2.100 (53.34)										2.195 (55.75)																																																																															
C										23										X 71973-5023										X 71973-5123										X 71973-5223										2.200 (55.88)										2.295 (58.29)																																																																															
										24										X 71973-5024										X 71973-5124										X 71973-5224										2.300 (58.42)										2.395 (60.83)																																																																															
										25										X 71973-5025										X 71973-5125										X 71973-5225										2.400 (60.96)										2.495 (63.37)																																																																															
										26										X 71973-5026										X 71973-5126										X 71973-5226										2.500 (63.50)										2.595 (65.91)																																																																															
										27										X 71973-5027										X 71973-5127										X 71973-5227										2.600 (66.04)										2.695 (68.45)																																																																															
										28										X 71973-5028										X 71973-5128										X 71973-5228										2.700 (68.58)										2.795 (70.99)																																																																															
B										29										X 71973-5029										X 71973-5129										X 71973-5229										2.800 (71.12)										2.895 (73.53)																																																																															
										30										X 71973-5030										X 71973-5130										X 71973-5230										2.900 (73.66)										2.995 (76.07)																																																																															
										31										X 71973-5031										X 71973-5131										X 71973-5231										3.000 (76.20)										3.095 (78.61)																																																																															
"X" INDICATES TOOLING IS NOT AVAILABLE.										ADD OPTION K & L EC NO: S2010-0534 DRWN:SKANG CHKD:ATSEE APPR:MLONG 2009/12/30 2010/01/08 2010/01/14										QUALITY SYMBOLS F _A =0 F _B =0 F _P =0										GENERAL TOLERANCES (UNLESS SPECIFIED)										DIMENSION STYLE IN/MM										SCALE NTS										DESIGN UNITS INCH										THIRD ANGLE PROJECTION																																																																					
																														4 PLACES ± --- ± ---										DRAWN BY DATE										TITLE																																																																																									
																														3 PLACES ± --- ± .010										CHECKED BY DATE																																																																																																			
																														2 PLACES ± 0.25 ± ---										APPROVED BY DATE																																																																																																			
																														1 PLACE ± --- ± ---										ANGULAR ± 1/2°										MATERIAL NO.										DOCUMENT NO.										SHEET NO.																																																																					
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS										SIZE A3										THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION										SEE TABLE										SDA-71973-****										20 OF 26																																																																																									
tb_frame_A3_P_AM_T Rev. F 2009/06/18										9										8										7										6										5										4										3										2										1																																																	

10			9			8			7			6			5			4			3			2			1																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																												
F	NO. OF CKTS		OPTION H ASSEMBLY PACKAGED IN TUBES PER PK-70873-0139 (SEE SHEET I FOR FINISH SPECIFICATIONS)									DIMENSION				NO. OF CKTS	OPTION H ASSEMBLY PACKAGED IN TUBES PER PK-70873-0139 (SEE SHEET I FOR FINISH SPECIFICATIONS)									DIMENSION				F																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																									
	PER ROW	TOTAL			15 GOLD			30 GOLD			50 GOLD			A	B			D			15 GOLD			30 GOLD			50 GOLD				A	B		D																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																					

X INDICATES TOOLING IS NOT AVAILABLE.

A	ADD OPTION K & L		QUALITY SYMBOLS		GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE		SCALE		DESIGN UNITS		THIRD ANGLE PROJECTION		A
	EC NO:	2009/12/30	DRWN:SKANG	2010/01/08	CHKD:ATSEE	2010/01/14	APPR:MLONG	REV	DESCRIPTION	mm	INCH	DRAWN BY	DATE	TITLE	
												DJB	1991/10/21	EARLY ENTRY R/A RECPT	
												DJB	1991/10/21	.120"PC TAIL W/O LOWER	
												DJB	1991/10/21	ROW PINSTOP-.100" GRID	
												MLONG	2010/01/14	MOLEX INCORPORATED	
												MLONG	2010/01/14	SDA-71973-****	
												MLONG	2010/01/14	21 OF 26	
												MLONG	2010/01/14	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION	

[illegible]

[illegible]

10		9		8		7		6		5		4		3		2		1			
NO. OF CKTS		OPTION I ASSEMBLY PACKAGED IN TUBES PER PK-70873-0138 (SEE SHEET I FOR FINISH SPECIFICATIONS)					DIMENSION				NO. OF CKTS		OPTION I ASSEMBLY PACKAGED IN TUBES PER PK-70873-0138 (SEE SHEET I FOR FINISH SPECIFICATIONS)					DIMENSION			
PER ROW	TOTAL			15 GOLD	30 GOLD	50 GOLD	A	B	C	D	PER ROW	TOTAL			15 GOLD	30 GOLD	50 GOLD	A	B	C	D
F	4	8		71973-9704	71973-9804	71973-9904	.300 (7.62)	.395 (10.03)	.200 (5.08)	.658 (16.71)	34	68			71973-9734	71973-9834	71973-9934	3.300 (83.82)	3.395 (86.23)	3.200 (81.28)	3.658 (92.91)
	5	10		71973-9705	71973-9805	71973-9905	.400 (10.16)	.495 (12.57)	.300 (7.62)	.758 (19.25)	35	70			71973-9735	71973-9835	71973-9935	3.400 (86.36)	3.495 (88.77)	3.300 (83.82)	3.758 (95.45)
	6	12		71973-9706	71973-9806	71973-9906	.500 (12.70)	.595 (15.11)	.400 (10.16)	.858 (21.79)	36	72			71973-9736	71973-9836	71973-9936	3.500 (88.90)	3.595 (91.31)	3.400 (86.36)	3.858 (97.99)
	7	14		71973-9707	71973-9807	71973-9907	.600 (15.24)	.695 (17.65)	.500 (12.70)	.958 (24.33)											
	8	16		71973-9708	71973-9808	71973-9908	.700 (17.78)	.795 (20.19)	.600 (15.24)	1.058 (26.87)											
	9	18		71973-9709	71973-9809	71973-9909	.800 (20.32)	.895 (22.73)	.700 (17.78)	1.158 (29.41)											
E	10	20		71973-9710	71973-9810	71973-9910	.900 (22.86)	.995 (25.27)	.800 (20.32)	1.258 (31.95)											
	11	22		71973-9711	71973-9811	71973-9911	1.000 (25.40)	1.095 (27.81)	.900 (22.86)	1.358 (34.49)											
	12	24		71973-9712	71973-9812	71973-9912	1.100 (27.94)	1.195 (30.35)	1.000 (25.40)	1.458 (37.03)											
	13	26		71973-9713	71973-9813	71973-9913	1.200 (30.48)	1.295 (32.89)	1.100 (27.94)	1.558 (39.57)											
	14	28		71973-9714	71973-9814	71973-9914	1.300 (33.02)	1.395 (35.43)	1.200 (30.48)	1.658 (42.11)											
	15	30		71973-9715	71973-9815	71973-9915	1.400 (35.56)	1.495 (37.97)	1.300 (33.02)	1.758 (44.65)											
	16	32		71973-9716	71973-9816	71973-9916	1.500 (38.10)	1.595 (40.51)	1.400 (35.56)	1.858 (47.19)											
D	17	34		71973-9717	71973-9817	71973-9917	1.600 (40.64)	1.695 (43.05)	1.500 (38.10)	1.958 (49.73)											
	18	36		71973-9718	71973-9818	71973-9918	1.700 (43.18)	1.795 (45.59)	1.600 (40.64)	2.058 (52.27)											
	19	38		71973-9719	71973-9819	71973-9919	1.800 (45.72)	1.895 (48.13)	1.700 (43.18)	2.158 (54.81)											
	20	40		71973-9720	71973-9820	71973-9920	1.900 (48.26)	1.995 (50.67)	1.800 (45.72)	2.258 (57.35)											
	21	42		71973-9721	71973-9821	71973-9921	2.000 (50.80)	2.095 (53.21)	1.900 (48.26)	2.358 (59.89)											
	22	44		71973-9722	71973-9822	71973-9922	2.100 (53.34)	2.195 (55.75)	2.000 (50.80)	2.458 (62.43)											
	23	46		71973-9723	71973-9823	71973-9923	2.200 (55.88)	2.295 (58.29)	2.100 (53.34)	2.558 (64.97)											
C	24	48		71973-9724	71973-9824	71973-9924	2.300 (58.42)	2.395 (60.83)	2.200 (55.88)	2.658 (67.51)											
	25	50		71973-9725	71973-9825	71973-9925	2.400 (60.96)	2.495 (63.37)	2.300 (58.42)	2.758 (70.05)											
	26	52		71973-9726	71973-9826	71973-9926	2.500 (63.50)	2.595 (65.91)	2.400 (60.96)	2.858 (72.59)											
	27	54		71973-9727	71973-9827	71973-9927	2.600 (66.04)	2.695 (68.45)	2.500 (63.50)	2.958 (75.13)											
	28	56		71973-9728	71973-9828	71973-9928	2.700 (68.58)	2.795 (70.99)	2.600 (66.04)	3.058 (77.67)											
	29	58		71973-9729	71973-9829	71973-9929	2.800 (71.12)	2.895 (73.53)	2.700 (68.58)	3.158 (80.21)											
	30	60		71973-9730	71973-9830	71973-9930	2.900 (73.66)	2.995 (76.07)	2.800 (71.12)	3.258 (82.75)											
B	31	62		71973-9731	71973-9831	71973-9931	3.000 (76.20)	3.095 (78.61)	2.900 (73.66)	3.358 (85.29)											
	32	64		71973-9732	71973-9832	71973-9932	3.100 (78.74)	3.195 (81.15)	3.000 (76.20)	3.458 (87.83)											
	33	66		71973-9733	71973-9833	71973-9933	3.200 (81.28)	3.295 (83.69)	3.100 (78.74)	3.558 (90.37)											
A		*X INDICATES TOOLING IS NOT AVAILABLE					ADD OPTION K & L EC NO: S2010-0534 DRWN:SKANG 2009/12/30 CHYD:ATSEE 2010/01/08 APPR:MLONG 2010/01/14 DESCRIPTION REV				QUALITY SYMBOLS $F_A=0$ $F_B=0$ $F_P=0$		GENERAL TOLERANCES (UNLESS SPECIFIED) 4 PLACES $\pm$ --- $\pm$ --- 3 PLACES $\pm$ --- $\pm$.010 2 PLACES $\pm$ 0.25 $\pm$ --- 1 PLACE $\pm$ --- $\pm$ --- ANGULAR $\pm$ 1/2° DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		DIMENSION STYLE IN/MM DRAWN BY DATE DJB 1991/10/21 CHECKED BY DATE DJB 1991/10/21 APPROVED BY DATE MLONG 2010/01/14 MATERIAL NO. SEE TABLE		SCALE NTS DESIGN UNITS INCH THIRD ANGLE PROJECTION TITLE EARLY ENTRY R/A RECPT .120"PC TAIL W/O LOWER ROW PINSTOP-.100" GRID MOLEX INCORPORATED SDA-71973-**** THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION		SHEET NO. 24 OF 26		
fb_frame_A3_P_AM_T Rev. F 2009/06/18		9		8		7		6		5		4		3		2		1			

10		9		8		7		6		5		4		3		2		1									
NO. OF CKTS		OPTION K ASSEMBLY PACKAGED IN TUBES PER PK-70873-0138 (SEE SHEET I FOR FINISH SPECIFICATIONS)						DIMENSION				NO. OF CKTS		OPTION K ASSEMBLY PACKAGED IN TUBES PER PK-70873-0138 (SEE SHEET I FOR FINISH SPECIFICATIONS)						DIMENSION							
PER ROW	TOTAL			15 GOLD		30 GOLD		50 GOLD		A	B			PER ROW	TOTAL			15 GOLD		30 GOLD		50 GOLD		A	B		
4	8				71973-6204		71973-6304		71973-6404	.300 (7.62)	.395 (10.03)			32	64				71973-6232		71973-6332		71973-6432	3.100 (78.74)	3.195 (81.15)		
5	10				71973-6205		71973-6305		71973-6405	.400 (10.16)	.495 (12.57)			33	66				71973-6233		71973-6333		71973-6433	3.200 (81.28)	3.295 (83.69)		
6	12				71973-6206		71973-6306		71973-6406	.500 (12.70)	.595 (15.11)			34	68				71973-6234		71973-6334		71973-6434	3.300 (83.82)	3.395 (86.23)		
7	14				71973-6207		71973-6307		71973-6407	.600 (15.24)	.695 (17.65)			35	70				71973-6235		71973-6335		71973-6435	3.400 (86.36)	3.495 (88.77)		
8	16				71973-6208		71973-6308		71973-6408	.700 (17.78)	.795 (20.19)			36	72				71973-6236		71973-6336		71973-6436	3.500 (88.90)	3.595 (91.31)		
9	18				71973-6209		71973-6309		71973-6409	.800 (20.32)	.895 (22.73)																
10	20				71973-6210		71973-6310		71973-6410	.900 (22.86)	.995 (25.27)																
11	22				71973-6211		71973-6311		71973-6411	1.000 (25.40)	1.095 (27.81)																
12	24				71973-6212		71973-6312		71973-6412	1.100 (27.94)	1.195 (30.35)																
13	26				71973-6213		71973-6313		71973-6413	1.200 (30.48)	1.295 (32.89)																
14	28				71973-6214		71973-6314		71973-6414	1.300 (33.02)	1.395 (35.43)																
15	30				71973-6215		71973-6315		71973-6415	1.400 (35.56)	1.495 (37.97)																
16	32				71973-6216		71973-6316		71973-6416	1.500 (38.10)	1.595 (40.51)																
17	34				71973-6217		71973-6317		71973-6417	1.600 (40.64)	1.695 (43.05)																
18	36				71973-6218		71973-6318		71973-6418	1.700 (43.18)	1.795 (45.59)																
19	38				71973-6219		71973-6319		71973-6419	1.800 (45.72)	1.895 (48.13)																
20	40				71973-6220		71973-6320		71973-6420	1.900 (48.26)	1.995 (50.67)																
21	42				71973-6221		71973-6321		71973-6421	2.000 (50.80)	2.095 (53.21)																
22	44				71973-6222		71973-6322		71973-6422	2.100 (53.34)	2.195 (55.75)																
23	46				71973-6223		71973-6323		71973-6423	2.200 (55.88)	2.295 (58.29)																
24	48				71973-6224		71973-6324		71973-6424	2.300 (58.42)	2.395 (60.83)																
25	50				71973-6225		71973-6325		71973-6425	2.400 (60.96)	2.495 (63.37)																
26	52				71973-6226		71973-6326		71973-6426	2.500 (63.50)	2.595 (65.91)																
27	54				71973-6227		71973-6327		71973-6427	2.600 (66.04)	2.695 (68.45)																
28	56				71973-6228		71973-6328		71973-6428	2.700 (68.58)	2.795 (70.99)																
29	58				71973-6229		71973-6329		71973-6429	2.800 (71.12)	2.895 (73.53)																
30	60				71973-6230		71973-6330		71973-6430	2.900 (73.66)	2.995 (76.07)																
31	62				71973-6231		71973-6331		71973-6431	3.000 (76.20)	3.095 (78.61)																
X INDICATES TOOLING IS NOT AVAILABLE										ADD OPTION K & L EC NO: S2010-0534 DRWN:SKANG CHKD:ATSEE APPR:MLONG 2009/12/30 2010/01/08 2010/01/14		QUALITY SYMBOLS FA=0 FC=0 FP=0		GENERAL TOLERANCES (UNLESS SPECIFIED) mm INCH 4 PLACES ± --- ± --- 3 PLACES ± --- ± .010 2 PLACES ± 0.25 ± --- 1 PLACE ± --- ± --- ANGULAR ± 1/2°		DIMENSION STYLE IN/MM DRAWN BY DATE DJB 1991/10/21 CHECKED BY DATE DJB 1991/10/21 APPROVED BY DATE MLONG 2010/01/14 MATERIAL NO.		SCALE NTS		DESIGN UNITS INCH		THIRD ANGLE PROJECTION		TITLE EARLY ENTRY R/A RECPT .120"PC TAIL W/O LOWER ROW PINSTOP-.100" GRID MOLEX INCORPORATED SDA-71973-****		SHEET NO. 25 OF 26	
tb_frame_A3_P_AM_T Rev. F 2009/06/18										9		8		7		6		5		4		3		2		1	

10		9		8		7		6		5		4		3		2		1									
NO. OF CKTS		OPTION L ASSEMBLY PACKAGED IN TUBES PER PK-70873-0138 (SEE SHEET I FOR FINISH SPECIFICATIONS)						DIMENSION				NO. OF CKTS		OPTION L ASSEMBLY PACKAGED IN TUBES PER PK-70873-0138 (SEE SHEET I FOR FINISH SPECIFICATIONS)						DIMENSION							
PER ROW	TOTAL			15 GOLD		30 GOLD		50 GOLD		A	B					15 GOLD		30 GOLD		50 GOLD		A	B				
4	8				71973-5404		71973-5504		71973-5604	.300 (7.62)	.395 (10.03)						71973-5431		71973-5531		71973-5631	3.000 (76.20)	3.095 (78.61)				
5	10				71973-5405		71973-5505		71973-5605	.400 (10.16)	.495 (12.57)						71973-5432		71973-5532		71973-5632	3.100 (78.74)	3.195 (81.15)				
6	12				71973-5406		71973-5506		71973-5606	.500 (12.70)	.595 (15.11)						71973-5433		71973-5533		71973-5633	3.200 (81.28)	3.295 (83.69)				
7	14				71973-5407		71973-5507		71973-5607	.600 (15.24)	.695 (17.65)						71973-5434		71973-5534		71973-5634	3.300 (83.82)	3.395 (86.23)				
8	16				71973-5408		71973-5508		71973-5608	.700 (17.78)	.795 (20.19)						71973-5435		71973-5535		71973-5635	3.400 (86.36)	3.495 (88.77)				
9	18				71973-5409		71973-5509		71973-5609	.800 (20.32)	.895 (22.73)						71973-5436		71973-5536		71973-5636	3.500 (88.90)	3.595 (91.31)				
10	20				71973-5410		71973-5510		71973-5610	.900 (22.86)	.995 (25.27)																
11	22				71973-5411		71973-5511		71973-5611	1.000 (25.40)	1.095 (27.81)																
12	24				71973-5412		71973-5512		71973-5612	1.100 (27.94)	1.195 (30.35)																
13	26				71973-5413		71973-5513		71973-5613	1.200 (30.48)	1.295 (32.89)																
14	28				71973-5414		71973-5514		71973-5614	1.300 (33.02)	1.395 (35.43)																
15	30				71973-5415		71973-5515		71973-5615	1.400 (35.56)	1.495 (37.97)																
16	32				71973-5416		71973-5516		71973-5616	1.500 (38.10)	1.595 (40.51)																
17	34				71973-5417		71973-5517		71973-5617	1.600 (40.64)	1.695 (43.05)																
18	36				71973-5418		71973-5518		71973-5618	1.700 (43.18)	1.795 (45.59)																
19	38				71973-5419		71973-5519		71973-5619	1.800 (45.72)	1.895 (48.13)																
20	40				71973-5420		71973-5520		71973-5620	1.900 (48.26)	1.995 (50.67)																
21	42				71973-5421		71973-5521		71973-5621	2.000 (50.80)	2.095 (53.21)																
22	44				71973-5422		71973-5522		71973-5622	2.100 (53.34)	2.195 (55.75)																
23	46				71973-5423		71973-5523		71973-5623	2.200 (55.88)	2.295 (58.29)																
24	48				71973-5424		71973-5524		71973-5624	2.300 (58.42)	2.395 (60.83)																
25	50				71973-5425		71973-5525		71973-5625	2.400 (60.96)	2.495 (63.37)																
26	52				71973-5426		71973-5526		71973-5626	2.500 (63.50)	2.595 (65.91)																
27	54				71973-5427		71973-5527		71973-5627	2.600 (66.04)	2.695 (68.45)																
28	56				71973-5428		71973-5528		71973-5628	2.700 (68.58)	2.795 (70.99)																
29	58				71973-5429		71973-5529		71973-5629	2.800 (71.12)	2.895 (73.53)																
30	60				71973-5430		71973-5530		71973-5630	2.900 (73.66)	2.995 (76.07)																
"X" INDICATES TOOLING IS NOT AVAILABLE										ADD OPTION K & L EC NO: S2010-0534 2009/12/30 DRWN:SKANG CHKD:ATSEE 2010/01/08 APPR:MLONG 2010/01/14		QUALITY SYMBOLS F _A =0 F _B =0 F _P =0		GENERAL TOLERANCES (UNLESS SPECIFIED) mm INCH 4 PLACES ± --- ± --- 3 PLACES ± --- ± .010 2 PLACES ± 0.25 ± --- 1 PLACE ± --- ± --- ANGULAR ± 1/2°		DIMENSION STYLE IN/MM DRAWN BY DATE DJB 1991/10/21 CHECKED BY DATE DJB 1991/10/21 APPROVED BY DATE MLONG 2010/01/14		SCALE NTS		DESIGN UNITS INCH		THIRD ANGLE PROJECTION		EARLY ENTRY R/A RECPT .120"PC TAIL W/O LOWER ROW PINSTOP-.100" GRID MOLEX INCORPORATED		SHEET NO. 26 OF 26	
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS										K		REV		SEE TABLE		MATERIAL NO.		DOCUMENT NO.		SDA-71973-****		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION					
tb_frame_A3_P_AM_T Rev. F 2009/06/18		9		8		7		6		5		4		3		2		1									

