

249 - Standard drift punches | 249.2



Standards

NF E 71-211, DIN 6450, ASME B107.410

Description

- Hexagonal shank, high-strength steel tip, hardened to 53-58 HRc.
- Zinc-plated finish.

Specifications

Reference	249.2
[g]	30
L [mm]	115
L1 [mm]	30
d [mm]	8
A [mm]	1,9
[kg]	0,030
Quantity	1

