

NOTES:

1. MATERIALS AND FINISHES:

TNC BULKHEAD JACK, IP 67 COMPLIANT - P/N: 122529-10
MICRO COAX PLUG TERMINATED USING 1.32 MM CABLE - P/N: 100910-01

2. ELECTRICAL:

A. IMPEDANCE: 50 OHM, NOMINAL



3. PACKAGING:

A. QUANTITY: SINGLE PACK
B. BAG TO BE MARKED: AMPHENOL RF, 336209-13-XXXX, AND DATE CODE

336209-13-XXXX

REVISIONS

DRAWING NO.	REV	DESCRIPTION	DATE	ECO	APPR
THIRD ANGLE PROJ.	A	RELEASE TO MFG.	23-Sep-10	--	KR
	B	SEE SHEET 1	25-Oct-10	2113	KR
	C	SEE SHEET 1	05-Jul-11	2193	HR
	D	SEE SHEET 1	17-Jan-12	2270	CL
	F	SEE SHEET 1	27-Mar-14	2716	MB/BCG



ORDERING INFORMATION

PART NUMBER (METRIC)	LENGTH IN INCHES * [METERS]
336209-13-0050	1.97 [0.050]
336209-13-0075	2.95 [0.075]
336209-13-0100	3.94 [0.100]
336209-13-0150	5.91 [0.150]
336209-13-0200	7.87 [0.200]
336209-13-0250	9.84 [0.250]
336209-13-0300	11.81 [0.300]

* ADDITIONAL LENGTHS CAN BE PROVIDED.
CONTACT AMPHENOL RF MARKETING FOR QUOTE

TOLERANCE TABLE

LENGTH IN INCHES/FT [METERS]	TOLERANCE
0" - 23.90" [0 - 0.607]	±0.25" [0.006]
24.00" - 59.00" [0.610 - 1.499]	±0.50" [0.013]
5.0' - 24.9' [1.524 - 7.617]	±2.5%
25.0' & UP [7.620 & UP]	±5.0%

DESIGN REQUIREMENTS:

☒ FREQUENCY: DC TO 6.0 GHz

☒ CONTINUITY

☐ VSWR _____ : 1 MAX

☒ HI-POT :200 VRMS

☐ INS. LOSS _____ dB MAX

☐ OTHER

CUSTOMER OUTLINE DRAWING

ALL OTHER SHEETS ARE FOR INTERNAL USE ONLY

UNLESS OTHERWISE SPECIFIED, TOLERANCES ARE AS FOLLOWS:
2 PLACE DECIMAL 3 PLACE DECIMAL ANGLES
±.015 (0,381 mm) ±.005 (0,127 mm) ± 1°

NOTICE - These drawings, specifications, or other data (1) are, and remain the property of Amphenol Corp. (2) must be returned upon request; and (3) are confidential and not to be disclosed to any person other than those to whom they are given by Amphenol Corp. The furnishing of these drawings, specifications, or other data by Amphenol Corp., or to any other person to anyone for any purpose is not to be regarded by implication or otherwise in any manner licensing, granting rights or permitting such holder or any other person to manufacture, use or sell any product, process or design, patented or otherwise, that may in any way be related to or disclosed by said drawings, specifications, or other data.

MATERIAL

SEE NOTES

REFERENCE

DRAWN

MOHAN

DATE

18-Mar-14

ENGINEER

MOHAN

DATE

18-Mar-14

APPROVED

B.C. GLEISSNER

DATE

27-Mar-14

CAD FILE

TITLE

TNC BULKHEAD JACK, IP 67 COMPLIANT
TO MICRO COAX PLUG TERMINATED,
USING 1.32 MM CABLE,
VARIOUS LENGTHS

SCALE: 4.0:1

SHEET 2 OF 2

DWG SIZE

B

DRAWING NO.

336209-13-XXXX

REV

E