

Type: CDRR127

UNDER DEVELOPMENT

Product Description




- 12.5×12.5mm Max. (LxW), 8.5 mm Max. Height.
- Inductance range: 22 μ H.
- Rated current range: 4.45A.
- Custom design is available.




Feature

- Magnetically shielded construction.
- Ideally used in engine control module.
- RoHS Compliance.

Dimensions (mm)



Land Pattern (mm)



Specification

Part Name	Stamp	Inductance [Within] 100kHz/1V	D.C.R. (m) Max. (at 20)	Saturation current Max.(Typ.) (A) 1	Temperature rise current Max.(Typ.) (A) 2
CDRR127NP-220MC	220	22 μ H \pm 20%	37(29)	4.88(6.10)	4.45(5.02)

1. Saturation Current: The DC current at which the inductance decreases to 75% of its initial value .
(Ta = 20)

2 Temperature rise current: The DC current at which the temperature rise is t = 40 .(Ta = 20)

NOTE: THIS SPEC IS NOT THE FINAL ISSUE. AND MAYBE SOME PARTS WILL BE CHANGED BEFORE PRODUCTION.