

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT 20

BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

P

LTR

DESCRIPTION

DATE

DWN

APVD

GP

00



A

RELEASED

11JAN2007

RG

DO



SECTION Z-Z

- PART NUMBER CHANGES AND/OR DESIGN CHANGES AFFECTING ITEM INTERCHANGEABILITY REQUIRES PRIOR TYCO APPROVAL AND AUTHORIZATION BY REVISION TO THIS DRAWING.
- ITEMS PROVIDED TO THIS SPECIFICATION SHALL BE IDENTIFIED ON THE PACKAGE AS FOLLOWS: MFG IDENTIFICATION AND PART NUMBER.

3 MATERIAL:
SOCKET BODY AND HOOD: COPPER ALLOY
CROWN: COPPER ALLOY
PROBE PROOF CAP: THERMOPLASTIC, UL 94V-0 RECOGNIZED.


4 FINISH:
SOCKET BODY AND HOOD: SILVER PLATE .000200 MIN THK. OVER
NICKEL PLATE .000040 MIN THK.
CROWN BANDS: GOLD PLATE .000030 MIN THK. OVER
NICKEL .000040 MIN THK.

AS SHOWN

1926301-1

DESCRIPTION

PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION
IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION
SHOULD BE CONTACTED FOR THE LATEST REVISION.DIMENSIONS:
INCHESTOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC	±-
1 PLC	±-
2 PLC	±.02
3 PLC	±.010
4 PLC	±-
ANGLES	±.5

MATERIAL

3

FINISH

4

DWN 20NOV2006

R.GRZYBOWSKI

CHK 20NOV2006

D.ORRIS

APVD 20NOV2006

S.FLICKINGER

PRODUCT SPEC

-

APPLICATION SPEC

-

WEIGHT

-

CUSTOMER DRAWING

tyco
ElectronicsTyco Electronics
Harrisburg, PA 17105-3608

NAME

CONTACT, SOCKET, SIZE #0
DOUBLE CROWN, CRIMP #2

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A300779C-1926301

SCALE 3:1

SHEET 1 OF 1

REV A