




GUARDIAN
Electric Manufacturing

ISO 9001 / AS9100 Certified Company

Woodstock, IL 60098 Ph. (815)334-3600 Fax (815)337-0377

Or visit us at our website www.guardian-electric.com

Model 22 DC Frame Solenoid



Solenoid shown energized and fully seated.

Spring kits are available (consult factory).

Total Weight: 1.6 oz.

Plunger Weight: .2 oz.

Model No.	Part No.	Duty Cycle	Voltage	Resistance (Ω)	Power (W)	Current (mA)
22-I-12D	A420-065803-00	Intermittent	12VDC	22.6	6.7	531
22-C-12D	A420-065802-00	Continuous	12VDC	45.7	3.3	263
22-I-24D	A420-065805-00	Intermittent	24VDC	93.2	6.5	258
22-C-24D	A420-065804-00	Continuous	24VDC	182	3.3	132

When ordering, please refer to Part No., as listed above.

Consult factory for custom configurations.

Pull Force (oz.)									Holding Force (oz.)
Stroke (in.)	0.050	0.125	0.250	0.375	0.500	0.625	0.750	1.000	-
Continuous Duty	13	7	2	1	n/a	n/a	n/a	n/a	39
Intermittent Duty	20	8	3	2	1	n/a	n/a	n/a	45

UL Recognition

Recognized under the 
Component Recognition Program of
Underwriters Laboratories, Inc.

Continuous Duty

100% 'On' Time

Intermittent Duty

25% 'On' Time, (100 Seconds 'On' Max.
Followed By 300 Seconds 'Off' Min.)

RoHS

These parts comply with **RoHS** Directive 2002/95/EC