









ISOMETERIC



NOTE:

1. ALL DIMENSIONS IN MM[INCH].
2. GENERAL TOLERANCE: X.X=± 0.4
X.XX=± 0.25
3. TERM. NOS. FOR REFERENCE ONLY.
4. CONTACT MATERIAL: SILVER
5. CONTACT RATING: 150MILLIAMP, 250VAC/DC
350MILLIAMP, 110VAC/DC
6. CONTACT RATING (NON-SWITCHING) 5A
7. OPERATING FORCE: 425± 100CM/STANDARD
- ▲8. OPERATING TEMP: -30°C TO 85°C
9. CIRCUIT SP: 12 POSITION 30° INDEX.
- ▲10. DIELECTRIC STRENGTH: 500VAC FOR 1 MIN.
11. HARDWARE SUPPLIED ON SWITCH:
LOCKWASHER, HEXNUT
12. ▲ DENOTES CRITICAL PARAMETER.
13. 2002/95/EC (ROHS) COMPLIANT



P.C.B MOUNTING LAYOUT



TITLE KC52A9.501NPS

D	17410	REVISED AND REDRAWN	6/26/07	TN
REV	PCR NO	DESCRIPTION	DATE	BY

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

SCALE 1.5:1

DATE 6/26/2007

DR TN

DWG G529690

REV D