


TwinMark
HSS 1/8 1.2-2.8/25W

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
www.weidmueller.com



Similar to illustration



The heat-shrinkable TwinMark sleeve is printable on 2 sides and can be used for marking and insulating conductors and cables between 1.2 and 24 mm in diameter. The flexible, heat-shrink material enables a firm, perfect fit around the conductor and therefore saves space.

Advantages:

- Application in extremely confined spaces
- Printing on 2 sides for better legibility
- Printed sleeves on a continuous backing
- Can be shrunk with conventional hot-air guns

TwinMark HSS standard version
 Delivered form: Leporello folding

General ordering data

Delivery status	This article will no longer be available in the future.
Available until	2016-12-01
Type	HSS 1/8 1.2-2.8/25W
Order No.	1962140000
Version	TwinMark, Conductor and cable markers, 1.2 - 2.8 mm, 25.4 x 6 mm, White
GTIN (EAN)	4032248642830
Qty.	1,000 pc(s).
Alternative product	2437510000
compatible printer	2430920000 2448870000 1140490000

TwinMark
HSS 1/8 1.2-2.8/25W

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data
Dimensions and weights

Width	6 mm	Width (inches)	0.236 inch
Height	25.4 mm	Height (inches)	1 inch
Depth	1 mm	Depth (inches)	0.039 inch
Net weight	0.257 g		

General data

Colour	White	Material	Polyolefine
Material colour according to resistance code	9	Recommended industries	Plant manufacture, Energy, Device manufacturer, Machinery, Process
Type of printing	blank	Width	6 mm

Conductor and cable markers

Conductor O.D.	1.2 - 2.8 mm	Conductor O.D., max.	2.8 mm
Conductor O.D., min.	1.2 mm	Conductor cross-section, max.	1.5 mm ²
Conductor cross-section, min.	0.5 mm ²	Halogen	Yes
Rate of shrinkage	3:1		

Classifications

ETIM 3.0	EC001530	ETIM 4.0	EC001288
ETIM 5.0	EC001530	ETIM 6.0	EC001530
UNSPSC	30-21-18-01	eClass 5.1	27-14-91-29
eClass 6.2	27-14-91-29	eClass 7.1	27-14-91-29
eClass 8.1	27-14-91-03	eClass 9.0	27-14-07-08
eClass 9.1	27-40-04-01		

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	EPLAN, WSCAD, Zuken E3.S
Engineering Data	STEP
Software	M-Print PRO configuration file

TwinMark HSS 1/8 1.2-2.8/25W

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings

