




		3.600	3.500	35	72	3 102393-4	
SUPERSEDED		3.500	3.400	34	70	3-	-3
		3.400	3.300	33	68	3-	-2
		3.300	3.200	32	66	3-	-1
		3.200	3.100	31	64	3-	1 -0
SUPERSEDED		3.100	3.000	30	62	2-	1 -9
		3.000	2.900	29	60	2-	1 -8
SUPERSEDED		2.900	2.800	28	58	2-	-7
SUPERSEDED		2.800	2.700	27	56	2-	-6
9 OBSOLETE		2.700	2.600	26	54	2-	1 -5
SUPERSEDED		2.600	2.500	25	52	2-	-4
		2.500	2.400	24	50	2-	1 -3
SUPERSEDED		2.400	2.300	23	48	2-	-2
		2.300	2.200	22	46	2-	-1
		2.200	2.100	21	44	2-	-0
		2.100	2.000	20	42	1-	-9
		2.000	1.900	19	40	1-	1 -8
SUPERSEDED		1.900	1.800	18	38	1-	-7
SUPERSEDED		1.800	1.700	17	36	1-	-6
		1.700	1.600	16	34	1-	1 1 -5
9 OBSOLETE		1.600	1.500	15	32	1-	1 1 -4
		1.500	1.400	14	30	1-	1 1 -3
9 OBSOLETE		1.400	1.300	13	28	1-	1 1 -2
		1.300	1.200	12	26	1-	1 1 -1
9 SUPERSEDED		1.200	1.100	11	24	1-	1 1 -0
9 OBSOLETE		1.100	1.000	10	22		1 1 -9
		1.000	.900	9	20		1 1 -8
		.900	.800	8	18		1 1 -7
		.800	.700	7	16		1 1 -6
		.700	.600	6	14		1 1 -5
		.600	.500	5	12		1 1 -4
		.500	.400	4	10		1 1 -3
9 SUPERSEDED		.400	.300	3	8		1 1 -2
		.300	.200	2	6	1 102393-1	
		C	B	A	NO OF POSN	ASSEMBLY PART NUMBER	

- | | | | | | | | |
|---|--|--|--|---|--|-------------------|--|
| THIS DRAWING IS A CONTROLLED DOCUMENT. | | DWN
L.D.RINGLEY
7-1-85 | |  TE Connectivity | | | |
| | | CHK
P.C.deJONG
7-1-85 | | | | | |
| DIMENSIONS:
INCHES | | TOLERANCES UNLESS OTHERWISE SPECIFIED: | | APVD
P.C.deJONG
7-1-85 | | NAME | |
|  | | 0 PLC ± - | | ASSEMBLY, MASS TERMINATION, AMPMODU,
DOUBLE ROW, .100 X .100 CL,
#26-#30 AWG WIRE SIZE | | | |
| | | 1 PLC ± - | | | | | |
| | | 2 PLC ± - | | | | | |
| | | 3 PLC ± .005 | | SIZE | | CAGE CODE | |
| | | 4 PLC ± - | | DRAWING NO | | RESTRICTED TO | |
| MATERIAL | | FINISH | | WEIGHT | | A2 00779 C-102393 | |
| HOUSING: FLAME RETARDANT THERMOPLASTIC, COLOR-BLACK CONTACTS: PHOS BRONZE | | CONTACTS: SEE TABLE | | — | | — | |
| CUSTOMER DRAWING | | | | SCALE 4:1 | | SHEET 1 of 1 | |
| | | | | | | REV S2 | |