






PLATING CONTACT AREA:	
DASH NR:	PERFORMANCE LEVEL
-1YY/1YYLF	TELCORDIA CO
-2YY/2YYLF	CUSTOMER SPECIAL
-3YY/3YYLF	CUSTOMER SPECIAL


PC BOARD VERSIONS		
PRODUCT NR:	PCB THICKNESS	DIM "A"
89013-X02/X02LF	1.6	2.90
89013-X12/X12LF	2.4	3.53



- NOTES:
- BODY MAT'L: LIQUID CRYSTAL POLYMER 30% GLASS
FLAME RETARDANT ACC. UL 94-V0
 - TERMINAL MATERIAL: PHOSPHOR BRONZE.
 - INDICATED HOLES ARE UNPLATED.
 - PLATING OF SOLDER TAILS 2-8 um SnPb 90-97 OR 2-8 um PURE Sn FOR LEAD FREE.
 - PRODUCT MARKING: PART NUMBER & BATCH ID.
 - SET BACK FOR TAIL BLOCK
 - TOP SURFACE OF PRESS BLOCK MAY EXTEND UP TO 0.4MM HIGHER THAN HOUSING. THIS MAY AFFECT THE TAIL LENGTH BEFORE APPLICATION TO A BOARD.
 - THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.
 - THE HOUSING WILL WITHSTAND EXPOSURE TO 260DEGREE PEAK TEMPERATURE FOR 10 SECONDS IN A WAVE SOLDER APPLICATION.



RECOMMENDED HOLE PATTERN,
COMPONENT SIDE.



mat'l. code				tolerances unless otherwise specified		CUSTOMER COPY		FCE ELECTRONICS	
ltr	ecn no	dr	date	linear		projection		title	www.falconconnect.com
A	H40101	VWO	940209					5 ROW R.A. S.T.B. SIGNAL	
B	V00578	LLA	000316					RECEPT. 12 mm MODULE	
C	V00850	GNV	000512	angles				product family	METRAL (tm)
D	p004-0104	CLU	041223	dr	H v Woensel	940126		size	dwg no
E	D007-0170	Cent	05/22/07	engr	H v Woensel	940126		scale	213
F	D009-0088	Cent	06/06/08	chr	E Feijen	940126		1 of 1	sheet
				app	H v Woensel	940126			
sheet	revision	F							
index	sheet	1							

PDM: Rev:F

STATUS: Released

Printed: May 19, 2011