


NOTES:

1. ALL DIMENSIONS IN MM
2. GENERAL TOLERANCE: $X.X = \pm 0.4$
 $X.XX = \pm 0.25$
3. TERM. NOS. FOR REF. ONLY
4. RATING: 50mA, @12V DC
5. TRAVEL: 0.25 ± 0.1 mm
6. OPERATING FORCE: 250 ± 50 gf
7. CONTACT RESISTANCE: 100 milliohms Max.
8. ELECTRICAL LIFE: 100,000 CYCLES MIN.
9. ▲ DESIGNATE MAJOR FEATURE
10. ▲ ACTUATOR COLOR: RED
11. ▲ HOUSING COLOR: BLACK



THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED						SCALE 4:1		DATE --		DR --		DWG P020226		REV B	
B	18128	ONE TOLERANCE WAS +/- 0.1	6/9/08	BLR	TITLE TL 1105 M F250 Q										
A	12370	RELEASED	8/14/02	CJB											
REV.	ECN No.	DESCRIPTION	DATE	CHKD											