

THIS DRAWING AND THE DESIGN IT DISCLOSES ARE THE PROPERTY OF KILDVAC CORP. AND IT IS ISSUED IN CONFIDENCE FOR ENGINEERING INFORMATION ONLY. THE DRAWING AND/OR DESIGN MAY NOT BE REPRODUCED, DISCLOSED TO OUTSIDERS OR USED FOR ANY OTHER PURPOSE WITHOUT THE PRIOR EXPRESS CONSENT OF KILDVAC. THE DRAWING IS LOANED FOR MUTUAL ASSISTANCE AND IS SUBJECT TO RECALL AT ANY TIME.

WC3-26DC-5SX-



SPECIFICATIONS

- LINE CURRENT:
OVER CURRENT ALLOWANCE:
OVER CURRENT ADJUST RANGE:
TIME DELAY:
HYSTERESIS:
CONTROL VOLTAGE:
TEMPERATURE DRIFT:
BURDEN:
OPERATING TEMPERATURE RANGE:
STORAGE TEMPERATURE:
OUTPUT CONTACTS:
CONTACT RATING:
- THREE PHASE, 50-400Hz., DIRECT OR FROM CT
500% FOR 0.25 SECONDS.
1 - 5A
APPROXIMATE .20 SECONDS.
.1A TYPICAL.
26VDC ± 10%
±0.05%/°C
CURRENT INPUT: 1.2VA MAX.
CONTROL VOLTAGE: 3.0VA MAX.
-40°C TO +70°C
-55°C TO +85°C
1 N.O AND 1 N.C (QUALIFIED TO M5757/23)
10A RESISTIVE AT 28VDC
5A RESISTIVE AT 115V 400HZ.
3A RESISTIVE AT 115V 60HZ.
2.5 LBS. MAX.

WEIGHT:

SOLID STATE SENSOR WITH ELECTROMECHANICAL OUTPUT RELAY, ENCLOSED IN A SEALED STEEL CAN,

RAYTHEON P/N	KILDVAC P/N	TYCO P/N	ENCLOSURE PLATING	CONFORMAL COATED PCB
H294518-1	WC3-26DC-5SX	3-1618103-5	PURE TIN	NO
H294518-2	WC3-26DC-5SX/01	7-1618395-9	90/10 TIN/LEAD	NO
H294518-3	WC3-26DC-5SX/02	7-1618403-2	90/10 TIN/LEAD	YES



REV	DCD/EC HISTORY
	DCD/EC

Form 13/08 rev. 1049

4

3

2

THIRD ANGLE PROJECTION				DESIGNATOR				
ALL DIMENSIONS ARE IN INCHES UNLESS OTHERWISE SPECIFIED. Block Tolerances are not applied if values are set to zero. FRACTIONS DECIMALS ANGLES XX/YY .XX = .01 ± 1 ° ±1/64 .XXX = ±.005				ITEM		DWG. NO.	QTY.	NOMENCLATURE OR DESCRIPTION
 TE connectivity Kilovac				KILDVAC BILL OF MATERIALS				
				550 Linden Ave. Carpentaria, CA US 93013 Internet: www.te.com				
TITLE RELAY, OVERCURRENT SERIES				ECD NO.		REV. TYCO ELECTRONICS NO.		
±1.		 .005  .005		DEV		3		KILDVAC. NO.
CAGE CODE	EDITED BY	EFTV DATE	APPROVED BY	APRY DATE	SCALE	1:1	SCALE	DRAWING
18741	RM	08-12-11	TN	08-12-11	WC3-26DC-5SX-		DO NOT	SHEET 1 of 1
					SIZE		B	

SIZE
B