# 7000 Series
# Miniature Toggle Switches

## *Features/Benefits*

- ***Multi-pole and multi-position***
- ***Wide variety of actuator and termination options***
- ***Epoxy terminal-seal compatible with bottom wash cleaning***
- ***RoHS complaint models available***

## *Typical Applications*

- ***Telecommunications***
- ***Instrumentation***
- ***Medical equipment***



c UL us

## Specifications

CONTACT RATING: B contact material: 0.4 VA max. @ 20 V AC or DC max. Q contact material: 5 AMPS @ 120 V AC or 28 V DC; 2 AMPS @ 250 V AC. See page F-15 for additional ratings.

ELECTRICAL LIFE: 7X01 and UX1 models: 100,000 make-and-break cycles at full load. All other models: 40,000 cycles.

CONTACT RESISTANCE: Below 10 m Ω typ. initial @ 2-4 V DC, 100 mA, for both silver and gold plated contacts.

INSULATION RESISTANCE: $10^9$ Ω min.

DIELECTRIC STRENGTH: 1000 Vrms min. @ sea level.

OPERATING TEMPERATURE: –30ºC to 85ºC.

SOLDERABILITY: Per MIL-STD-202F method 208D, or EIA RS-186E method 9 (1 hour steam aging).

**For materials see page F-4.**

**NOTE:** Any models supplied with P, S R, Q, B or G contact material are RoHS compliant and compatible.

**NOTE**: Specifications listed above are for switches with standard options. For information on specific and custom switches, consult Customer Service Center.

## Build-A-Switch

To order, simply select desired option from each category and place in the appropriate box. Available options are shown and described on pages F–4 thru F–16. For additional options not shown in catalog, consult our Customer Service Center.

### Switch Function

**7101** SP On-None-On
**7103** SP On-Off-On
**7105** SP Mom.-Off-Mom.
**7107** SP On-Off-Mom.
**7108** SP On-None-Mom.
**7109** SP None-On-Mom.
**7201** DP On-None-On
**7203** DP On-Off-On
**7205** DP Mom.-Off-Mom.
**7207** DP On-Off-Mom.
**7208** DP On-None-Mom.
**7211** DP On-On-On
**7213** DP On-On-Mom.
**7215** DP Mom.-On-Mom.
**7301** 3P On-None-On
**7303** 3P On-Off-On
**7305** 3P Mom.-Off-Mom.
**7308** 3P On-None-Mom.
**7401** 4P On-None-On
**7403** 4P On-Off-On
**7405** 4P Mom.-Off-Mom.
**7408** 4P On-None-Mom.
**7411** 4P On-On-On
**7413** 4P On-On-Mom.
**7415** 4P Mom.-On-Mom.

**Note:** UL models available, see pages F-4 & F-5.

### Actuator

**M** .200" high
**P3** Flatted, anti-rotation, .450" high
**S** .420" high
**T** .687" high, 15/32 bushing
**K2** Locking lever, .704" high
**K9** Locking lever, .704" high
**K12** Locking lever, .732" high
**K19** Locking lever, .732" high
**L** .840" high
**L1** .640" high
**L1P** Anti-rotation, .640" high
**L2** .550" high
**L2P** Anti-rotation, .550" high
**L3** Plastic .940" inch
**L40** Lever handle without cap
**L41** .531" high lever handle with cap
**L42** .838" high lever handle with cap
**MP** Anti-rotation, .200" high
**P1** Flatted, anti-rotation, .840" high
**P4** Flatted, anti-rotation, .250" high
**SP** Anti-rotation, .420" high
**T1** .487" high, 15/32 bushing
**T1P** Anti-rotation, .487" high, 15/32 bushing
**T2P** Flatted, anti-rotation, .610" high, 15/32 bushing,
**TP** Anti-rotation, .687" high, 15/32 bushing

### Bushing

**D** .280 high, keyway
**H** .296 high, flat
**Y** .350 high, keyway
**NONE** No bushing choice required
**CW** Splashproof
**D8** .280" high, flat
**D9** .280" high, keyway
**H3** .315" high, keyway
**H4** 8mm high, keyway
**Y1** .378" high, keyway
**Y3** 8.9mm high, keyway
**Y4** .378" high, flat
**Y9** .350" high, keyway

### Terminations

**A** Right angle, PC thru-hole
**AV2** Vert. right angle, PC thru-hole
**C** PC Thru-hole
**V3** .460 high, V-bracket
**Z** Solder lug
**A2** Right angle, PC thru-hole
**A3** Right angle, PC thru-hole
**A4** Right angle, PC thru-hole
**AW1** Right angle, extended, PC thru-hole
**AW4** Right angle, extended, PC thru-hole
**V2** .555" high, V-bracket
**V4** .630" high, V-bracket
**V6** .460" high, V-bracket
**V7** .630" high, V-bracket
**V8** .953" high, V-bracket
**V9** 1.150" high, V-bracket
**V21** .555" high, snap-in V-bracket
**V31** .460" high, snap-in V-bracket
**V41** .630" high, snap-in V-bracket
**V71** .630" high, snap-in V-bracket
**V81** .953" high, snap-in V-bracket
**W** .750" long, wire wrap
**W1** .964" long, wire wrap
**W3** .425" long, wire wrap
**W4** 1.062" long, wire wrap
**W5** 1.305" long, wire wrap
**Z3** Quick connect

### Contact Material

**B** Gold
**P** Gold, matte-tin
**Q** Silver
**S** Silver, matte-tin
**G** Gold over silver
**R** Gold over silver, matte-tin

### Seal

**E** Epoxy
**I** Epoxy potted base

### Actuator Color/Finish

**NONE** Bright chrome
**2** Black
**3** Red
**S** Satin chrome

### KXX Actuator Color/Finish

**NONE** Natural aluminum
**2** Black anodized aluminum
**3** Red anodized aluminum
**7** Blue anodized aluminum

### Bushing Finish

**NONE** Nickel on all bushings (except D8, satin chrome)
**2** Black

# 7000 Series
# Miniature Toggle Switches

## Materials

CASE: Glass filled nylon 6/6, flame retardant, heat stabilized, or diallyl phthalate (DAP) (UL 94V-0).

ACTUATOR: Brass, chrome plated.

BUSHING: Brass or zinc, nickel plated.

HOUSING: Stainless steel.

SWITCH SUPPORT: Brass or steel, tin plated.

END CONTACTS: B contact material: Copper alloy, with gold plate over nickel plate. Q contact material: Coin silver, silver plated. See page F-15 for additional contact materials.

CENTER CONTACTS & ALL TERMINALS: B contact material: Copper alloy, with gold plate over nickel plate. Q contact material: Copper alloy, silver plated. See above for additional contact materials.

TERMINAL SEAL: Epoxy.

HARDWARE: Nut & Locking Ring: Brass, nickel plated. Lockwasher: Steel, nickel plated.

**NOTE:** Materials listed above are for switches with standard options. For information on specific and custom switches, consult Customer Service Center.

## SWITCH FUNCTION

| NO. POLES | MODEL NO. | UL** MODEL NO. | SWITCH FUNCTION POS. 1 | POS. 2 | POS. 3 | CONNECTED TERMINALS POS. 1 | POS. 2 | POS. 3 | SCHEMATIC |
|---|---|---|---|---|---|---|---|---|---|
| SP | 7101 | U11 | ON | NONE | ON | 2-3 | N/A | 2-1 | |
| | 7103 | U13 | ON | OFF | ON | | | | |
| | 7105 | U15 | MOM. | OFF | MOM. | 2-3 | OPEN | 2-1 | |
| | 7107 | U17 | ON | OFF | MOM. | | | | |
| | 7108 | U18 | ON | NONE | MOM. | 2-3 | N/A | 2-1 | |
| | 7109 | U19 | NONE | ON | MOM. | N/A | 2-3 | 2-1 | SPDT |

**SPDT**







Terminal Numbers For Reference Only

Part number shown: 7101SYZBE

| | | | | | | | | | |
|---|---|---|---|---|---|---|---|---|---|
| DP | 7201 | U21 | ON | NONE | ON | 2-3,5-6 | N/A | 2-1,5-4 | |
| | 7203 | U23 | ON | OFF | ON | | | | |
| | 7205 | U25 | MOM. | OFF | MOM. | 2-3,5-6 | OPEN | 2-1,5-4 | |
| | 7207 | U27 | ON | OFF | MOM. | | | | |
| | 7208 | U28 | ON | NONE | MOM. | 2-3,5-6 | N/A | 2-1,5-4 | |
| | 7211 * | U211* | ON | ON | ON | | | | |
| | 7213* | U213* | ON | ON | MOM. | 2-3,5-6 | 2-3,5-4 | 2-1,5-4 | |
| | 7215* | U215* | MOM. | ON | MOM. | | | | DPDT |

**DPDT**







Terminal Numbers For Reference Only

Part number shown: 7201SYZQE

MOM. = Momentary

* Wiring for 3-way switch, see Section N.

** U11–U415 model nos. with all options when ordered with G, R, Q or S contact material.

Third Angle Projection

*Dimensions are shown: Inches (mm)*
*Specifications and dimensions subject to change*

## SWITCH FUNCTION

| NO. POLES | MODEL NO. | UL** MODEL NO. | SWITCH FUNCTION POS. 1 | SWITCH FUNCTION POS. 2 | SWITCH FUNCTION POS. 3 | CONNECTED TERMINALS POS. 1 | CONNECTED TERMINALS POS. 2 | CONNECTED TERMINALS POS. 3 | SCHEMATIC |
|---|---|---|---|---|---|---|---|---|---|
| 3P | 7301 | U31 | ON | NONE | ON | 2-3,5-6,8-9 | N/A | 2-1,5-4,8-7 | |
| | 7303 | U33 | ON | OFF | ON | 2-3,5-6,8-9 | OPEN | 2-1,5-4,8-7 | |
| | 7305 | U35 | MOM. | OFF | MOM. | | | | |
| | 7307 | U37 | ON | OFF | MOM. | | | | |
| | 7308 | U38 | ON | NONE | MOM. | 2-3,5-6,8-9 | N/A | 2-1,5-4,8-7 | 3PDT |

**3PDT**







Part number shown: 7301SYZQE

Terminal Numbers
For Reference Only

| NO. POLES | MODEL NO. | UL** MODEL NO. | SWITCH FUNCTION POS. 1 | SWITCH FUNCTION POS. 2 | SWITCH FUNCTION POS. 3 | CONNECTED TERMINALS POS. 1 | CONNECTED TERMINALS POS. 2 | CONNECTED TERMINALS POS. 3 | SCHEMATIC |
|---|---|---|---|---|---|---|---|---|---|
| 4P | 7401 | U41 | ON | NONE | ON | 2-3,5-6,8-9,11-12 | N/A | 2-1,5-4,8-7,11-10 | |
| | 7403 | U43 | ON | OFF | ON | 2-3,5-6,8-9,11-12 | OPEN | 2-1,5-4,8-7,11-10 | |
| | 7405 | U45 | MOM. | OFF | MOM. | | | | |
| | 7408 | U48 | ON | NONE | MOM. | 2-3,5-6,8-9,11-12 | N/A | 2-1,5-4,8-7,11-10 | |
| | 7411* | U411* | ON | ON | ON | 2-3,5-6,8-9,11-12 | 2-3,5-4,8-9,11-10 | 2-1,5-4,8-7,11-10 | |
| | 7413* | U413* | ON | ON | MOM. | | | | |
| | 7415* | U415* | MOM. | ON | MOM. | | | | 4PDT |

**4PDT**







Part number shown: 7401SYZQE

Terminal Numbers
For Reference Only

MOM. = Momentary

Wiring for 3-way switch, see Section N.

** U11–U415 model nos. c UL us with all options when ordered with G, Q, R or S contact material.



Third Angle Projection

*Dimensions are shown: Inches (mm)*
*Specifications and dimensions subject to change*

# 7000 Series
# Miniature Toggle Switches

## ACTUATOR




**S** .420" HIGH [1]

**SP** ANTIROTATION, .420" HIGH [2,3]




S actuator standard when ordered with C, W-W5, Z & Z3 terminations.
Caps are available separately, see page F-16.

**M** .200" HIGH [1]

**MP** ANTIROTATION, .200" HIGH [2,3]




M actuator standard when ordered with all terminations except C, W-W5, Z & Z3.
Caps are available separately, see page F-16.

**L, L1, L2** .840", .640", .550" HIGH [1]

**L1P, L2P** ANTIROTATION, .840", .640", .550" HIGH [2,3]




| OPTION CODE | DIM 'A' |
|---|---|
| L | .840 (21,34) |
| L1, L1P | .640 (16,26) |
| L2, L2P | .550 (13,97) |

Caps are available separately, see page F-16.

***P1** FLATTED WITH ANTIROTATION, .840" HIGH [2,3]




***P3** FLATTED WITH ANTIROTATION, .450" HIGH [2,3]




***P4** FLATTED WITH ANTIROTATION, .250" HIGH [2,3]




*Dress nut part number 709901201 supplied standard with threaded bushing. (Part number 709903201 with metric threaded bushings.)

**T** .687 (17,45) HIGH [1,2]

**TP** ANTIROTATION, .687 (17,45) HIGH, 15/32 BUSHING [1,2,3]




**T1** .487 (12,37) HIGH [1,2]

**T1P** ANTIROTATION, .487 (12,37) HIGH, 15/32 BUSHING [1,2,3]




Bushing option code not required unless CW splashproof bushing ordered. TP & T1P actuators not available with CW splashproof bushing. All TXX actuators not available on single pole models with A-A4, AW1-AW4 terminations.

**T2P** FLATTED, ANTIROTATION, .610" HIGH, 15/32 BUSHING [1,2,3]




Bushing option code not required. T2P actuator not available with CW splashproof bushing or single pole models with A-A4, AW1-AW4 terminations.

[1] L, L1, L2, M, S & TXX actuators not available with Y1 bushing.

[2] L1P, L2P, MP, P1, P3, P4, SP & TXX actuators not available with D8 & H4 bushing.

[3] Antirotation: Provides anti-'push-in' feature on actuator.

* Add .070 (1,78) for D, D8 & D9 bushings, subtract .020 (0,51) for H3 bushing.

| OPTION CODE | ACTUATOR FINISH |
|---|---|
| NONE | BRIGHT CHROME-With Nickel Plated Bushing |
| 2 | BLACK |
| S | SATIN CHROME |

**NOTE:** Black hardware is supplied when either black actuators or bushings are specified. For additional hardware, see Section N.

Third Angle Projection

*Dimensions are shown: Inches (mm)*
*Specifications and dimensions subject to change*

## ACTUATOR




**K2** LOCKING LEVER, .704" HIGH (threaded)

**K9** LOCKING LEVER, .704" HIGH (unthreaded)

**K12** LOCKING LEVER, .732" HIGH (threaded)

**K19** LOCKING LEVER, .732" HIGH (unthreaded)




Replaces K, K8




Replaces K1, K18

| OPTION CODE | ACTUATOR CAP FINISH |
|---|---|
| NONE | NATURAL ALUMINUM–With Nickle Plated Bushing |
| 2 | BLACK ANODIZED ALUMINUM |
| 3 | RED ANODIZED ALUMINUM |
| 7 | BLUE ANODIZED ALUMINUM |

* All KXX models including KXXCW have a keyway

### Locking Positions



–01 Models
2 Position lock

–03 & –11 Models
3 Position lock

–05, –09 & –15 Models
1 Position lock

–07 & –13 Models
2 Position lock

–08 Models
1 Position lock

**NOTE:** To prevent accidental actuation, toggle must be lifted before being actuated. When released, toggle will lock in place. Overtightening mounting nut may cause actuator to bind.

Locking levers supplied with bushing shown.

Bushing option code not required unless CW splashproof bushing ordered.

**L40** LEVER HANDLE WITHOUT CAP



No color choice required

**L41** PLASTIC LEVER HANDLE WITH ANTIROTATION AND CAP, P/N 4810




**L42** PLASTIC LEVER HANDLE WITH ANTIROTATION AND CAP, P/N 4811




Finish: Matte (L41 & L42).

**L3** PLASTIC .940" HIGH




| OPTION CODE | PLASTIC ACTUATOR COLORS |
|---|---|
| NONE | No Actuator Color (L40 option) |
| 2 | BLACK |
| 3 | RED |

* Add .070 (1,78) for D, D8 & D9 bushings, subtract .020 (0,51) for H3 bushing.

**NOTE:** Lever handle for L41 & L42 actuators supplied, but not installed. For interchangeability, order L40 actuator option and lever handles separately, see page F-16. L4X actuators not available with H4, Y1, Y4 bushings. Antirotation: Provides anti-'push-in' feature on actuator.

Third Angle Projection

*Dimensions are shown: Inches (mm)*
*Specifications and dimensions subject to change*

# 7000 Series
# Miniature Toggle Switches

## BUSHING




**Y** .350" HIGH, THREADED, KEYWAY

**Y9** .350" HIGH, UNTHREADED, KEYWAY







Y bushing standard with C, W-W5, Z or Z3 terminations.

**NONE** NO BUSHING

No bushing choice required with KXX, TXX actuators. (exception: Specify CW if splashproof bushing desired).

**D** .280" HIGH, THREADED, KEYWAY

**D8** .280" HIGH, UNTHREADED, FLAT [3]

**D9** .280" HIGH, UNTHREADED, KEYWAY




D8 D, D9




D9 bushing standard with all terminations except C, W-W5, Z or Z3. Add .070 (1,78) to all actuators lengths with D, D8 & D9 bushings.

**H** .296" HIGH, FLAT THREADED, HIGH TORQUE [1,2]




**H3** .315" HIGH, KEYWAY THREADED, HIGH TORQUE [1,2]




Subtract .020 (0,51) from all actuator lengths for H3 bushing.

**H4** 8mm HIGH, KEYWAY, THREADED, METRIC HIGH TORQUE [1,2,3]




**Y1** .378" HIGH, KEYWAY, THREADED, HIGH TORQUE [1,2,4]




**Y3** 8.9mm HIGH, KEYWAY, THREADED, METRIC




**Y4** .378" HIGH, FLAT, THREADED, HIGH TORQUE [1,2,5]




**CW** THREADED, SPLASHPROOF [1,2]

For T & T1 actuators.




IP67 Degree of protection, totally protected against dust, full-scale voltage protection, temporary immersion. Internal actuator seal standard.
External bushing seal available separately from APM Hexseal, part # MFS-60064.

For actuators other than T, T1 and KXX.




IP67 Degree of protection, totally protected against dust, full-scale voltage protection, temporary immersion. Internal actuator seal and external bushing seal washer standard. IP65 degree of protection for LXP, MP, PX or SP with CW option.

| OPTION CODE | BUSHING FINISH |
|---|---|
| NONE | NICKEL on all bushings except 'D8' satin chrome. |
| 2 | BLACK |

**[1] Will withstand 12 in.-lbs. of torque with no distortion.**

[2] CW. H, H3, H4, Y1 & Y4 bushings not available on single pole models with A4 terminations.

[3] D8 & H4 bushings available only with L, L1, L2, M & S actuators.

[4] Y1 bushing available only with LXP, MP, PX & SP actuators.

[5] Y4 bushing not available with L4X actuators.

**NOTE:** Two mounting nuts, locking ring and lockwasher supplied standard with threaded bushings. Black hardware is supplied when either black bushings or actuators are specified. Optional mounting nut and locking ring styles and finishes available, see Section N.

### PANEL MOUNTING

**1/4 INCH BUSHING**




Without locking ring.




With standard locking ring.




With small locking ring.

**METRIC BUSHING**




Without locking ring. With locking ring.

**15/32 INCH BUSHING**




Without locking ring. With standard locking ring.

Third Angle Projection

*Dimensions are shown: Inches (mm)*
*Specifications and dimensions subject to change*

## TERMINATIONS

### Z SOLDER LUG




.030 (0,76) Thk.

**SPDT thru 4PDT**

Not available with P, R or S contact materials.

### C PC THRU-HOLE




PC MOUNTING




**SPDT thru 4PDT**

### Z3 QUICK CONNECT




.030 (0,76) Thk.

Not available with P, R or S contact materials.
Mating quick connector available, order part number 530100000, page F-16.

**SPDT thru 4PDT**

### W, W1, W3, W4, W5 WIRE WRAP




.030 (0,76) Thk.

| OPTION CODE | DIM 'A' |
|---|---|
| W | .750 (19,05) |
| W1 | .964 (24,48) |
| W3 | .425 (10,80) |
| W4 | 1.062 (26,97) |
| W5 | 1.305 (33,15) |

**SPDT thru 4PDT**

### A RIGHT ANGLE, PC THRU-HOLE




Actuator Shown In Pos. 1







Switch support with CW, H, H3, H4, Y1, Y4 bushings and KXX actuators.

Part No. Shown: 7101MHABE




SECTION A-A

Terminal Nos. For Reference Only



7101MD9ABE
Horizontal Actuation
**SPDT**

### A3 RIGHT ANGLE, SNAP-IN, PC THRU-HOLE




Not available with I seal option.
Terminal bend radii and lead-in manufacturing option.

### AW1, AW4 RIGHT ANGLE, EXTENDED, PC THRU-HOLE




| OPTION CODE | DIM 'A' |
|---|---|
| AW1 | .72 (18,3) |
| AW4 | .83 (21,1) |

PC MOUNTING




Third Angle Projection

*Dimensions are shown: Inches (mm)*
*Specifications and dimensions subject to change*

# 7000 Series
# Miniature Toggle Switches

## TERMINATIONS

### A RIGHT ANGLE, PC THRU-HOLE

7201MD9ABE
Horizontal Actuation
**DPDT**










SECTION A-A

### A3 RIGHT ANGLE, SNAP-IN, PC THRU-HOLE




### AW1, AW4 RIGHT ANGLE, EXTENDED, PC THRU-HOLE




| OPTION CODE | DIM 'A' |
|---|---|
| AW1 | .40 (10,2) |
| AW4 | .50 (12,7) |

**PC MOUNTING**




Not available with I seal option.
Terminal bend radii and lead-in manufacturing option.

### A RIGHT ANGLE, PC THRU-HOLE



7301MD9ABE
Horizontal Actuation
**3PDT**










SECTION A-A

### AW4 RIGHT ANGLE, EXTENDED, PC THRU-HOLE




**PC MOUNTING**




Not available with I seal option.
Terminal bend radii and lead-in manufacturing option.

## TERMINATIONS

### A2 RIGHT ANGLE, PC THRU-HOLE, .156" PITCH



7101MHA2BE
Horizontal Actuation
**SPDT**

Not available with TXX actuators and I seal.
Terminal bend radii and lead-in manufacturing option.

Part No. Shown: 7101MHA2BE

### A4 RIGHT ANGLE, PC THRU-HOLE .156" PITCH






7101MD9A4BE
Horizontal Actuation
**SPDT**

Actuator Shown In Pos. 1

Not available with KXX & TXX actuators, CW, H, H3, H4, Y1 & Y4 bushings, and I seal. Terminal bend radii and lead-in manufacturing option.

**NOTE:** The A4 option is available with any contact material and can be UL recognized and CSA certified. The PC pattern must clear switch support legs.

### AV2 VERTICAL RIGHT ANGLE, PC THRU-HOLE, .150" PITCH



7101MD9AV2BE
Horizontal Actuation
**SPDT**

Actuator Shown In Pos. 1

Not available with I seal option.
Terminal bend radii and lead-in manufacturing option.

### AV2 VERTICAL RIGHT ANGLE, PC THRU-HOLE, .150" PITCH



7201MD9AV2BE
Vertical Actuation
**DPDT**

Actuator Shown In Pos. 1

Not available with I seal option.
Terminal bend radii and lead-in manufacturing option.

Third Angle Projection

*Dimensions are shown: Inches (mm)*
*Specifications and dimensions subject to change*

## TERMINATIONS

### AV2 VERTICAL RIGHT ANGLE, PC THRU-HOLE, .150" PITCH

7301MD9AV2BE
Vertical Actuation
**3PDT**




Actuator Shown In Pos. 1




SECTION A-A

PC MOUNTING




Not available with I seal option.
Terminal bend radii and lead-in manufacturing option.

### AV2 VERTICAL RIGHT ANGLE, PC THRU-HOLE, .150" PITCH

7401MD9AV2BE
Vertical Actuation
**4PDT**




Actuator Shown In Pos. 1




SECTION A-A

PC MOUNTING




Not available with I seal option.
Terminal bend radii and lead-in manufacturing option.

### V2, V6, V7, V8 VERTICAL MOUNT, V-BRACKET
### V21, V71, V81 VERTICAL MOUNT, V-BRACKET, SNAP-IN

7101MD9__BE
**SPDT**




Actuator Shown In Pos. 1

PC MOUNTING




| OPTION CODE | DIM 'A' |
|---|---|
| V2, V21 | .555 (14,10) |
| V6 | .460 (11,68) |
| V7, V71 | .630 (16,00) |
| V8, V81 | .953 (24,21) |

Not available with I seal option.

Third Angle Projection

*Dimensions are shown: Inches (mm)*
*Specifications and dimensions subject to change*

## TERMINATIONS

### V2, V6, V7, V8 VERTICAL MOUNT, V-BRACKET
### V21, V61, V71, V81 VERTICAL MOUNT, V-BRACKET, SNAP-IN




Actuator Shown In Pos. 1

Not available with I seal option.

**PC MOUNTING**




| OPTION CODE | DIM 'A' |
|---|---|
| V2, V21 | .555 (14,10) |
| V6, V61 | .460 (11,68) |
| V7, V71 | .630 (16,00) |
| V8, V81 | .953 (24,21) |



7201MD9__BE
**DPDT**

### V2, V7, V8 VERTICAL MOUNT, V-BRACKET
### V21, V71, V81 VERTICAL MOUNT, V-BRACKET, SNAP-IN




Actuator Shown In Pos. 1

Not available with I seal option.

**PC MOUNTING**




| OPTION CODE | DIM 'A' |
|---|---|
| V2, V21 | .555 (14,10) |
| V7, V71 | .630 (16,00) |
| V8, V81 | .953 (24,21) |

7301MD9__BE
**3PDT**

### V2, V7, V8 VERTICAL MOUNT, V-BRACKET
### V21, V71, V81 VERTICAL MOUNT, V-BRACKET, SNAP-IN




Actuator Shown In Pos. 1

Not available with I seal option.

**PC MOUNTING**




| OPTION CODE | DIM 'A' |
|---|---|
| V2, V21 | .555 (14,10) |
| V7, V71 | .630 (16,00) |
| V8, V81 | .953 (24,21) |



7401MD9__BE
**4PDT**

Third Angle Projection

*Dimensions are shown: Inches (mm)*
*Specifications and dimensions subject to change*

## TERMINATIONS

### V3, V4, V9 VERTICAL MOUNT, V-BRACKET
### V31, V41 VERTICAL MOUNT, V-BRACKET, SNAP-IN



7101MD9__BE
**SPDT**




Actuator Shown In Pos. 1

Not available with I seal option.

**PC MOUNTING**




| OPTION CODE | DIM 'A' |
|---|---|
| V3, V31 | .460 (11,68) |
| V4, V41 | .630 (16,00) |
| V9 | 1.150 (29,21) |

### V3, V4, V9 VERTICAL MOUNT, V-BRACKET
### V31, V41 VERTICAL MOUNT, V-BRACKET, SNAP-IN










Actuator Shown In Pos. 1

Not available with I seal option.

**PC MOUNTING**



7201MD9__BE
**DPDT**

| OPTION CODE | DIM 'A' |
|---|---|
| V3, V31 | .460 (11,68) |
| V4, V41 | .630 (16,00) |
| V9 | 1.150 (29,21) |

### V4, V9 VERTICAL MOUNT, V-BRACKET
### V41 VERTICAL MOUNT, V-BRACKET, SNAP-IN










Actuator Shown In Pos. 1

Not available with I seal option.

**PC MOUNTING**



7301MD9__BE
**3PDT**

| OPTION CODE | DIM 'A' |
|---|---|
| V4, V41 | .630 (16,00) |
| V9 | 1.150 (29,21) |

Third Angle Projection

*Dimensions are shown: Inches (mm)*
*Specifications and dimensions subject to change*

## TERMINATIONS

**V4, V9** VERTICAL MOUNT, V-BRACKET

**V41** VERTICAL MOUNT, V-BRACKET, SNAP-IN




Actuator Shown In Pos. 1



Snap-In




**PC MOUNTING**






7401MD9__BE
**4PDT**

| OPTION CODE | DIM 'A' |
|---|---|
| V4, V41 | .630 (16,00) |
| V9 | 1.150 (29,21) |

Not available with I seal option.

## CONTACT MATERIAL

| OPTION CODE | CONTACT MATERIAL | TERMINAL PLATING | RATINGS | |
|---|---|---|---|---|
| B | GOLD [1] | GOLD [1] | LOW LEVEL/ DRY CIRCUIT | 0.4 VA MAX. @ 20 V AC OR DC MAX. |
| P | | MATTE-TIN [6] | | |
| Q | SILVER [4,5] | SILVER [5] | POWER | 5 AMPS @ 120 V AC OR 28 V DC; 2 AMPS @ 250 V AC. |
| S | | MATTE-TIN [6] | | |
| G | GOLD OVER SILVER [2,3] | GOLD [3] | LOW LEVEL/DRY CIRCUIT OR POWER | 0.4 VA MAX @ 20 V AC OR DC MAX. OR 5 AMPS @ 120 V AC OR 28 V DC; 2 AMPS @ 250 V AC. |
| R | | MATTE-TIN [6] | | |

* Note: See Technical Data section of this catalog for RoHS compliant and compatible definitions and specifications.

[1] CONTACTS & TERMINALS: Copper alloy, with gold plate over nickel plate.

[2] END CONTACTS: Coin silver, with gold plate over nickel plate.

[3] CENTER CONTACTS & ALL TERMINALS: Copper alloy, with gold plate over nickel plate.

[4] END CONTACTS: Coin silver, silver plated.

[5] CENTER CONTACT & ALL TERMINALS: Copper alloy, silver plated.

[6] TERMINALS: Copper alloy, with matte tin alloy nickel plate.

**NOTE:** Any models supplied with P, S, R, Q, B or G contact material are RoHS compliant.

U11-U415 model numbers c UL us with all options when ordered with G, S, R, or Q contact material.

B contact material standard with all terminations except C, Z & Z3.

Q contact material standard with C, Z & Z3 terminations.

P, S & R contact materials not available with Z & Z3 terminations.

F Toggle

Third Angle Projection

*Dimensions are shown: Inches (mm)*
*Specifications and dimensions subject to change*

# 7000 Series
# Miniature Toggle Switches

## SEAL

### E EPOXY SEAL




Compatible with “bottom-wash” PC board cleaning methods.

### I EPOXY POTTED BASE




| NO. POLES | DIM 'A' |
|---|---|
| SP | .410 (10,41) |
| DP | .440 (11,18) |
| 3P | .505 (12,83) |
| 4P | .505 (12,83) |

Available with C, W-W5, Z & Z3 terminations only.

## AVAILABLE HARDWARE

**Cap**




**PART NO.**

**896801000** WHITE
**896802000** BLACK
**896803000** RED

Material: Polyethylene
Finish: Matte

**Cap**




**PART NO.**

**763701000** WHITE
**763702000** BLACK
**763703000** RED

Material: Vinyl
Finish: Matte

**Cap**




**PART NO.**

**706201000** WHITE
**706202000** BLACK
**706203000** RED

Material: Vinyl
Finish: Matte

**L41 Lever handle**

**PART NO.**

**481001000** WHITE
**481002263** BLACK
**481003000** RED

Material: Nylon
Finish: Matte

**L42 Lever handle**




**PART NO.**

**481101000** WHITE
**481102263** BLACK
**481103000** RED

Material: Nylon
Finish: Matte

**Fits Z3 Termination female connector**

**PART NO.**

**530100000**

Available in loose pieces.

**NOTE:** Additional nuts, locking rings and lockwashers available separately, see Section N.

Other colors available, consult Customer Service Center.

**759D02000 Sealing Boot**




NOTE: For use with S actuator style when combined with D, H, H3, Y, and Y4 bushings

**703D02000 Sealing Boot**




NOTE: For use with T and TP style actuators. **Can not be used for Switch Functions: 7103, 7203, 7303, 7403, 7107, 7207, 7307, 7407.**

**704D02000 Sealing Boot**




NOTE: For use with T, TP and T2P style actuators. Can not be used for Switch Functions: 7103, 7203, 7303, 7403, 7107, 7207, 7307, and 7407.

Third Angle Projection

*Dimensions are shown: Inches (mm)*
*Specifications and dimensions subject to change*

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

C&K Components:

7401MDZQE 7201MDV61QE 7303MYZQE 7101K9V3BE2 7103L40CWV31KE 7203SYZBE 7101SYV31QE 7407P3H3ZQE 7101MD9V4BE 7103MYZQE 7401P3YZQE 7105P3YWBE 7101P3YWQE 7107SDZBE 7211MDAV2BE 7101T1CWCQE 7101SD9V31KE 7101SYV3BE 7101K9AKE 7208MD9ABE 7108P3YZQE 7208SYZQE 7208P3YZQE 7108MD9V3QE 7108MD9AQE 7108K2ZQE 7108SYZQE 7107TCQE 7215SYZQE 7415SYZQE 7103K2AV2BE 7211P3YCQE 7205TCQE 7105TCQE 7207K12ZBE 7205P3Y4CQE 7211SYCQE 7411SYZQE 7401P3YZQE2 7211SYAQE 7211SYZQE 7401MDCQE 7205TCWCQE 7207SYCQE 7213P1YZQE2 7413SYZQE 7213SYZQE 7103K2V2QE 7305P1H3ZQE 7211MD9ABE 7201P3DZQE 7105SYZBE 7105P4D9ZQE 7205TPZQE 7205P3YZQE 7107MHA2BE 7105SYZQE 7105P3D9V3BE 7105MD9ABE 7405SYZQE 7305SYZQE 7105L42YZQE2 7205SYZQE 7105P3YCQE 7105SYCQE 7103MYZBE 7301SYAQE 7101SYZQI 7201K2CQE 7103P3D9V3BE 7208TCWZQE 7203SYCQE 7203SYZQE 7103MD9AV2BE 7203L1YZQE 7403SYZQE 7103L1YZQE 7203SYAQE 7103MD9ABE 7203MDZQE 7203TZQE 7103TZQE 7103SYZBE 7303SYZQE 7103P3YZQE22 7103MD9V3BE 7403SYZBE 7103SYZQE 7103SD9ABE 7103P3YZQE 7303SYCBE 7103SYCQE 7107SDV3BE 7105TZQE 7101L41YZQE2 7101SDCQE 7211MD9ALE 7211MD9AGE 7201K2CWZQE 7201MD9V3BE