


## Features

- LOW POWER CONSUMPTION.
- POPULAR T-1 DIAMETER PACKAGE.
- GENERAL PURPOSE LEADS.
- RELIABLE AND RUGGED.
- LONG LIFE - SOLID STATE RELIABILITY.
- AVAILABLE ON TAPE AND REEL.

### Description

The Pure Green source color devices are made with Gallium Phosphide Pure Green Light Emitting Diode.

## Package Dimensions



Notes:

1. All dimensions are in millimeters (inches).
2. Tolerance is  $\pm 0.25(0.01")$  unless otherwise noted.
3. Lead spacing is measured where the lead emerge package.
4. Specifications are subject to change without notice.

## Selection Guide

|          | Dice             | Lens Type         | Iv (mcd)<br>@ 10 mA |      | Viewing<br>Angle |
|----------|------------------|-------------------|---------------------|------|------------------|
|          |                  |                   | Min.                | Typ. | θ1/2             |
| W132XPGT | PURE GREEN (GaP) | GREEN TRANSPARENT | 3                   | 10   | 50°              |

Note:

1. θ1/2 is the angle from optical centerline where the luminous intensity is 1/2 the optical centerline value.

## Electrical / Optical Characteristics at T<sub>A</sub>=25°C

| Symbol            | Parameter                | Device     | Typ. | Max. | Units | Test Conditions           |
|-------------------|--------------------------|------------|------|------|-------|---------------------------|
| λ <sub>peak</sub> | Peak Wavelength          | Pure Green | 555  |      | nm    | I <sub>F</sub> =20mA      |
| λ <sub>D</sub>    | Dominate Wavelength      | Pure Green | 555  |      | nm    | I <sub>F</sub> =20mA      |
| Δλ <sub>1/2</sub> | Spectral Line Half-width | Pure Green | 30   |      | nm    | I <sub>F</sub> =20mA      |
| C                 | Capacitance              | Pure Green | 45   |      | pF    | V <sub>F</sub> =0V;f=1MHz |
| V <sub>F</sub>    | Forward Voltage          | Pure Green | 2.25 | 2.5  | V     | I <sub>F</sub> =20mA      |
| I <sub>R</sub>    | Reverse Current          | Pure Green |      | 10   | uA    | V <sub>R</sub> = 5V       |


## Absolute Maximum Ratings at T<sub>A</sub>=25°C

| Parameter                     | Pure Green          | Units |
|-------------------------------|---------------------|-------|
| Power dissipation             | 105                 | mW    |
| DC Forward Current            | 25                  | mA    |
| Peak Forward Current [1]      | 135                 | mA    |
| Reverse Voltage               | 5                   | V     |
| Operating/Storage Temperature | -40°C To +85°C      |       |
| Lead Solder Temperature [2]   | 260°C For 5 Seconds |       |

Notes:

1. 1/10 Duty Cycle, 0.1ms Pulse Width.

2. 2mm below package base.



## Pure Green

### W132XPGT

