

Search Results

Evaluate

- FAQ's

Design a Solution

- Part Drawings

- PDF-Fiber Optic ..

How to Buy

- Bill of Material

- Favorite Products List

- Locate Distributor

Home > Product On-Line Catalog > Search Results >

Current refinements (click ☐ to remove) Search Tips [?](#)

☒ Text Search: 'F9D2-3M12Y'

Your search criteria matched only one product, shown below

F9D2-3M12Y



- Pass all TIA/EIA-568-B.3 performance requirements
- 100% factory inspected end face geometry in compliance with Telcordia GR-326-CORE, Issue 3
- Typical insertion loss per connection: 0.25dB
- UPC polished (55dB minimum return loss)
- Factory terminated and 100% tested for insertion loss and return loss
- Insertion loss and return loss data recorded for every singlemode patch cord
- Lifetime traceability of test data to a Q.C. number on each patch cord
- Highest quality flame retardant fiber optic cable with tight-buffered coating on each optical fiber

• Part Number	F9D2-3M12Y
• RoHS Compliancy Status	Intended for use in fixed installations which are outside the scope of RoHS
• Note	F9D2-3M12Y replaces F9D2-3M12
• Part Description	ST to SC singlemode duplex patch cord, 3mm jacketed cable (two ST connectors on one end and two SC connectors on the other end) – 9/125µm.
• Product Type	Hybrid Patch Cords
• Length (m)	12
• Fiber Compatibility	9/125µm
• Fiber Cable Size	3mm
• Fiber Cable Type	Jacketed
• Fiber Type	Singlemode
• Cable Color	Yellow
• Cable Type	Duplex
• CE Compliant	No
• Connector 1 Type	ST Connector
• Connector 2 Type	SC Connector
• End Configurations	ST to SC
• Fiber Count	2
• Flammability Rating	Riser (OFNR)
• Pricing Description	ST-SC 9µm Dupl Singlemode Patch Cord 12m
• Min. Order UOM	PC
• Min. Order Qty.	1
• BOM Qty. (# of Pkgs.)	<input type="text" value="0"/>
• Add to Favorite Product List	<input type="checkbox"/>

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.