







PART NUMBER
48QN50T17070

PROPRIETARY

UNLESS OTHERWISE SPECIFIED			
XXX = ±.003	SURFACE FINISH	MATERIAL	PROCESSES
XX = ±.010			
X = ±.020			
FINISH = 12			
ALL DIMENSIONS IN INCHES			
ALL DIM (XX) ARE MILLIMETERS			
REMOVE ALL BURRS AND			
SHARP EDGES			
DIAGONAL DIMENSIONS			
PROCESS			
0.015 THRU .125 = +.004 - .001			
.125 THRU .250 = +.003 - .001			
.251 THRU .500 = +.005 - .001			
.501 THRU .750 = +.006 - .001			
.751 THRU 1.000 = +.007 - .001			
1.001 THRU 2.000 = +.012 - .001			
HOLE TOLERANCES			
0.015 THRU .125 = +.004 - .001			
.125 THRU .250 = +.003 - .001			
.251 THRU .500 = +.005 - .001			
.501 THRU .750 = +.006 - .001			
.751 THRU 1.000 = +.007 - .001			
1.001 THRU 2.000 = +.012 - .001			
SIZE	COD NO	DWG NO	REV
C		48QN50T17070	-
TITLE			SH
OFFN SOCKET:			
7 X 7mm, 0.50mm-PITCH;			
48 PINS PLUS CENTER GROUND PIN;			
THRU-HOLE			
PLASTRONICS			
2601 TEXAS DRIVE			
IRVING, TX 75062			