

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION




19

© COPYRIGHT 19

BY AMP INCORPORATED. ALL RIGHTS RESERVED.


LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
CM	53		B	REACT & REDWN PER EC 0730-0171-96	6-25-96	BL	RS

1. WIRE RANGE: 20-14 (0.5-2mm²) AWG
INSULATION RANGE: .125 MAX.



.050	1.27	.139	3.53	.180	4.57		
.043	1.09	.135	3.43	.165	4.19		
.035	0.89	.130	3.30	.157	3.99		
.018	0.46	.125	3.18	.156	3.96	.935	23.75
.015	0.38	.115	2.92	.155	3.94	.915	23.24
.005	0.13	.063	1.60	.154	3.91	.189	4.80
IN	MM	IN	MM	IN	MM	IN	MM

CONVERSION TABLE



TIN	.018 BRASS	61251-1
FINISH	MATERIAL	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN B. LEWIS 6-25-96	AMP AMP Incorporated Harrisburg, PA 17105-3608		
		CHK R. SWING 6-25-96			
DIMENSIONS: INCHES		APVD C. MARTIN 6-25-96	NAME PIN, LOOSE PIECE, .156 MATE-N-LOK™		
		PRODUCT SPEC			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPLY SPEC	SIZE A2		
		—			
MATERIAL BRASS		WEIGHT —	CAGE CODE 00779		
		FINISH PRE-TIN			
		CUSTOMER DRAWING	DRAWING NO C-61251		
			SCALE 5:1	SHEET 1 OF 1	REV B