

**Long-life grade capacitors
for professional electronic ballasts****Applications**

- Electronic ballasts
- Power supplies
- High-temperature environments
- Energy-saving lamps

Features

- Miniaturized dimensions
- High ripple current capability
- Wide temperature range

Construction


- Radial leads
- Charge-discharge proof, polar
- Aluminum case with insulating sleeve
- Minus pole marking on insulating sleeve
- Case with safety vent
- Stand off rubber seal

Delivery mode


Special terminal configurations and packing:

- Bulk
- Taped, Ammo pack
- Cut
- Kinked

Refer to page 503 for further details and ordering example.




KAL0707-F



Specifications and characteristics in brief


Rated voltage U_R	160 ... 350 VDC	
Surge voltage U_S	$1,1 \cdot U_R$	
Rated capacitance C_R	3,3 ... 100 μ F	
Capacitance tolerance	$\pm 20 \% \triangleq M$	
Useful life 140 °C; U_R ; I_{-R}	> 1 000 h	Requirements: $\Delta C/C \leq \pm 35 \%$ of initial value $ESR \leq 3$ times initial specified limit $I_L \leq$ initial specified limit Failure percentage: $\leq 1 \%$ Failure rate: ≤ 100 fit ($\leq 100 \cdot 10^{-9}/h$) (for definition "fit", refer to chapter "Quality", page 62)
Voltage endurance test 140 °C; U_R	1 000 h	Post test requirements: $\Delta C/C \leq \pm 30 \%$ of initial value $\tan \delta \leq 2$ times initial specified limit $I_L \leq$ initial specified limit
IEC climatic category	To IEC 60068-1 $U_R \leq 250$ V: 40/140/56 (– 40 °C/+ 140 °C/56 days damp heat test) $U_R = 350$ V: 25/140/56 (– 25 °C/+ 140 °C/56 days damp heat test)	
Sectional specification	IEC 60384-4	
Vibration resistance	To IEC 60068-2-6, test Fc: displacement amplitude 0,75 mm, frequency range 10 ... 2000 Hz, acceleration max. 10 g, duration 3×2 h	



B43867

140 °C

Dimensional drawing



Dimensions and weights

Dimensions (mm)				Approx. weight g
$d \times l$	$d_{\max} \times l_{\max}$	$a \pm 0,5$	b	
10 × 20	10,5 × 22	5,0	$0,60 \pm 0,05$	2,6
12,5 × 20	13 × 22	5,0	$0,60 \pm 0,05$	3,6
12,5 × 25	13 × 27	5,0	$0,60 \pm 0,05$	4,5
16 × 20	16,5 × 22	7,5	$0,80 \pm 0,05$	5,5
16 × 25	16,5 × 27	7,5	$0,80 \pm 0,05$	7,5
16 × 31,5	16,5 × 33,5	7,5	$0,80 \pm 0,05$	7,8

Overview of available types

U_R (VDC)	160	200	250	350
C_R (μF)	Case dimensions $d \times l$ (mm)			
3,3				10 × 20
3,9				10 × 20
4,7				10 × 20
6,8				12,5 × 20
10		10 × 20	10 × 20	12,5 × 25
15		10 × 20	12,5 × 20	
22	10 × 20	12,5 × 20	12,5 × 25	16 × 25
33	12,5 × 20	12,5 × 25	12,5 × 25	16 × 31,5
47	12,5 × 25	12,5 × 25	16 × 31,5	
68	16 × 20	16 × 25		
100	16 × 25	16 × 31,5		
220				


Other voltage and capacitance ratings are also available upon request.



Technical data and ordering codes

U_R	C_R 120 Hz 20 °C μF	Case dimensions $d \times l$ mm	I_L 5 min 20 °C μA	$\tan \delta_{max}$ 120 Hz 20 °C	ESR_{max} 120 Hz 20 °C Ω	$I_{\sim R}$ 120 Hz 140 °C mA	Ordering code ¹⁾
VDC							
160	22	10 × 20,0	95	0,20	15,1	145	B43867A1226M00*
	33	12,5 × 20,0	130	0,20	10,0	200	B43867A1336M00*
	47	12,5 × 25,0	175	0,20	7,1	270	B43867A1476M00*
	68	16 × 20,0	242	0,20	4,9	345	B43867A1686M00*
	100	16 × 25,0	345	0,20	3,3	450	B43867A1107M00*
200	10	10 × 20,0	65	0,20	33,2	90	B43867A2106M00*
	15	10 × 20,0	85	0,20	22,1	120	B43867A2156M00*
	22	12,5 × 20,0	113	0,20	15,1	170	B43867A2226M00*
	33	12,5 × 25,0	157	0,20	10,0	225	B43867A2336M00*
	47	12,5 × 25,0	213	0,20	7,1	270	B43867A2476M00*
	68	16 × 25,0	297	0,20	4,9	370	B43867A2686M00*
	100	16 × 31,5	425	0,20	3,3	495	B43867A2107M00*
250	10	10 × 20,0	75	0,20	33,2	95	B43867F2106M00*
	15	12,5 × 20,0	100	0,20	22,1	120	B43867F2156M00*
	22	12,5 × 25,0	135	0,20	15,1	185	B43867F2226M00*
	33	12,5 × 25,0	190	0,20	10,0	225	B43867F2336M00*
	47	16 × 31,5	260	0,20	7,1	330	B43867F2476M00*
350	3,3	10 × 20,0	48	0,25	125,6	55	B43867A4335M00*
	3,9	10 × 20,0	52	0,25	106,3	65	B43867A4395M00*
	4,7	10 × 20,0	57	0,25	88,2	75	B43867A4475M00*
	6,8	12,5 × 20,0	72	0,25	61,0	90	B43867A4685M00*
	10	12,5 × 25,0	95	0,25	41,4	122	B43867A4106M00*
	22	16 × 25,0	179	0,25	18,8	210	B43867A4226M00*
	33	16 × 31,5	256	0,25	12,6	280	B43867A4336M00*

1) * = "0" for bulk version. For taping versions, other lead configurations and packing information see page 503.




B43867

140 °C


Useful life

depending on ambient temperature T_A under ripple current operating conditions¹⁾

$U_R = 160 \dots 350 \text{ VDC}$




Frequency factor of permissible ripple current $I_{\sim}$ versus frequency f




Equivalent series resistance ESR

versus temperature T
Typical behavior at 120 Hz




1) Refer to page 40 for an explanation on how to interpret the useful life graphs.



Impedance Z

versus frequency f

Typical behavior at 20 °C



Herausgegeben von EPCOS AG**Unternehmenskommunikation, Postfach 80 17 09, 81617 München, DEUTSCHLAND****☎ ++49 89 636 09, FAX (0 89) 636-2 26 89**

© EPCOS AG 2002. Vervielfältigung, Veröffentlichung, Verbreitung und Verwertung dieser Broschüre und ihres Inhalts ohne ausdrückliche Genehmigung der EPCOS AG nicht gestattet.

Bestellungen unterliegen den vom ZVEI empfohlenen Allgemeinen Lieferbedingungen für Erzeugnisse und Leistungen der Elektroindustrie, soweit nichts anderes vereinbart wird.

Diese Broschüre ersetzt die vorige Ausgabe.

Fragen über Technik, Preise und Liefermöglichkeiten richten Sie bitte an den Ihnen nächstgelegenen Vertrieb der EPCOS AG oder an unsere Vertriebsgesellschaften im Ausland. Bauelemente können aufgrund technischer Erfordernisse Gefahrstoffe enthalten. Auskünfte darüber bitten wir unter Angabe des betreffenden Typs ebenfalls über die zuständige Vertriebsgesellschaft einzuholen.

Published by EPCOS AG**Corporate Communications, P.O. Box 80 17 09, 81617 Munich, GERMANY****☎ ++49 89 636 09, FAX (0 89) 636-2 26 89**

© EPCOS AG 2002. Reproduction, publication and dissemination of this brochure and the information contained therein without EPCOS' prior express consent is prohibited.

Purchase orders are subject to the General Conditions for the Supply of Products and Services of the Electrical and Electronics Industry recommended by the ZVEI (German Electrical and Electronic Manufacturers' Association), unless otherwise agreed.

This brochure replaces the previous edition.

For questions on technology, prices and delivery please contact the Sales Offices of EPCOS AG or the international Representatives.

Due to technical requirements components may contain dangerous substances. For information on the type in question please also contact one of our Sales Offices.