

10

9

8

7

6


5

4



3

2



38710



REF. -50 OPT. SCREW
(WHERE APPLICABLE)



4 CIRCUIT SHOWN



NOTES:

1. MATERIAL: SEE TABLE
2. FINISH: SEE TABLE
3. INCH DIMS ARE SHOWN IN BRACKETS [XXX].
4. "XX" REFERS TO THE NUMBER OF CIRCUITS.
5. ALL COMPONENTS ARE ROHS COMPLIANT.

5	XX	SCREW&WASHER, #6-32X.250, PAN, PH/SL (-50 OPT)	STEEL	ZN, CLEAR CHROMATE
4	XX	SCREW, #6-32X.250, BHD, PH/SL (-49 OPT)	BRASS	NICKEL PLATE
3	XX	SCREW, #6-32X.250, BHD, PH/SL (STD)	STEEL	ZN, CLEAR CHROMATE
2	XX	TERMINAL, PC, #6-32	BRASS	TIN PLATE
1	1	INSULATOR, SR, NO MTG.	30% G.F. PBT	BLACK

ITEM QTY. DESCRIPTION

MATERIAL FINISH

INITIAL RELEASE
EC NO: ETC2006-0520
DRAWN BY: C. YORK 2006/07/12
CHKD BY: R. DEROSS 2006/07/13
APPR. BY: R. DEROSS 2006/07/13

DESCRIPTION
A

QUALITY SYMBOLS
▽=0
▽=0

GENERAL TOLERANCES (UNLESS SPECIFIED)

	mm	INCH
4 PLACES	± ---	± ---
3 PLACES	± ---	± .005
2 PLACES	± 0.13	± .01
1 PLACE	± 0.25	± ---
ANGULAR ± 2 °		

DRAFT WHERE APPLICABLE
MUST REMAIN
WITHIN DIMENSIONS

DIMENSION STYLE

MM/IN	DATE
DRAWN BY	C. YORK 2006/06/30
CHECKED BY	R. DEROSS 2006/06/30
APPROVED BY	R. DEROSS 2006/06/30
MATERIAL NO.	SEE SHEET 2

SCALE

2:1

DESIGN UNITS

INCH

THIRD ANGLE PROJECTION

9.53MM [0.375] SR BTS
ASSY, PC TERM. WITHOUT
MTG. ENDS, LOW PROJ.

MOLEX INCORPORATED

DOCUMENT NO.
SD-38710-005

SHEET NO.
1 OF 2

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

ib_frame_B.P_ME_T
Rev. D 2004/04/02

9

8

7

6

5

4

3

2

1

