

LAMINATED TRANSFORMERS

Type UI30 / 10.5 - 6VA



Primary (V)	Secondary (V / mA)	No-Load Voltage (V)	Part Number	Agency Approvals
2x115	6/500 / 6/500	8.50/8.50	030-7004.0	1/3*
2x115	9/333 / 9/333	12.70/12.70	030-7007.0	1/3*
2x115	12/250 / 12/250	16.30/16.30	030-7010.0	1/3*
2x115	15/200 / 15/200	20.30/20.30	030-7013.0	1/3*
2x115	18/166 / 18/166	24.30/24.30	030-7016.0	1/3*
2x115	21/142 / 21/142	28.30/28.30	030-7019.0	1

Frequency 50/60Hz

Potted under vacuum

Split-bobbin

Temperature class ta 40°C/B


Weight: 0.175kg

Packaging unit: 15 pieces (tray)

Fixing material for □ 2,5mm (0.098 inch)

- Self-tapping screws: DIN 7513 (M 3x8)
- Sheet-metal screws: DIN 7971 (2,9x6,5)

Mechanical



Schematics

