

# HUBER+SUHNER® DATA SHEET

## Coaxial Cable Connector: 11\_N-50-3-5/133\_N

Rev.: B



### Description

Straight cable plug

### Interface Standards

IEC 61169-16\_MIL-STD-348A/304\_CECC 22210



### Technical Data

#### Electrical Data

Impedance	50 Ω
Interface frequency max.	11 GHz

#### Mechanical Data

Centre contact	soldered
Outer contact	clamped
Weight	0.0365 kg

#### Environmental Data

Operating Temperature	-65 °C to 165 °C
2002/95/EC (RoHS)	compliant

#### Material Data

Piece Parts	Material	Surface Plating
Centre contact	Brass	Gold Plating (Nickel underplated)
Outer contact	Brass	SUCOPLADE (R) Plating
Body	Brass	SUCOPLADE (R) Plating
Insulator	PFA / PTFE	
Coupling nut	Brass	SUCOPLADE (R) Plating
Gasket	MVQ (Silicone Rubber)	

#### Related Documents

Outline drawing	DOU-00008106
Catalogue drawing	DOU-00006125
Assembly instruction	DOC-0000177464

#### Ordering Information

Bulk 100 pcs package	11_N-50-3-5/133_NH
Single package	11_N-50-3-5/133_NE

#### Additional Information

Suitable cables	RG_223 /U, ENVIROFLEX_142, RG_142_B/U, RG 400 /U
-----------------	--

HUBER+SUHNER is certified according to ISO 9001 and ISO 14001

#### WAIVER!

It is exclusively in written agreements that we provide our customers with warrants and representations as to the technical contained specifications and/or the fitness for any particular purpose. The facts and figures herein are carefully compiled to the best of our knowledge, but they are intended for general informational purposes only.



HUBER+SUHNER AG

RF Technology

9100 Herisau, Switzerland

Phone +41 (0)71 353 41 11

Fax +41 (0)71 353 45 90

[www.hubersuhner.com](http://www.hubersuhner.com)

**HUBER+SUHNER – Excellence in Connectivity Solutions**