1. Scope

The present specifications shall apply to an EU02Z.

2. Outline

| | |
|---|---|
| Type | Silicon Diode |
| Structure | Resin Molded |
| Applications | High Frequency Rectification |

3. Flammability

UL94V-0(Equivalent)

4. Absolute maximum ratings

| No. | Item | Symbol | Unit | Rating | Conditions |
|---|---|---|---|---|---|
| 1 | Transient Peak Reverse Voltage | $V_{RSM}$ | V | 250 | |
| 2 | Peak Reverse Voltage | $V_{RM}$ | V | 200 | |
| 3 | Average Forward Current | $I_{F(AV)}$ | A | 1.0 | Refer to Derating of 7 |
| 4 | Peak Surge Forward Current | $I_{FSM}$ | A | 15 | 10msec.<br>Half sinewave, one shot |
| 5 | $I^2t$ Limiting Value | $I^2t$ | $A^2s$ | 1.13 | 1msec≤t≤10msec |
| 6 | Junction Temperature | $T_j$ | °C | -40~+150 | |
| 7 | Storage Temperature | $T_{stg}$ | °C | -40~+150 | |

5. Electrical characteristics (Ta=25°C ， unless otherwise specified)

| No. | Item | Symbol | Unit | Value | Conditions |
|---|---|---|---|---|---|
| 1 | Forward Voltage Drop | $V_F$ | V | 1.4 max. | $I_F$=1.0A |
| 2 | Reverse Leakage Current | $I_R$ | uA | 10 max. | $V_R=V_{RM}$ |
| 3 | Reverse Leakage Current Under High Temperature | $H \cdot I_R$ | uA | 300 max. | $V_R=V_{RM}$, $T_j$=100℃ |
| 4 | Reverse Recovery Time | trr-1 | ns | 400 max. | $I_F=I_{RP}$=10mA<br>90% Recovery point, $T_j$=25°C |
| | | trr-2 | ns | 180 max. | $I_F$=10mA, $I_{RP}$=20mA<br>75% Recovery point, $T_j$=25°C |
| 5 | Thermal Resistance | $R_{th(j-l)}$ | °C /W | 20 max. | Between Junction and Lead |

6. Characteristics

$I_{F(AV)}$ - $P_F$




$V_R$ - $P_R$



7. Derating


$T_l$ - $I_{F(AV)}$
$V_R$=200(V)
1.0
0.8
0.6
0.4
0.2
0.0
t/T=1/6
t/T=1/3
t/T=1/2
DC
sinewave
Tj=150°C
t
T
50
100
150
$I_{F(AV)}$ (A)
Average Forward Current (A)
$T_l$ (°C)
Lead Temperature (°C)

8. Package information

8-1 Package type, physical dimensions and material




*1 The allowance position of Body against the center of whole lead wire is 0.5mm(max.)
*2 The centric allowance of lead wire against center of physical body is 0.2mm(max.)
*3 The burr may exit up to 2mm from the body of lead

Dimensions in mm

8-2 Appearance

The body shall be clean and shall not bear any stain, rust or flaw.

8-3 Marking




① Type number : EU02Z is abbreviated as $\overset{U0}{2Z}$

② Lot number 1
First digit: Last digit of Year
Second digit: Month
From 1 to 9 for Jan. to Sep.
O for Oct., N for Nov., and D for Dec.

③ Lot number 2 (ten days)
・ : Top of the month
・・ : Middle of month
・・・ : End of month