## Standard Frequency MEMS (VC)TCXO



### **Features**

- 27 standard frequencies between 10 MHz and 40 MHz
- 100% pin-to-pin drop-in replacement to quartz-based (VC)TCXO
- Frequency stability as low as ±5 ppm. Contact SiTime for tighter stability options
- Low phase jitter: 0.5 ps (12 kHz to 20 MHz)
- LVCMOS compatible output with SoftEdge™ option for EMI reduction
- Voltage control, standby, output enable or no connect modes
- Standard 4-pin packages: 2.5 x 2.0, 3.2 x 2.5, 5.0 x 3.2, 7.0 x 5.0 mm
- Outstanding silicon reliability of 2 FIT, 10 times better than quartz
- Pb-free, RoHs and REACH compliant

### **Applications**

- WiFi, 3G, LTE, SDI, Ethernet, SONET, DSL
- Telecom, networking, smart meter, wireless, test instrumentation







### **Electrical Characteristics**

Parameter	Symbol	Min.	Тур.	Max.	Unit	Condition
Output Frequency Range	f	Refer to the	frequency l	ist (page 6)	MHz	27 standard frequencies between 10 MHz and 40 MHz
Initial Tolerance	F_init	-1.5	-	+1.5	ppm	At 25°C after two reflows
Stability Over Temperature	F_stab	-5	-	+5	ppm	Over operating temperature range at rated nominal power supply voltage and load. (see ordering codes on page 6)
						Contact SiTime for tighter stability options.
Supply Voltage	F_vdd	_	50	_	ppb	±10% Vdd (±5% for Vdd = 1.8V)
Output Load	F_load	-	0.1	-	ppm	15 pF ±10% of load
First year Aging	F_aging	-2.5	-	+2.5	ppm	25°C
10-year Aging		-4.0	-	+4.0	ppm	25°C
Operating Temperature Range	T_use	-20	-	+70	°C	Extended Commercial
		-40	-	+85	°C	Industrial
Supply Voltage	Vdd	1.71	1.8	1.89	V	Contact SiTime for any other supply voltage options.
		2.25	2.5	2.75	V	
		2.52	2.8	3.08	V	
		2.70	3.0	3.3	V	
		2.97	3.3	3.63	V	
Pull Range	PR		±12.5		ppm	
Upper Control Voltage	VC_U	Vdd-0.1	-	_	V	All Vdds. Voltage at which maximum deviation is guaranteed.
Control Voltage Range	VC_L	-	_	0.1	V	
Control Voltage Input Impedance	Z_vc	100	-	_	kΩ	
Frequency Change Polarity	ı	F	Positive slop	е	-	
Control Voltage -3dB Bandwidth	V_BW	-	-	8	kHz	
Current Consumption	ldd	-	31	33	mA	No load condition, f = 20 MHz, Vdd = 2.5V, 2.8V or 3.3V.
		-	29	31	mA	No load condition, f = 20 MHz, Vdd = 1.8V.
OE Disable Current	I_OD	_	-	31	mA	Vdd = 2.5V, 2.8V or 3.3V, OE = GND, output is Weakly Pulled Down
		-	-	30	mA	Vdd = 1.8 V. OE = GND, output is Weakly Pulled Down
Standby Current	I_std	-	-	70	μΑ	Vdd = 2.5V, 2.8V or 3.3V, $\overline{\text{ST}}$ = GND, output is Weakly Pulled Down.
		-	-	10	μΑ	Vdd = 1.8V. ST = GND, output is Weakly Pulled Down.
Duty Cycle	DC	45	-	55	%	All Vdds
LVCMOS Rise/Fall Time	Tr, Tf	_	1.5	2	ns	LVCMOS option. Default rise/fall time, All Vdds, 10% - 90% Vdd.
SoftEdge™ Rise/Fall Time		SoftEdge <sup>1</sup>	™ Rise/Fall	Time Table	ns	SoftEdge™ option. Frequency and supply voltage dependent.
Output Voltage High	VOH	90%	_	_	Vdd	OH = -7 mA, IOL = 7 mA, (Vdd = 3.3V, 3.0V)
Output Voltage Low	VOL	-	-	10%	Vdd	IOH = -4 mA, IOL = 4 mA, (Vdd = 2.8V, 2.5V) IOH = -2 mA, IOL = 2 mA, (Vdd = 1.8V)
Input Voltage High	VIH	70%	-	-	Vdd	Pin 1, OE or ST
Input Voltage Low	VIL	-	-	30%	Vdd	Pin 1, OE or ST
Input Pull-up Impedance	Z_in	-	100	250	kΩ	

SiTime Corporation 990 Almanor Avenue Sunnyvale, CA 94085 (408) 328-4400 www.sitime.com

Rev. 1.0 Revised November 12, 2015

### Standard Frequency MEMS (VC)TCXO




### **Electrical Characteristics (continued)**

Parameter	Symbol	Min.	Тур.	Max.	Unit	Condition		
Startup Time	T_start	-	-	10	ms	Measured from the time Vdd reaches its rated minimum value		
OE Enable/Disable Time	T_oe	-	_	150	ns	f = 80 MHz. For other frequencies, T_oe = 100 ns + 3 cycle		
Resume Time	T_resume	-	6	10	ms	Measured from the time ST pin crosses 50% threshold		
RMS Period Jitter	T_jitt	-	1.7	2	ps	f = 10 MHz, Vdd = 2.5V, 2.8V or 3.3V		
		-	1.7	2	ps	f = 10 MHz, Vdd = 1.8V		
RMS Phase Jitter (random)	T_phj	-	0.5	1	ps	f = 10 MHz, Integration bandwidth = 12 kHz to 20 MHz, All Vdds		

#### Note

### **Pin Configuration**

Pin	Symbol	Functionality				
		V control	Voltage control			
	1 VC/OE/ST/NC Standby  NC		H or Open <sup>[2]</sup> : specified frequency output L: output is high impedance. Only output driver is disabled.			
1			H or Open <sup>[2]</sup> : specified frequency output L: output is low (weak pull down). Device goes to sleep mode. Supply current reduces to I_std.			
			No connect (input receiver off)			
2	GND	Power	Electrical and case ground			
3	CLK	Output	Oscillator output			
4	VDD	Power	Power supply voltage			



#### Note:

### **Absolute Maximum**

Attempted operation outside the absolute maximum ratings of the part may cause permanent damage to the part. Actual performance of the IC is only guaranteed within the operational specifications, not at absolute maximum ratings.

Parameter	Min.	Max.	Unit
Storage Temperature	-65	150	°C
VDD	-0.5	4	V
Electrostatic Discharge	_	2000	V
Soldering Temperature (follow standard Pb free soldering guidelines)	-	260	°C

### **Thermal Consideration**

Package	θJA, 4 Layer Board (°C/W)	θJA, 2 Layer Board (°C/W)	θJC, Bottom (°C/W)
7050	191	263	27
5032	97	199	24
3225	109	212	27
2520	117	222	26

### **Environmental Compliance**

Parameter	Condition/Test Method
Mechanical Shock	MIL-STD-883F, Method 2002
Mechanical Vibration	MIL-STD-883F, Method 2007
Temperature Cycle	JESD22, Method A104
Solderability	MIL-STD-883F, Method 2003
Moisture Sensitivity Level	MSL1 @ 260°C


<sup>1.</sup> All electrical specifications in the above table are measured with 15pF output load, Contact SiTime for higher drive options.

<sup>2.</sup> A pull-up resistor of <10 k? between OE/ST pin and Vdd is recommended in high noise environment when the device operates in OE/ST mode.


# Standard Frequency MEMS (VC)TCXO



### **Timing Diagram**



### **Phase Noise Plot**



### Standard Frequency MEMS (VC)TCXO



### SoftEdge™ Option

The SoftEdge™ output is available as a standard option for the SiT500x family of MEMS (VC)TCXOs. It is typically used for EMI reduction similar to that of the clipped sinewave output common to many quartz based TCXOs.


In the SoftEdge<sup>TM</sup> mode, the slower rise/fall edges of the output waveform reduce the higher clock harmonics in a digital clock signal, minimizing EMI radiation at these harmonics. The table below show the actual rise/fall time in relation to the desired output frequency and the supply voltage with a 10 k $\Omega$  / 10 pF load. Rail-to-rail swing of the output is maintained for these supported frequencies.


### Rise/Fall Time for SoftEdge™ Option


Parameter	Symbol	Min.	Тур.	Max.	Unit	Condition		
Rise/Fall Time	Tr, Tf	4.0	6.5	9.5	ns	1-26 MHz, 1.8V, 3.0 and 3.3V, MHz 10k and 10 pF, 20%-80% V		
		2.5	4.0	6.0	ns	1-26 MHz, 2.5V and 2.8V, MHz 10k and 10 pF, 20%-80% Vdd		
		1.5	3.5	5.0	ns	26-40 MHz, 1.8V, 3.0V and 3.3V, MHz 10k and 10 pF, 20%-80% Vdd		
		1.5	2.5	4.5	ns	26-40 MHz, 2.5V and 2.8V, MHz 10k and 10 pF, 20%-80% Vdd		


### SoftEdge™ Waveform Examples and Corresponding Harmonics Reduction


Figures below illustrate the harmonic power reduction as the rise/fall times are slowed from the standard squarewave output to that of the SoftEdge™ output. In general, the 1.8V device shows the lowest harmonics and provides best EMI performance comparing to devices with higher operating voltages.















# Standard Frequency MEMS (VC)TCXO



### **Dimensions and Patterns**



#### Notes


- 3. Top marking: Y denotes manufacturing origin and XXXX denotes manufacturing lot number. The value of "Y" will depend on the assembly location of the device.
- 4. A capacitor of value 0.1  $\mu\text{F}$  between Vdd and GND is recommended.

### Standard Frequency MEMS (VC)TCXO



### **Ordering Information**

The Part No. Guide is for reference only. To customize and build an exact part number, use the SiTime Part Number Generator.



#### Notes:

- 5. SiTime's SoftEdge™ output waveform with 6 ns rise/fall time reduces EMI and is similar to clipped sine wave in functionality.
- 6. Contact SiTime for tighter stability options.

### **Supported Frequencies**

10 MHz	12 MHz	12.288 MHz	12.8 MHz	13 MHz	14 MHz	14.4 MHz	14.7456 MHz	16 MHz
16.357 MHz	16.3676 MHz	16.367667 MHz	16.368 MHz	16.369 MHz	16.8 MHz	19.2 MHz	19.44 MHz	19.68 MHz
20 MHz	20.8 MHz	24 MHz	25 MHz	26 MHz	27.456 MHz	33.6 MHz	38.4 MHz	40 MHz

### Standard Frequency MEMS (VC)TCXO



#### **Additional Information**

Document	Description	Download Link
Manufacturing Notes	Tape & Reel dimension, reflow profile and other manufacturing related info	http://www.sitime.com/component/docman/doc_download/85-manufacturing-notes-for-sitime-oscillators
Qualification Reports	RoHS report, reliability reports, composition reports	http://www.sitime.com/support/quality-and-reliability
Performance Reports	Additional performance data such as phase noise, current consumption and jitter for selected frequencies	http://www.sitime.com/support/performance-measurement-report
Termination Techniques	Termination design recommendations	http://www.sitime.com/support/application-notes
Layout Techniques	Layout recommendations	http://www.sitime.com/support/application-notes

### **Revision History**

Version	Release Date	Change Summary
1.0	11/12/15	Final production release  Revised initial tolerance, stability over temperature and first/10 year aging values in the electrical characteristics table  Revised frequency stability option

© SiTime Corporation 2015. The information contained herein is subject to change at any time without notice. SiTime assumes no responsibility or liability for any loss, damage or defect of a Product which is caused in whole or in part by (i) use of any circuitry other than circuitry embodied in a SiTime product, (ii) misuse or abuse including static discharge, neglect or accident, (iii) unauthorized modification or repairs which have been soldered or altered during assembly and are not capable of being tested by SiTime under its normal test conditions, or (iv) improper installation, storage, handling, warehousing or transportation, or (v) being subjected to unusual physical, thermal, or electrical stress.

Disclaimer: SiTime makes no warranty of any kind, express or implied, with regard to this material, and specifically disclaims any and all express or implied warranties, either in fact or by operation of law, statutory or otherwise, including the implied warranties of merchantability and fitness for use or a particular purpose, and any implied warranty arising from course of dealing or usage of trade, as well as any common-law duties relating to accuracy or lack of negligence, with respect to this material, any SiTime product and any product documentation. Products sold by SiTime are not suitable or intended to be used in a life support application or component, to operate nuclear facilities, or in other mission critical applications where human life may be involved or at stake. All sales are made conditioned upon compliance with the critical uses policy set forth below.

#### CRITICAL USE EXCLUSION POLICY

BUYER AGREES NOT TO USE SITIME'S PRODUCTS FOR ANY APPLICATION OR IN ANY COMPONENTS USED IN LIFE SUPPORT DEVICES OR TO OPERATE NUCLEAR FACILITIES OR FOR USE IN OTHER MISSION-CRITICAL APPLICATIONS OR COMPONENTS WHERE HUMAN LIFE OR PROPERTY MAY BE AT STAKE.

SiTime owns all rights, title and interest to the intellectual property related to SiTime's products, including any software, firmware, copyright, patent, or trademark. The sale of SiTime products does not convey or imply any license under patent or other rights. SiTime retains the copyright and trademark rights in all documents, catalogs and plans supplied pursuant to or ancillary to the sale of products or services by SiTime. Unless otherwise agreed to in writing by SiTime, any reproduction, modification, translation, compilation, or representation of this material shall be strictly prohibited.



# **Supplemental Information**

The Supplemental Information section is not part of the datasheet and is for informational purposes only.



# Silicon MEMS Outperforms Quartz

### Silicon MEMS Outperforms Quartz



#### **Best Reliability**

Silicon is inherently more reliable than quartz. Unlike quartz suppliers, SiTime has in-house MEMS and analog CMOS expertise, which allows SiTime to develop the most reliable products. Figure 1 shows a comparison with quartz technology.

#### Why is SiTime Best in Class:

- SiTime's MEMS resonators are vacuum sealed using an advanced EpiSeal<sup>™</sup> process, which eliminates foreign particles and improves long term aging and reliability
- · World-class MEMS and CMOS design expertise




Figure 1. Reliability Comparison<sup>[1]</sup>

#### **Best Aging**

Unlike quartz, MEMS oscillators have excellent long term aging performance which is why every new SiTime product specifies 10-year aging. A comparison is shown in Figure 2.

#### Why is SiTime Best in Class:

- SiTime's MEMS resonators are vacuum sealed using an advanced EpiSeal process, which eliminates foreign particles and improves long term aging and reliability
- Inherently better immunity of electrostatically driven MEMS resonator




Figure 2. Aging Comparison<sup>[2]</sup>

#### Best Electro Magnetic Susceptibility (EMS)

SiTime's oscillators in plastic packages are up to 54 times more immune to external electromagnetic fields than quartz oscillators as shown in Figure 3.

#### Why is SiTime Best in Class:

- Internal differential architecture for best common mode noise rejection
- Electrostatically driven MEMS resonator is more immune to EMS




Figure 3. Electro Magnetic Susceptibility (EMS)[3]

#### **Best Power Supply Noise Rejection**

SiTime's MEMS oscillators are more resilient against noise on the power supply. A comparison is shown in Figure 4.

#### Why is SiTime Best in Class:

- On-chip regulators and internal differential architecture for common mode noise rejection
- · Best analog CMOS design expertise




Figure 4. Power Supply Noise Rejection<sup>[4]</sup>

### Silicon MEMS Outperforms Quartz



#### **Best Vibration Robustness**

High-vibration environments are all around us. All electronics, from handheld devices to enterprise servers and storage systems are subject to vibration. Figure 5 shows a comparison of vibration robustness.

#### Why is SiTime Best in Class:

- The moving mass of SiTime's MEMS resonators is up to 3000 times smaller than guartz
- Center-anchored MEMS resonator is the most robust design




Figure 5. Vibration Robustness<sup>[5]</sup>

#### Notes:

- 1. Data Source: Reliability documents of named companies.
- 2. Data source: SiTime and quartz oscillator devices datasheets.
- 3. Test conditions for Electro Magnetic Susceptibility (EMS):
  - According to IEC EN61000-4.3 (Electromagnetic compatibility standard)
  - Field strength: 3V/m
  - Radiated signal modulation: AM 1 kHz at 80% depth
  - Carrier frequency scan: 80 MHz 1 GHz in 1% steps
  - · Antenna polarization: Vertical
  - DUT position: Center aligned to antenna

#### Devices used in this test:

SiTime, SiT9120AC-1D2-33E156.250000 - MEMS based - 156.25 MHz

Epson, EG-2102CA 156.2500M-PHPAL3 - SAW based - 156.25 MHz

TXC, BB-156.250MBE-T - 3rd Overtone quartz based - 156.25 MHz

Kyocera, KC7050T156.250P30E00 - SAW based - 156.25 MHz

Connor Winfield (CW), P123-156.25M - 3rd overtone quartz based - 156.25 MHz

SiLabs, Si590AB-BDG - 3rd overtone quartz based - 156.25 MHz

4. 50 mV pk-pk Sinusoidal voltage.

#### Devices used in this test:

SiTime, SiT8208AI-33-33E-25.000000, MEMS based - 25 MHz

NDK, NZ2523SB-25.6M - quartz based - 25.6 MHz

Kyocera, KC2016B25M0C1GE00 - quartz based - 25 MHz

Epson, SG-310SCF-25M0-MB3 - quartz based - 25 MHz

- 5. Devices used in this test: same as EMS test stated in Note 3.
- 6. Test conditions for shock test:
  - MIL-STD-883F Method 2002
  - Condition A: half sine wave shock pulse, 500-g, 1ms
  - $\bullet$  Continuous frequency measurement in 100  $\mu s$  gate time for 10 seconds

Devices used in this test: same as EMS test stated in Note 3

7. Additional data, including setup and detailed results, is available upon request to qualified customers. Please contact productsupport@sitime.com.

#### **Best Shock Robustness**

SiTime's oscillators can withstand at least  $50,000\ g$  shock. They all maintain their electrical performance in operation during shock events. A comparison with quartz devices is shown in Figure 6.

#### Why is SiTime Best in Class:

- The moving mass of SiTime's MEMS resonators is up to 3000 times smaller than guartz
- Center-anchored MEMS resonator is the most robust design




Figure 6. Shock Robustness<sup>[6]</sup>

### **Document Feedback Form**



SiTime values your input in improving our documentation. Click <u>here</u> for our online feedback form or fill out and email the form below to <u>productsupport@sitime.com</u>.

1. Does the Electrica	I Characteristics table provide complete info	ormation?	Yes	No	
If No, what paramete	ers are missing?				
2. Is the organization	of this document easy to follow?		Yes	No	
If "No," please sugge	est improvements that we can make:				
3. Is there any applic	ation specific information that you would like	e to see in this o	document? (Ch	eck all that appl	y)
EMI	Termination recommendations	Shock an	d vibration perf	ormance	Other
If "Other," please spe	ecify:				
4. Are there any erro	rs in this document?	Yes	No		
If "Yes", please speci	fy (what and where):				
5. Do you have addit	ional recommendations for this document?				
Title					
Company					
Address					
City / State or Province	ce / Postal Code / Country				
Telephone					
Application					
Would you like a repl	ly? Yes No				

Thank you for your feedback. Please click the email icon in your Adobe Reader tool bar and send to <a href="mailto:productsupport@sitime.com">productsupport@sitime.com</a>. Or you may use our <a href="mailto:online-feedback-form">online-feedback form</a>.

Feedback Form Rev. 1.0 www.sitime.com