

Contact insert - HC-M-HS 200/40-MOD-ST-PE - 1637184

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



HEAVYCON contact insert module, connector, 1-pos., for axial screw connection, 200 A, 25-40 mm², for the PE connection



Key commercial data

Packing unit	1 pc
Weight per Piece (excluding packing)	98.5 GRM
Custom tariff number	85366990
Country of origin	Germany

Technical data

Electrical characteristics

Note	Required for housing HC-B6 to B48, (housing height min. 72 mm), housing HC-ADVANCE-B6 to B24, hinged retaining frame HC-M-MHR..., axial connection for 5 mm Allen wrench
Rated current	200 A
Number of positions	1

Ambient conditions

Ambient temperature (operation)	-40 °C ... 125 °C
---------------------------------	-------------------

Mechanical characteristics

Conductor cross section	25 mm ² ... 40 mm ²
Connection cross section AWG	3 ... 2
Stripping length of the individual wire	16 mm
Tightening torque	8 Nm (25-35 mm ²)
	9 Nm (40 mm ²)
Wire diameter including insulation	12 mm (25 mm ²)
	16 mm (40 mm ²)
Hexagonal socket	WAF 5

Contact insert - HC-M-HS 200/40-MOD-ST-PE - 1637184

Technical data

Mechanical characteristics

Insertion/withdrawal cycles	≥ 500
-----------------------------	-------

General

Series	HC-M-HS
Number of module slots	2
Connection method	Axial screw connection
Inflammability class according to UL 94	V0
Assembly instructions	<ul style="list-style-type: none">- Use only flexible conductors,- Connection of wires with 5 mm an Allen wrench,- Housing height $h \geq 72$ mm,- Connectors may only be operated without load/voltage.
Connection	<p>Note on axial connection technology: Only for stranded wires. The specified conductor cross sections refer to the geometric cross section of the cable used. Use of cables with a geometric cross section that differs greatly from the nominal cross section of the cable should be checked before use. The wiring space for axial screw technology is designed for fine strand cables according to VDE 0295 Class 5. Deviating cable structures (e.g., Class 6 cables) should be checked before use.</p> <p>Assembly instructions Before assembly, ensure that the tapered screw is turned back all the way (chamber is open). The cables must not be twisted. The wires should be inserted as far as they will go into the contact chamber (until the insulation touches the contact). Hold the wires in position and use the socket wrench to tighten. The used wire end should be cut off before connecting again. The connection screw may only be retightened once to prevent the litz wires from breaking. To prevent damage to the contact, the wire/cable should be mechanically intercepted at an appropriate distance from the connection point (e.g., by using a plate cutout). DIN VDE 0100-520:2003-06 contains information on how to do this correctly. The module cannot be used simultaneously with HC-B..-TMB-SD-IP65 and HC-B..-TMS-SD-IP65 protective covers.</p> <p>PE mounting plate The PE plate must be pressed hard against the swing frame using the 4 screws. First loosen the 4 screws of the PE plate and then tighten them again once the module is fixed in the swing frame.</p>

Material data

Contact material	Copper alloy
Contact surface material	Ag
Contact carrier material	PC

Classifications

eCl@ss

eCl@ss 4.0	272607xx
eCl@ss 4.1	27260701

Contact insert - HC-M-HS 200/40-MOD-ST-PE - 1637184

Classifications

eCl@ss

eCl@ss 5.0	27143424
eCl@ss 5.1	27143424
eCl@ss 6.0	27143424
eCl@ss 7.0	27440209
eCl@ss 8.0	27440209

ETIM

ETIM 3.0	EC000438
ETIM 4.0	EC000438
ETIM 5.0	EC000438

UNSPSC

UNSPSC 6.01	30211923
UNSPSC 7.0901	39121522
UNSPSC 11	39121522
UNSPSC 12.01	39121522
UNSPSC 13.2	39121522

Approvals

Approvals

Approvals

UL Recognized / GOST

Ex Approvals

Approvals submitted

Approval details

UL Recognized 	
mm ² /AWG/kcmil	2-0

Contact insert - HC-M-HS 200/40-MOD-ST-PE - 1637184


Approvals

Nominal current IN	200 A
--------------------	-------

GOST 


Drawings

Diagram




Three modules in B24 housing

Diagram




Two modules in B24 housing

Dimensioned drawing



Male insert

Schematic diagram



Axial screw connection