

KA4558/KA4558A


Dual Operational Amplifier

Features



- No frequency compensation required.
- No latch-up.
- Large common mode and differential voltage range.
- Parameter tracking over temperature range.
- Gain and phase match between amplifiers.
- Internally frequency compensated.
- Low noise input transistors.

Descriptions

The KA4558/KA4558A are a monolithic integrated circuit designed for dual operational amplifier.




Internal Block Diagram



Schematic Diagram

(One Section Only)



Absolute Maximum Ratings

Parameter	Symbol	Value	Unit
Supply Voltage	VCC	±22	V
Differential Input Voltage	VI(DIFF)	30	V
Input Voltage	VI	±15	V
Power Dissipation	PD	400	mW
Operating Temperature Range	TOPR	0 ~ 70	°C
Storage Temperature Range	TSTG	-65 ~ 150	°C

Electrical Characteristics

($V_{CC} = 15V$, $V_{EE} = -15V$, $T_A = 25^\circ C$ unless otherwise specified)

Parameter	Symbol	Conditions	KA4558A			KA4558			Unit
			Min	Typ	Max	Min	Typ	Max	
Input Offset Voltage	V_{IO}	$R_S \leq 10K\Omega$	-	1	5	-	2	6	mV
		NOTE 1	-	1	6	-	-	7.5	
Input Offset Current	I_{IO}		-	5	200	-	5	200	nA
		$T_A = T_A(MAX)$	-	3	200	-	-	300	
		$T_A = T_A(MIX)$	-	20	500	-	-	300	
Input Bias Current	I_{BIAS}		-	30	500	-	30	500	nA
		$T_A = T_A(MAX)$	-	20	500	-	-	800	
		$T_A = T_A(MIN)$	-	100	1500	-	-	800	
Large Signal Voltage Gain	G_V	$V_{O(P-P)} = \pm 10V, R_L \leq 2K\Omega$	50	200	-	20	200	-	V/mV
		NOTE 1	25	-	-	-	-	-	
Common Mode Input Voltage Range	$V_{I(R)}$		± 12	± 13	-	± 12	± 13	-	V
		NOTE 1	± 12	± 13	-	-	-	-	
Common Mode Rejection Ratio	CMRR	$R_S \leq 10K\Omega$	70	90	-	70	90	-	dB
		NOTE 1	70	90	-	-	-	-	
Supply Voltage Rejection Ratio	PSRR	$R_S \leq 10K\Omega$	76	90	-	76	90	-	dB
		NOTE 1	76	90	-	76	90	-	
Output Voltage Swing	$V_{O(P,P)}$	$R_L \geq 10K\Omega$	± 12	± 14	-	± 12	± 14	-	V
		$R_L \geq 2K\Omega$	± 10	± 13	-	± 10	± 13	-	
Supply Current (Both Amplifiers)	I_{CC}		-	3.5	5.0	-	3.5	5.8	mA
		$T_A = T_A(MAX)$	-	-	4.5	-	-	5.0	
		$T_A = T_A(MIN)$	-	-	6.0	-	-	6.7	
Power Consumption (Both Amplifiers)	P_C		-	70	150	-	70	170	mW
		$T_A = T_A(MAX)$	-	-	135	-	-	150	
		$T_A = T_A(MIN)$	-	-	180	-	-	200	
Slew Rate	SR	$V_I = 10V, R_L \geq 2K\Omega$ $C_I \leq 100pF$	1.2	-	-	1.2	-	-	V/ μs
Rise Time	T_R	$V_I = 20mV, R_L \geq 2K\Omega$ $C_I \leq 100pF$	-	0.3	-	-	0.3	-	μs
Overshoot	OS	$V_I = 20mV, R_L \geq 2K\Omega$ $C_I \leq 100pF$	-	15	-	-	15	-	%

Note 1

KA4558A : $T_A(MIN) \leq T_A \leq T_A(MAX) = 0 \leq T_A \leq 70^\circ C$

Typical Performance Characteristics




Figure 1. Burst Noise vs Source Resistance




Figure 2. RMS Noise vs Source Resistance




Figure 3. Output Noise vs Source Resistance




Figure 4. Spectral Noise Density




Figure 5. Open Loop Frequency Response




Figure 6. Phase Margin vs Frequency

Typical Performance Characteristics (continued)




Figure 7. Positive Output Voltage Swing vs Load Resistance




Figure 8. Negative Output Voltage Swing vs Load Resistance





Figure 9. Power Bandwidth
(Large Signal Output Swing Versus Frequency)

Mechanical Dimensions

Package


8-DIP



Mechanical Dimensions (Continued)

Package


8-SOP



Mechanical Dimensions (Continued)

Package

9-SIP



Ordering Information

Product Number	Package	Operating Temperature
KA4558	8 DIP	0 ~ + 70°C
KA4558A		
KA4558S	9 SIP	
KA4558AS		
KA4558D	8 SOP	
KA4558AD		

LIFE SUPPORT POLICY

FAIRCHILD'S PRODUCTS ARE NOT AUTHORIZED FOR USE AS CRITICAL COMPONENTS IN LIFE SUPPORT DEVICES OR SYSTEMS WITHOUT THE EXPRESS WRITTEN APPROVAL OF THE PRESIDENT OF FAIRCHILD SEMICONDUCTOR INTERNATIONAL. As used herein:

1. Life support devices or systems are devices or systems which, (a) are intended for surgical implant into the body, or (b) support or sustain life, and (c) whose failure to perform when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in a significant injury of the user.
2. A critical component in any component of a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.