



KTC4373

Features

- Lead Free Finish/RoHS Compliant ("P" Suffix designates RoHS Compliant. See ordering information)
- Low noise
- Halogen free available upon request by adding suffix "-HF"
- Epoxy meets UL 94 V-0 flammability rating
- Moisture Sensitivity Level 1

Maximum Ratings

Symbol	Rating	Rating	Unit
V_{CEO}	Collector-Emitter Voltage	120	V
V_{CBO}	Collector-Base Voltage	120	V
V_{EBO}	Emitter-Base Voltage	5	V
I_C	Collector Current	0.8	A
P_C	Collector power dissipation	0.5	W
T_J	Junction Temperature	150	°C
T_{STG}	Storage Temperature	-55 to +150	°C

Electrical Characteristics @ 25°C Unless Otherwise Specified

Symbol	Parameter	Min	Typ	Max	Units
--------	-----------	-----	-----	-----	-------

OFF CHARACTERISTICS

I_{CBO}	Collector Cutoff Current ($V_{CB} = 120Vdc$)	---	---	100	nAdc
I_{EBO}	Emitter Cutoff Current ($V_{EB} = 5.0Vdc$)	---	---	100	nAdc

ON CHARACTERISTICS



BV_{CBO}	Collector-base breakdown voltage ($I_C = 1mA_{dc}$)	120	---	---	Vdc
BV_{CEO}	Collector-emitter breakdown voltage ($I_C = 10mA_{dc}$)	120	---	---	Vdc
BV_{EBO}	Emitter-base breakdown voltage ($I_E = 1mA_{dc}$)	5	---	---	Vdc
h_{FE}	DC Current Gain ($I_C = 0.1A_{dc}$, $V_{CE} = 5.0Vdc$)	80	---	240	---
$V_{CE(sat)}$	Collector Saturation Voltage ($I_C = 0.5A_{dc}$, $I_B = 50mA_{dc}$)	---	---	1	Vdc
C_{ob}	Output Capacitance ($V_{CE} = 10.0Vdc$, $I_E = 0$, $f = 1.0MHz$)	---	---	30	pF
f_T	Transition frequency ($V_{CE} = 5Vdc$, $I_C = 500mA_{dc}$)	---	120	---	MHz

h_{FE} CLASSIFICATION

Rank	O	Y
Marking	CO	CY
Range	80-160	120-240

NPN Plastic-Encapsulate Transistors







SOT-89



1. BASE
2. COLLECTOR
3. EMITTER

DIMENSINS					
DIM	INCHES		MM		NOTES
	MIN	MAX	MIN	MAX	
A	.173	.181	4.39	4.60	REF.
B	.061	-----	1.55	-----	
C	.154	.165	3.91	4.25	
D	.031	.039	0.80	1.00	
E	.092	.100	2.34	2.54	TYP
F	.118	-----	3.00	-----	
G	.013	.019	0.33	0.48	
H	.015	.021	0.38	0.53	
J	.015	.016	0.38	0.41	
K	.055	.063	1.40	1.60	

Typical Characteristics



Ordering Information :

Device	Packing
Part Number-TP	Tape&Reel; 1Kpcs/Reel

Note : Adding "-HF" suffix for halogen free, eg. Part Number-TP-HF

IMPORTANT NOTICE

Micro Commercial Components Corp. reserves the right to make changes without further notice to any product herein to make corrections, modifications , enhancements , improvements , or other changes . **Micro Commercial Components Corp .** does not assume any liability arising out of the application or use of any product described herein; neither does it convey any license under its patent rights ,nor the rights of others . The user of products in such applications shall assume all risks of such use and will agree to hold **Micro Commercial Components Corp .** and all the companies whose products are represented on our website, harmless against all damages.

LIFE SUPPORT

MCC's products are not authorized for use as critical components in life support devices or systems without the express written approval of Micro Commercial Components Corporation.

CUSTOMER AWARENESS

Counterfeiting of semiconductor parts is a growing problem in the industry. Micro Commercial Components (MCC) is taking strong measures to protect ourselves and our customers from the proliferation of counterfeit parts. MCC strongly encourages customers to purchase MCC parts either directly from MCC or from Authorized MCC Distributors who are listed by country on our web page cited below. Products customers buy either from MCC directly or from Authorized MCC Distributors are genuine parts, have full traceability, meet MCC's quality standards for handling and storage. **MCC will not provide any warranty coverage or other assistance for parts bought from Unauthorized Sources.** MCC is committed to combat this global problem and encourage our customers to do their part in stopping this practice by buying direct or from authorized distributors.