

Products

[Micro Audio Components](#)

[Microphones](#)

[Receivers](#)

[Dynamic Speakers](#)

[Magnetic Sounders](#)

[NFT Series](#)

[MLT-C Series](#)

[MLT-CHN Series](#)

[MLT-GC Series](#)

[MLT-HH Series](#)

[MRT Series](#)

[MZT Series](#)

[NAT Series](#)

[NBT Series](#)

[QMB-105 Series](#)


[QMB-108 Series](#)

[Homepage](#) > [Products](#) > [Micro Audio Components](#) > [Magnetic Sounders](#) > QMB-105 Series

Magnetic Sounders **QMB-105 Series**

QMB-105P (EIAJ:MS-CP2-C12-20)

- Ultra thin ($\phi 12 \times h5.4$)



Frequency response

QMB-105P

applied voltage: 1.5V,
square wave, 1/2 duty
distance for
measurement: 10cm

[QMB-111 Series](#)

[PMX-06 Series](#)

[PMX-04 Series](#)

[QMX Series](#)

[HGP Series](#)

[RMX Series](#)

[QMB Series](#)

[TMX Series](#)

[TMX-H Series](#)


[TMX-F Series](#)

[Patents & Design
rights](#)

[Soldering and Washing
etc](#)

[Recommend
temperature profile for
lead-free solder](#)

[Magnetic Buzzers](#)



Specifications

Type	QMB-105P
Rated Voltage (V)	1.5
*Mean Current Consumption (mA)	MAX10 (TYP9.1)
Coil Resistance (Ω)	50 ± 7.5
#Coil Impedance (Ω)	140
*Sound Output at 10cm (dB)	MIN70 (TYP77)
Rated Frequency (Hz)	2,048
Operating Voltage (V)	MAX 2
Operating Temperature ($^{\circ}\text{C}$)	-20 to +60

Storage Temperature (°C)

-30 to +70

Weight (g)


2

*Value applying rated voltage (2,048Hz, 1/2duty, square wave)

#Value applying rated voltage (2,048Hz, sine wave, measuring current 60μA)

Note) Lead wire type is available on request(Standard leangth: 110mm, 60mm)

Dimensions



unit: mm

housing material: PPE-M

[Back to the Micro Audio Components' Top Page](#)

[Homepage](#)

[Top](#)

[Site Policy](#)