

Product data sheet

Characteristics

ZBRRD

Programmable receiver - 2 relays - 24..240 V AC/
DC - 2 pushbuttons - 6 LEDs



Main

Commercial Status	Commercialised
Range of product	Harmony
Product or component type	Programmable receiver
Device short name	ZBRRD
Product specific application	Interface to actuators
Function of module	Monostable Bi-stable
Reset time	2 ms (time delay)

Complementary

Nominal output current	3 A at 240 V AC for CSA C22.2 No 14 3 A at 24 V DC for CSA C22.2 No 14 3 A at 240 V AC for UL 508 3 A at 120 V AC for EN/IEC 60947-5-1 1.5 A at 240 V AC for EN/IEC 60947-5-1 3 A at 24 V DC for UL 508 0.3 A at 48 V DC for EN/IEC 60947-5-1
Output type	2 relays
Output contacts	2 C/O
Input output isolation	Galvanic isolation
Time delay range	0.5 s (tolerance: - 15...15 %)
Switching capacity in VA	1250 VA
Maximum switching current	5 mA
Maximum switching voltage	250 V AC/DC
[Us] rated supply voltage	24...240 V AC/DC 50/60 Hz - 10...10 %
Communication port protocol	Zigbee (green power) at 2.4 GHz
Maximum sensing distance	131.23 ft (40 m) (transmitter in box type XAL D, receiver in metal enclosure and use relay-antenna) 82.02 ft (25 m) (transmitter in a plastic box type XAL D and receiver in a metal enclosure) 328.08 ft (100 m) (in free field)
Response time	< 30 ms (after transmitter clicks)
Channels utilisation	<= 32 per receiver
Utilisation category	DC-12 conforming to EN/IEC 60947-5-1 AC-15 : B300 conforming to EN/IEC 60947-5-1
Power consumption in W	<= 4 W
Breaking capacity	15 W
Breaking capacity	750 VA
Control circuit frequency	50...60 Hz +/- 10 %
Short circuit protection	0.4 A fuse fast blow
Operating position	Any position without derating

The information provided in this documentation contains general descriptions and/or technical characteristics of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein. *Prices are indicative

Electrical connection	2 conductors cable 0...0 in ² (0.14...1.5 mm ²) - AWG26...AWG16 - flexible - with cable end conforming to IEC 60947-1 1 conductor cable 0...0.01 in ² (0.14...4 mm ²) - AWG26...AWG12 - flexible - with cable end conforming to IEC 60947-1 2 conductors cable 0...0 in ² (0.14...1.5 mm ²) - AWG26...AWG16 - solid - without cable end conforming to IEC 60947-1 1 conductor cable 0...0 in ² (0.14...2.5 mm ²) - AWG26...AWG14 - solid - without cable end conforming to IEC 60947-1
Tightening torque	4.42...8.85 lbf.in (0.5...1 N.m) conforming to EN/IEC 60947-1
Housing material	Self-extinguishing plastic
Status LED	1 LED, color: green and yellow for reception signal 2 LEDs, color: green for function mode 2 LEDs, color: green for relay ON 1 LED, color: green for power ON
Mounting support	Mounting plate 35 mm symmetrical DIN rail conforming to EN/IEC 60715
Rated short-duration power frequency withstand voltage	1.5 kV 50 Hz conforming to EN/IEC 60947-5-1
[Uimp] rated impulse withstand voltage	4 kV
Surge withstand	2 kV (common mode) conforming to IEC 61000-4-5 1 kV (differential mode) conforming to IEC 61000-4-5
Width	1.42 in (36 mm)
Height	4.25 in (108 mm)
Depth	2.95 in (75 mm)
Product weight	0.29 lb(US) (0.13 kg)

Environment

Standards	EN/IEC 60947-1 EN/IEC 60947-5-1 UL 508 CSA C22.2 No 14
Radio agreement	ICASA FCC ARIB T66 ANATEL SRRC RSS
Product certifications	CCC CSA C-Tick GOST UL
Marking	CE
Ambient air temperature for storage	-40...158 °F (-40...70 °C)
Relative humidity	90 % at -4...131 °F (-20...55 °C) without condensation conforming to EN 300-440-1
Vibration resistance	2 gn (f= 8...150 Hz) conforming to IEC 60068-2-6 +/- 7.5 mm (f= 5...14 Hz) conforming to IEC 60068-2-6
Shock resistance	10 gn (duration = 16 ms) 6000 shocks conforming to IEC 60068-2-27
IP degree of protection	IP20 on terminals IP20 on casing conforming to IEC 60529
Pollution degree	2 conforming to IEC 60664-1
Overvoltage category	II conforming to IEC 60664-1
Insulation resistance	> 500 MOhm at 500 V DC conforming to NF C 20-030
[Ui] rated insulation voltage	250 V conforming to IEC 60664-1

Electromagnetic compatibility	Radiated emission conforming to EN 300-440-2 Conducted emission conforming to EN 300-489-3 Conducted emission conforming to EN 300-489-1 Radiated emission conforming to EN 300-440-1 Immunity to microbreaks and voltage drops (test level: 10 ms) conforming to IEC 61000-4-11 Conducted RF disturbances (test level: 10 V) conforming to IEC 61000-4-6 1.2/50 μs shock waves immunity test (test level: 2 kV)common mode conforming to IEC 61000-4-5 1.2/50 μs shock waves immunity test (test level: 1 kV)differential mode conforming to IEC 61000-4-5 Electrical fast transient/burst immunity test (test level: 2 kV)power supply wires conforming to IEC 61000-4-4 Electrical fast transient/burst immunity test (test level: 2 kV)relay wires conforming to IEC 61000-4-4 Susceptibility to electromagnetic fields (test level: 3 V/m)80...2700 MHz, distance = 20 m conforming to IEC 61000-4-3 Susceptibility to electromagnetic fields (test level: 10 V/m)80...2000 MHz conforming to IEC 61000-4-3 Electrostatic discharge immunity test (test level: 6 kV)on contact (on metal parts) conforming to IEC 61000-4-2 Electrostatic discharge immunity test (test level: 8 kV)in free air (in insulating parts) conforming to IEC 61000-4-2 Conducted and radiated emissions , class B conforming to CISPR 22 Immunity for industrial environments conforming to EN/IEC 61000-6-2
Electrical durability	100000 cycles
Mechanical durability	1000000 cycles

Ordering and shipping details

Category	22470 - XB5R WIRELESS PUSH BUTTON
Discount Schedule	I
GTIN	00785901298625
Nbr. of units in pkg.	1
Package weight(Lbs)	0.29
Returnability	Y
Country of origin	ID