

■ Description

The FA7610CP(N), 7612CP(N) and 7617CP(N) are bipolar ICs containing basic circuits necessary for PWM-type switching power supply control. To minimize the number of external discrete components, the FA7610CP(N) is provided for a flyback or step-up power-supply circuit, the FA7612CP(N) for a step-down power-supply circuit and FA7617CP(N) for a flyback power supply circuit.

■ Features

FA7610CP(N)

- For flyback transformer-type or step-up power-supply circuit (maximum output duty = 64% typical)
- Totem-pole predriver
- PWM-type switching power supply control
- Low-voltage operation ($V_{CC} = 3.6$ to $22V$)
- Latch-mode short-circuit protection function (no malfunction by noise)
- Soft-start function
- Undervoltage lockout function
- One capacitor shared for short circuit protection and for soft-start to minimize the number of external discrete components

FA7612CP(N)

- For step-down power-supply circuit (maximum output duty = up to 100%)
- Open collector output
- PWM-type switching power supply control
- Low-voltage operation ($V_{CC} = 3.6$ to $22V$)
- Latch-mode short-circuit protection function (no malfunction by noise)
- Soft-start function
- Undervoltage lockout function
- One capacitor shared for short circuit protection and for soft-start to minimize the number of external discrete components

FA7617CP(N)


- For flyback transformer-type power-supply circuit (maximum output duty = 67% typical)
- Open collector output
- PWM-type switching power supply control
- Low-voltage operation ($V_{CC} = 3.6$ to $22V$)
- Latch-mode short-circuit protection function (no malfunction by noise)
- Soft-start function
- Undervoltage lockout function
- One capacitor shared for short circuit protection and for soft-start to minimize the number of external discrete components

■ Applications


- Battery power supply for portable equipment

■ Dimensions, mm

• SOP-8




• DIP-8




■ Block diagram

● FA7610CP(N)




Pin No.	Pin symbol	Description
1	IN (-)	Inverting input to error amplifier
2	FB	Error amplifier output
3	GND	Ground
4	OUT	Output
5	VCC	Power supply
6	CS	Capacitor for soft-start, short-circuit protection and delay
7	CT	Oscillator timing capacitor
8	REF	Reference voltage output (2.5V)

● FA7612CP(N)



Pin No.	Pin symbol	Description
1	IN (-)	Inverting input to error amplifier
2	FB	Error amplifier output
3	GND	Ground
4	OUT	Output
5	VCC	Power supply
6	CS	Capacitor for soft-start, short-circuit protection and delay
7	CT	Oscillator timing capacitor
8	REF	Reference voltage output (2.5V)

● FA7617CP(N)



Pin No.	Pin symbol	Description
1	IN (-)	Inverting input to error amplifier
2	FB	Error amplifier output
3	GND	Ground
4	OUT	Output
5	VCC	Power supply
6	CS	Capacitor for soft-start, short-circuit protection and delay
7	CT	Oscillator timing capacitor
8	REF	Reference voltage output (2.5V)

■ Absolute maximum ratings (Ta = 25°C)

Item	Symbol	Rating		Unit
		FA7610C	FA7612C/17C	
Supply voltage	V _{CC}	22	22	V
Reference voltage output current	I _{OR}	5	5	mA
Output current	I _O	±50	80	mA
Total power dissipation	P _d	400	400	mW
Operating temperature	T _{opr}	−20 to +85	−20 to +85	°C
Storage temperature	T _{stg}	−40 to +150	−40 to +150	°C

■ Recommended operating conditions

Item	Symbol	FA7610C		FA7612/17C		Unit
		Min.	Max.	Min.	Max.	
Supply voltage	V _{CC}	3.6	20	3.6	20	V
Feedback resistance	R _{NF}	100		100		kΩ
Oscillator timing capacitor	C _T	220	22,000	220	22,000	pF
Oscillator timing resistance	R _T	10	100	10	100	kΩ
Oscillation frequency	f _{osc}	5	200	5	500	kHz

■ Electrical characteristics (Ta = 25°C, V_{CC} = 6V, R_T = 33kΩ, C_T = 1000pF)

Reference voltage section Common to FA7610C/12C/17C

Item	Symbol	Test condition	Min.	Typ.	Max.	Unit
Output voltage	V _{REF}	I _{OR} = 1mA	2.528	2.580	2.632	V
Line regulation	LINE	V _{CC} = 3.6 to 20V, I _{OR} = 1mA		4	12	mV
Load regulation	LOAD	I _{OR} = 0.1 to 1mA		1	6	mV
Output voltage variation due to temperature change	V _{TC1}	Ta = −20 to +25°C	−1		1	%
	V _{TC2}	Ta = +25 to +85°C	−1		1	%

Oscillator section Common to FA7610C/12C/17C

Item	Symbol	Test condition	Min.	Typ.	Max.	Unit
Oscillation frequency	f _{osc}	C _T = 1000pF, R _T = 33kΩ	100	111	122	kHz
Frequency variation 1 (due to supply voltage change)	f _{dV}	V _{CC} = 3.6 to 20V		1		%
Frequency variation 2 (due to temperature change)	f _{dT}	Ta = −20 to +85°C		5		%

Error amplifier section Common to FA7610C/12C/17C

Item	Symbol	Test condition	Min.	Typ.	Max.	Unit
Reference voltage	V _B		0.515	0.525	0.535	V
Input bias current	I _B			5	100	nA
Open-loop voltage gain	A _V		70			dB
Unity-gain bandwidth	G _B			0.6		MHz
Maximum output voltage (Pin 2)	V _{OM+}	R _{NF} = 100kΩ	V _{REF} − 0.2			V
	V _{OM−}	R _{NF} = 100kΩ			200	mV
Output source current (Pin 2)	I _{OM+}	V _{OM} = 1V	40	85	200	μA

PWM comparator section

Item	Symbol	Test condition	FA7610C			FA7612C			FA7617C			Unit
			Min.	Typ.	Max.	Min.	Typ.	Max.	Min.	Typ.	Max.	
Input threshold voltage (pin 2)	V _{TH0}	Duty cycle = 0%		0.85	0.95		0.85	0.95		0.85	0.95	V
Input threshold voltage (pin 2)	V _{TH50}	Duty cycle = 50%		1.1			1.1			1.1		V
Maximum duty cycle	α _M	(Pin 2 = 1.2V)	58	64	75		100		63	67	71	%

Soft-start circuit section Common to FA7610C/12C/17C

Item	Symbol	Test condition	Min.	Typ.	Max.	Unit
Input bias current (Pin 6)	I _{BCS}			80	300	nA
Input threshold voltage (Pin 6)	V _{TH CS0}	Duty cycle = 0%		0.22	0.32	V
Input threshold voltage (Pin 6)	V _{TH CS50}	Duty cycle = 50%		0.46		V

Short-circuit protection circuit section Common to FA7610C/12C/17C

Item	Symbol	Test condition	Min.	Typ.	Max.	Unit
Input threshold voltage (Pin 2)	V _{TH PC}		1.20	1.50	1.80	V
Charge current (Pin 6)	I _{CHG}	Pin 6 = 0V, Pin 2 = 2V	20	30	40	μA
Latch-mode threshold voltage (Pin 6)	V _{TH LA}		1.20	1.50	1.80	V

Undervoltage lockout circuit section Common to FA7610C/12C/17C

Item	Symbol	Test condition	Min.	Typ.	Max.	Unit
OFF-to-ON threshold voltage	V _{TH ON}			2.70		V
ON-to-OFF threshold voltage	V _{TH OFF}			2.52		V
Voltage hysteresis	V _{HYS}		60	180		mV

Output section


Item	Symbol	Test condition	FA7610C			FA7612C/17C			Unit
			Min.	Typ.	Max.	Min.	Typ.	Max.	
H-level output voltage (Pin 4)	V _{OH}	R _L = 10kΩ	3.5	4.0		—	—	—	V
L-level output voltage (Pin 4)	V _{OL}	Output sink current = 20mA		0.25	0.65		0.9	1.5	V
Output source current (Pin 4)	I _{SOURCE}	Pin 4 = 0V	8	11	14	—	—	—	mA

Overall device


Item	Symbol	Test condition	FA7610C			FA7612C/17C			Unit
			Min.	Typ.	Max.	Min.	Typ.	Max.	
Supply current	I _{CC LA}	Latch mode		1.6	2.2		1.5	2.2	mA
Operating-state supply current	I _{CC AV}	R _L = ∞ Duty cycle = 50%		2.6	3.8		1.8	3.0	mA

■ Characteristic curves ($T_a = 25^\circ\text{C}$)


Oscillation frequency(f_{osc}) vs. timing capacitor capacitance(C_T)




Output duty cycle vs. CS terminal voltage(V_{cs})




Output source current (I_{source}) vs. supply voltage(V_{cc})




L-level output voltage(V_{OL}) vs. output sink current (I_{sink})



Supply current(I_{cc}) vs. supply voltage(V_{cc})




Error amplifier frequency(f) vs. voltage gain(A_V) / phase (θ)



■ Application circuit


● FA7610CP(N)

Flyback-transformer type converter circuit




● FA7612CP(N)

Chopper type buck converter circuit



• FA7617CP(N)

Flyback-transformer type converter circuit



Parts tolerances characteristics are not defined in the circuit design sample shown above. When designing an actual circuit for a product, you must determine parts tolerances and characteristics for safe and economical operation.

Please connect a capacitor, which the value is about $0.01\mu\text{F}$ to $0.1\mu\text{F}$, between VCC and REF terminals in order to prevent from irregular output pulse at start up.

WARNING

1. This Data Book contains the product specifications, characteristics, data, materials, and structures as of September 1999. The contents are subject to change without notice for specification changes or other reasons. When using a product listed in this Data Book, be sure to obtain the latest specifications.
2. All applications described in this Data Book exemplify the use of Fuji's products for your reference only. No right or license, either express or implied, under any patent, copyright, trade secret or other intellectual property right owned by Fuji Electric Co., Ltd. is (or shall be deemed) granted. Fuji makes no representation or warranty, whether express or implied, relating to the infringement or alleged infringement of other's intellectual property rights which may arise from the use of the applications described herein.
3. Although Fuji Electric is enhancing product quality and reliability, a small percentage of semiconductor products may become faulty. When using Fuji Electric semiconductor products in your equipment, you are requested to take adequate safety measures to prevent the equipment from causing a physical injury, fire, or other problem if any of the products become faulty. It is recommended to make your design fail-safe, flame retardant, and free of malfunction.
4. The products introduced in this Data Book are intended for use in the following electronic and electrical equipment which has normal reliability requirements.
 - Computers • OA equipment • Communications equipment (terminal devices) • Measurement equipment
 - Machine tools • Audiovisual equipment • Electrical home appliances • Personal equipment • Industrial robots etc.
5. If you need to use a product in this Data Book for equipment requiring higher reliability than normal, such as for the equipment listed below, it is imperative to contact Fuji Electric to obtain prior approval. When using these products for such equipment, take adequate measures such as a backup system to prevent the equipment from malfunctioning even if a Fuji's product incorporated in the equipment becomes faulty.
 - Transportation equipment (mounted on cars and ships) • Trunk communications equipment
 - Traffic-signal control equipment • Gas leakage detectors with an auto-shut-off feature
 - Emergency equipment for responding to disasters and anti-burglary devices • Safety devices
6. Do not use products in this Data Book for the equipment requiring strict reliability such as (without limitation)
 - Space equipment • Aeronautic equipment • Atomic control equipment
 - Submarine repeater equipment • Medical equipment
7. Copyright ©1995 by Fuji Electric Co., Ltd. All rights reserved.
No part of this Data Book may be reproduced in any form or by any means without the express permission of Fuji Electric.
8. If you have any question about any portion in this Data Book, ask Fuji Electric or its sales agents before using the product. Neither Fuji nor its agents shall be liable for any injury caused by any use of the products not in accordance with instructions set forth herein.