

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT – By –

ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL RELEASE	26NOV2013	GSK	BvH

NOTES:

Tolerances cable lengths:

0m to 0.5m +30mm

0.5m to 1.0m +50mm

1.0m to 3.0m +100mm

< 3.0m +1.5%

VIEW 'A'

A

L

20mm

PVC CABLE

No./diameter of wires	5 x 0.34 mm²
Wire isolation	PVC (br, wh, bl, bk, gnye)
C-track properties	
Jacket	PVC (UL/CSA)
Outer diameter	approx. 5.2 mm
Bend radius (moving)	10 x outer diameter
Temperature range (fixed)	−30...+80 °C
Temperature range (mobile)	−5...+80 °C

TECHNICAL DATA

Operating voltage	max. 125 V AC/DC
Operating current per contact	max. 4 A
Locking of ports	Screw thread M12 x 1 mm (recommended torque 0.6 Nm) self-securing
Protection	IP65 and IP67 when plugged and screwed down (EN 60529)

PUR CABLE

No./diameter of wires	5 x 0.34 mm²
Wire isolation	PP (br, wh, bl, bk, gnye)
C-track properties	yes
Jacket	PUR (UL/CSA)
Outer diameter	approx. 5.0 mm
Bend radius (moving)	10 x outer diameter
Temperature range (fixed)	−50...+80 °C
Temperature range (mobile)	−25...+80 °C

5 pos	10mtr	PVC	Black	1-2273089-4	5x22AWG PVC 10.0m	8
	5mtr			1-2273089-3	5x22AWG PVC 5.0m	7
	3mtr			1-2273089-2	5x22AWG PVC 3.0m	6
	1.5mtr			1-2273089-1	5x22AWG PVC 1.5m	5
5 pos	10mtr	PUR	Black	2273089-4	5x22AWG PUR 10.0m	4
	5mtr			2273089-3	5x22AWG PUR 5.0m	3
	3mtr			2273089-2	5x22AWG PUR 3.0m	2
	1.5mtr			2273089-1	5x22AWG PUR 1.5m	1
LENGTH”L”		MATERIAL	JACKET COLOR	TE PN	DESCRIPTION	ITEM

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

mm

DWN

SATHISH KUMAR .G

26NOV2013

CHK

B.VELDHOVEN

26NOV2013

APVD

A.VAN ZANDVOORT

26NOV2013

PRODUCT SPEC

—

APPLICATION SPEC

—

WEIGHT

—

CUSTOMER DRAWING

SCALE

NTS

SHEET

1 OF 1

REV

A

STE

TE Connectivity

M12 X 1.0 ANGLED SOCKET PIGT A

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3

00779

C-2273089

—

1470-19 (3/11)