

9157 Multi-Conductor - Audio, Control and Instrumentation Cable



For more Information
please call

1-800-Belden1

**Description:**

18 AWG stranded (16x30) tinned copper conductors, PVC insulation, twisted pairs, PVC jacket.

Physical Characteristics (Overall)**Conductor****AWG:**

# Pairs	AWG	Stranding	Conductor Material
4	18	16x30	TC - Tinned Copper

Insulation**Insulation Material:**

Insulation Material	Wall Thickness (mm)
PVC - Polyvinyl Chloride	0.330

Inner Shield**Inner Shield Material:**

Inner Shield Material
Unshielded

Outer Shield**Outer Shield Material:**

Outer Shield Material
Unshielded

Outer Jacket**Outer Jacket Material:**

Outer Jacket Material	Nom. Wall Thickness (mm)
PVC - Polyvinyl Chloride	0.8128

Overall Cabling

Overall Nominal Diameter: 9.677 mm

Pair**Pair Color Code Chart:**

Number	Color
1	Black & Red
2	Black & White
3	Black & Green
4	Black & Blue

Mechanical Characteristics (Overall)

Operating Temperature Range:	-20°C To +80°C
Non-UL Temperature Rating:	80°C (UL AWM Style 2464)
Bulk Cable Weight:	110.127 Kg/Km
Max. Recommended Pulling Tension:	796.228 N
Min. Bend Radius (Install)/Minor Axis:	101.600 mm

Applicable Specifications and Agency Compliance (Overall)**Applicable Standards & Environmental Programs**

9157 Multi-Conductor - Audio, Control and Instrumentation Cable

NEC/(UL) Specification:	CMG
-------------------------	-----

CEC/C(UL) Specification:	CMG
--------------------------	-----

AWM Specification:	UL Style 2464 (300 V 80°C)
--------------------	----------------------------

EU CE Mark:	Yes
-------------	-----

EU Directive 2000/53/EC (ELV):	Yes
--------------------------------	-----

EU Directive 2002/95/EC (RoHS):	Yes
---------------------------------	-----

EU RoHS Compliance Date (mm/dd/yyyy):	04/01/2005
---------------------------------------	------------

EU Directive 2002/96/EC (WEEE):	Yes
---------------------------------	-----

EU Directive 2003/11/EC (BFR):	Yes
--------------------------------	-----

CA Prop 65 (CJ for Wire & Cable):	Yes
-----------------------------------	-----

MII Order #39 (China RoHS):	Yes
-----------------------------	-----

Flame Test

C(UL) Flame Test:	FT4
-------------------	-----

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Electrical Characteristics (Overall)**Nom. Capacitance Conductor to Conductor:**

Capacitance (pF/m)

83.6655

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/km)

19.2267

Max. Operating Voltage - UL:

Voltage

300 V RMS (UL AWM Style 2464)

Max. Recommended Current:

Current

3.4 Amps per conductor @ 20°C

Related Documents:

No related documents are available for this product

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
9157 060100	30 MT	3.810 KG	CHROME		4 PR #18 PVC FRPVC
9157 0601000	305 MT	37.648 KG	CHROME	C	4 PR #18 PVC FRPVC
9157 060500	152 MT	18.597 KG	CHROME	C	4 PR #18 PVC FRPVC

Notes:

C = CRATE REEL PUT-UP.

Revision Number: 2 Revision Date: 05-26-2010

© 2011 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

9157 Multi-Conductor - Audio, Control and Instrumentation Cable

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product. Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.