




LOC	DIST	REVISIONS					
FT	0	P	LTR	DESCRIPTION	DATE	DWN	APVD
			E3	REVISED PER ECO-11-004587	11MAR2011	RK	HMR



PRELIMINARY	0.76µm GOLD	-	-	60.60	55.88	10	2-796859-6
PRELIMINARY	0.2µm GOLD		DETAIL G	35.20	30.48	5	2-796859-5
PRELIMINARY	TIN		DETAIL F	25.04	20.32	3	2-796859-4
	TIN	-	-	126.64	121.92	23	2-796859-3
	TIN	-	-	121.56	116.84	22	2-796859-2
	TIN	-	-	116.48	111.76	21	2-796859-1
	TIN	-	-	111.40	106.68	20	2-796859-0
	TIN	-	-	106.32	101.60	19	1-796859-9
	TIN	-	-	101.24	96.52	18	1-796859-8
	TIN	-	-	96.16	91.44	17	1-796859-7
	TIN	-	-	91.08	86.36	16	1-796859-6
	TIN	-	-	86.00	81.28	15	1-796859-5
	TIN	-	-	80.92	76.20	14	1-796859-4
	TIN	-	-	75.84	71.12	13	1-796859-3
	TIN	-	-	70.76	66.04	12	1-796859-2
	TIN	-	-	65.68	60.96	11	1-796859-1
	TIN	-	-	60.60	55.88	10	1-796859-0
	TIN	-	-	55.52	50.80	9	796859-9
	TIN	-	-	50.44	45.72	8	796859-8
	TIN	-	-	45.36	40.64	7	796859-7
	TIN	-	-	40.28	35.56	6	796859-6
	TIN	-	-	35.20	30.48	5	796859-5
	TIN	-	-	30.12	25.40	4	796859-4
	TIN	-	-	25.04	20.32	3	796859-3
	TIN	-	-	19.96	15.24	2	796859-2
TERMINAL PLATING	MARKING	SPECIAL	L	H	NO. OF POSN	PART NUMBER	

- 1

MATERIALS AND FINISH:
HOUSING: PA 6-6, UL 94-V0, COLOR: GREEN.
TERMINAL: PHOSPHOR BRONZE, PLATING: SEE TABLE, OVER 2-3µm NICKEL
- 2

SUITABLE FOR 1,6-2, 4mm PC BOARD THICKNESS.
- 3

RECOGNIZED UNDER THE COMPONENT PROGRAM OF
UNDERWRITERS LABORATORIES INC. FILE No. E60677.
- 4

IMQ CERTIFICATE WITH SURVEILLANCE ON CONFORMITY
WITH IEC 998-1/998-2-1.
- 5

INK MARKING, COLOR: WHITE.
- 6

LABEL APPLIED OR INK MARKING AS SHOWN.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN S. WELDON 12FEB2001
CHK D. BIEVENOUR 12FEB2001
APVD D. BIEVENOUR 12FEB2001

DIMENSIONS:
mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ±
1 PLC ±0.2
2 PLC ±0.00
3 PLC ±0.000
4 PLC ±0.0000
ANGLES ±
FINISH

PRODUCT SPEC
APPLICATION SPEC
WEIGHT

-
-
-


NAME
SIZE
CAGE CODE
DRAWING NO
RESTRICTED TO

TE Connectivity
TERMINAL BLOCK, PLUG
90 DEGREE, WITH FLANGE,
5.08mm PITCH
A200779C-796859
SCALE 2:1
SHEET 1 OF 2
REV E3

CUSTOMER DRAWING

SCALE 2:1
SHEET 1 OF 2
REV E3



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S.WELDON 12FEB2001 CHK D.BIEVENOUR 12FEB2001 APVD D.BIEVENOUR 12FEB2001		 TE Connectivity	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±.2 1 PLC ±0.00 2 PLC ±0.00 3 PLC ±0.00 4 PLC ±0.0000 ANGLES ±.		NAME TERMINAL BLOCK, PLUG 90 DEGREE, WITH FLANGE, 5.08mm PITCH	
		PRODUCT SPEC -		APPLICATION SPEC -	
MATERIAL -		FINISH -		WEIGHT -	
CUSTOMER DRAWING				SIZE A2	
SCALE 4:1				CAGE CODE 00779	
DRAWING NO C-796859				RESTRICTED TO -	
SHEET 2 OF 2				REV F3	