





4. QUALIFICATION OF THE CRIMP APPLICATION TOOLING SHALL BE CONTROLLED BY THE REQUIREMENTS ESTABLISHED UNDER USCAR 21.
5. LOOSE END SPLICING TO BE USED.



3	1326032-6 REELED FOR AMP APPLICATORS							12 AWG	1-1326032-2
	1326032-5 REELED FOR AMP APPLICATORS							14 AWG	1-1326032-1
	1326032-4 REELED FOR AMP APPLICATORS							16 AWG	1-1326032-0
	1326032-3 REELED FOR AMP APPLICATORS							18 AWG	1326032-9
	1326032-2 REELED FOR AMP APPLICATORS							20 AWG	1326032-8
	1326032-1 REELED FOR AMP APPLICATORS							22 AWG	1326032-7
2	1.35	6.8	4.30	6.09	4.7	2.70	5.25	12 AWG	1326032-6
	1.35	6.5	4.30	5.62	3.9	1.70	3.88	14 AWG	1326032-5
	1.10	5.6	3.80	4.54	3.9	1.70	3.88	16 AWG	1326032-4
	1.10	5.6	3.80	4.54	3.3	1.30	2.76	18 AWG	1326032-3
	0.90	5.0	3.40	4.11	3.3	1.30	2.76	20 AWG	1326032-2
	0.90	5.0	3.40	4.11	2.5	0.90	2.11	22 AWG	1326032-1
REELING	N	L	ØK	J	H	ØF	E	WIRE SIZE	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN D. STRAUSSER 28APR99 CHK D. BROWN 28APR99 APP'D D. BROWN 28APR99		 TE Connectivity	
DIMENSIONS: mm		TOLERANCES, UNLESS OTHERWISE SPECIFIED: 0 PLC $\pm$. 2 PLC $\pm$.02, .10 3 PLC $\pm$. 4 PLC $\pm$. ANGLES $\pm$ $^{\circ}$ 45		NAME 2.8mm RECEPTACLE, SEALED	
		PRODUCT SPEC SAE/J1537-2 8/97 APPLICATION SPEC 114-13013		SIZE CAGE CODE DRAWING NO A1 00779 C=1326032	
MATERIAL 		FINISH 		RESTRICTED TO -	
CUSTOMER DRAWING					
SCALE 10:				SHEET 1 OF 1 REV E	