




**.100" [2.54 mm] Contact Centers, .431" [10.95 mm] Insulator Height,
Dip Solder/Eyelet/Right Angle for .062" [1.57 mm] or .031" [0.79 mm] Mating PCB**

SPECIFICATIONS

- Accommodates .062" $\pm$.008" [1.57 mm $\pm$ 0.20 mm] or .031" $\pm$.006" [0.79 mm $\pm$ 0.15 mm] mating PCB (for .093" [2.36 mm] PC board see following pages)
- PBT, PPS, PA9T or PEEK insulator
- Molded-in key available
- 3 Amps current rating for one contact energized
- 30 milli Ohms maximum at rated current
- UL Flammability Rating: 94V-0



READOUT




DUAL (D)

HALF LOADED (H)











POLARIZING KEYS (For .062" Mating PCB Only)

**PLA-K1
KEY IN BETWEEN CONTACTS
(ORDER SEPARATELY)**



CONSULT FACTORY FOR MOLDED-IN KEY

TERMINATION TYPE

FULL BELLOW	TAIL LENGTH	ROW SPACING	MIN HOLE SIZE	FULL BELLOW	
	RIGHT ANGLE .125" [3.18] (RA)	.156" [3.96]	Ø.043" [1.09]	STRAIGHT  .007" [0.18] THICK (RE)	EYELET ACCEPTS 3-#26 AWG  .014" [0.36] THICK (TE)
 	STRAIGHT .200" [5.08] (RT) .440" [11.19] (RY)	.140" [3.56] .140" [3.56]	Ø.043" [1.09] Ø.043" [1.09]	CARD EXTENDER 	ACCEPTS .062" [1.57] PCB TAIL LENGTH .210" [5.33] EYELET (RE) .185" [4.70] (RT) .425" [10.80] (RY) MODIFICATION CODE -S13 -S13 -S13
	CRIMP TO CENTER (SX) .160" [4.06]		Ø.043" [1.09]	SURFACE MOUNT (RT)  MODIFICATION CODE -S924	
CANTILEVER 	TAIL LENGTH .200" [5.08] (ET) .440" [11.19] (EY)	ROW SPACING .140" [3.56] .140" [3.56]	MIN HOLE SIZE Ø.040" [1.02] Ø.040" [1.02]	RIGHT ANGLE SURFACE MOUNT (RA)  MODIFICATION CODE -S2106	

MOUNTING STYLE



CLEARANCE HOLE (H)

THREADED INSERT (I)

FLOATING BOBBIN (F)

NO MOUNTING EARS (N)

SIDE MOUNTING (S)

OPEN CARDSLOT (B)



.100" [2.54 mm] Contact Centers, .431" [10.95 mm] Insulator Height, Dip Solder/Eyelet/Right Angle for .062" [1.57 mm] or .031" [0.79 mm] Mating PCB

PART NUMBER OPTIONS

MATERIALS (INSULATOR/CONTACT)

- E = PBT/Phosphor Bronze (Standard)
 R = PPS/Phosphor Bronze
 G = PA9T/Phosphor Bronze
 H = PBT/Beryllium Copper
 A = PPS/Beryllium Copper
 J = PA9T/Beryllium Copper
 *F = PPS/Spinodal (Overall Gold Plating Only)
 Consult Factory for Special Soldering Guidelines
 *C = PPS/Beryllium Nickel (Overall Gold Plating Only)
 *W = PEEK/Beryllium Nickel (Overall Gold Plating Only)
 *Consult factory for availability.
 Refer to Page 7 for Operating/Processing Temperatures

CONTACT FINISH - RoHS Compliant

All platings are Lead Free and have .000050" Nickel underplate

Contact Surface	Termination
B = .000010" Gold	.000100" Pure Tin, Matte
C = .000030" Gold	.000100" Pure Tin, Matte
G = .000010" Gold	.000005" Gold
Y = .000030" Gold	.000005" Gold
Contact Surface	Overall Plating
S = .000010" Gold	.000010" Gold
M = .000030" Gold	.000010" Gold
E = .000100" Pure Tin, Matte	.000100" Pure Tin, Matte

CONTACT CENTERS

C = .100" [2.54 mm]

E B C 43 D RE H - Sxxx

MODIFICATIONS (Consult Factory)

OMIT FOR STANDARD

-S13 = Card Extender Accepts .062" [1.57 mm] PCB

(RE, RT, RY Terminations Only)

-S734 = .031" ± .006" [0.79 mm ± 0.15 mm] Mating PCB

-S924 = Surface Mount

-S2106 = Right Angle Surface Mount

MOUNTING STYLE (Opposite Page)

H = .125" [3.18 mm] Clearance Holes

N = No Mounting

B = Open Card slot

S = Side Mounting

I = Threaded Insert

F = Floating Bobbin

TERMINATION TYPE (Opposite Page)

RA = Right Angle

RE = Eyelet (Standard)

TE = Eyelet (Overall Plated Only)

**ET, RT = .140" [3.56 mm] X .200" [5.08 mm] Dip Solder

**EY, RY = .140" [3.56 mm] X .440" [11.19 mm] Dip Solder

RX = .200" [5.08 mm] X .185" [4.70 mm] Dip Solder

RJ = .250" [6.35 mm] X .165" [4.19 mm] Dip Solder

SX = .110" [2.79 mm] Centered Dip Solder

READOUT (Opposite Page)

D = Dual


H = Half Loaded

NUMBER OF CONTACT POSITIONS

See Chart Below

**ET & EY Only available in 'B' & 'C' Plating code

DIMENSIONS Dimensions in [] are in millimeters, all others are in inches.



Female Card Edge

Tolerances on non-critical dimensions may vary slightly due to shrinkage differential per insulator material; Consult factory.

POSITIONS/ CONTACTS	INCHES						MILLIMETERS					
	A±.008	B±.008	C±.015	D±.010	E±.020	F+.005/- .015	A±.020	B±.020	C±.038	D±.025	E±.051	F+.013/-0.38
04/08*	0.300	0.500	0.675	0.975	1.275	0.330	7.62	12.70	17.15	24.77	32.39	8.38
05/10	0.400	0.600	0.775	1.075	1.375		10.16	15.24	19.69	27.31	34.93	
06/12	0.500	0.700	0.875	1.175	1.475		12.70	17.78	22.23	29.85	37.47	
07/14	0.600	0.800	0.975	1.275	1.575		15.24	20.32	24.77	32.39	40.01	
08/16	0.700	0.900	1.075	1.375	1.675		17.78	22.86	27.31	34.93	42.55	
10/20	0.900	1.100	1.275	1.575	1.875		22.86	27.94	32.39	40.01	47.63	
12/24	1.100	1.300	1.475	1.775	2.075		27.94	33.02	37.47	45.09	52.71	
13/26	1.200	1.400	1.575	1.875	2.175		30.48	35.56	40.01	47.63	55.25	
15/30	1.400	1.600	1.775	2.075	2.375		35.56	40.64	45.09	52.71	60.33	
17/34	1.600	1.800	1.975	2.275	2.575		40.64	45.72	50.17	57.79	65.41	
18/36	1.700	1.900	2.075	2.375	2.675		43.18	48.26	52.71	60.33	67.95	
19/38	1.800	2.000	2.175	2.475	2.775		45.72	50.80	55.25	62.87	70.49	
20/40	1.900	2.100	2.275	2.575	2.875		48.26	53.34	57.79	65.41	73.03	
22/44	2.100	2.300	2.475	2.775	3.075		53.34	58.42	62.87	70.49	78.11	
23/46*	2.200	2.400	2.575	2.875	3.175		55.88	60.96	65.41	73.03	80.65	
25/50	2.400	2.600	2.775	3.075	3.375		60.96	66.04	70.49	78.11	85.73	
26/52	2.500	2.700	2.875	3.175	3.475		63.50	68.58	73.03	80.65	88.27	
28/56	2.700	2.900	3.075	3.375	3.675		68.58	73.66	78.11	85.73	93.35	
30/60	2.900	3.100	3.275	3.575	3.875		73.66	78.74	83.19	90.81	98.43	
31/62	3.000	3.200	3.375	3.675	3.975	0.400	76.20	81.28	85.73	93.35	100.97	10.16
35/70	3.400	3.600	3.775	4.075	4.375		86.36	91.44	95.89	103.51	111.13	
36/72	3.500	3.700	3.875	4.175	4.475		88.90	93.98	98.43	106.05	113.67	
40/80	3.900	4.100	4.275	4.575	4.875		99.06	104.14	108.59	116.21	123.83	
43/86	4.200	4.400	4.575	4.875	5.175		106.68	111.76	116.21	123.83	131.45	
44/88	4.300	4.500	4.675	4.975	5.275		109.22	114.30	118.75	126.37	133.99	
49/98	4.800	5.000	5.175	5.475	5.775		121.92	127.00	131.45	139.07	146.69	
50/100	4.900	5.100	5.275	5.575	5.875		124.46	129.54	133.99	141.61	149.23	
52/104*	5.100	5.300	5.475	5.775	6.075		129.54	134.62	139.07	146.69	154.31	
60/120	5.900	6.100	6.275	6.575	6.875		149.86	154.94	159.39	167.01	174.63	
65/130	6.400	6.600	6.775	7.075	7.375		162.56	167.64	172.09	179.71	187.33	

* Consult factory for availability.