




ALL RIGHTS RESERVED. NO PORTION OF THIS PUBLICATION,
WHETHER IN WHOLE OR IN PART CAN BE REPRODUCED
WITHOUT THE EXPRESS WRITTEN CONSENT OF SPC
TECHNOLOGY.

SPC-F005.DWG

REVISIONS

DOC. NO. SPC-F005 * Effective: 7/6/02 * DCP No: 1398

DCP #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
1355	A	RELEASED	JWM	1/2/04	JN	03/04/08	JN	03/04/08



Combine the benefits of a 4mm dia. contact and a 2mm dia.
smooth tip in one probe set. Tips thread into probe bodies.
IEC61010 Ratings: 1000V CAT III



36 Amps

Reinforced or Double Insulation

Materials: Body: Polymide (Nylon)

Tip: Brass, Nickel Plated

Jack: Brass

Internal Resistance: <5 milliohms

Temperature: -20°C to 80°C

DISCLAIMER:
ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED
HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE
BELIEVE TO BE ACCURATE AND RELIABLE. SINCE
CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE
USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT
FOR THE INTENDED USE AND ASSUME ALL RISK AND
LIABILITY WHATSOEVER IN CONNECTION THEREWITH.

TOLERANCES:
UNLESS OTHERWISE
SPECIFIED,
DIMENSIONS ARE
FOR REFERENCE
PURPOSES ONLY.

DRAWN BY: Jeff McVicker DATE: 1/2/04
CHECKED BY: Jason Nash DATE: 03/04/08
APPROVED BY: Jason Nash DATE: 03/04/08

DRAWING TITLE:
Replaceable Tip Probe w/4mm Safety Jack
SIZE DWG. NO. A 76-080 ELECTRONIC FILE 16F7739.dwg REV A
SCALE: NTS U.O.M.: INCHES [mm] SHEET: 1 OF 1