



Technical drawing of a mechanical part showing dimensions: 2,1 ± 0,2, 5,0, 8,4, and 23,6.



1 Noryl (UL94-VI) Colore Nero (Black Colour).

2 Tolleranza non Cumulativa.
(Non-Cumulative Tolerance.)

3 PA 6.6 15% g.f. masterizzato ROSSO
(PA 6.6 15% g.f. masterized - RED)

4 OBSOLETE PARTS: OBSOLETE CIS
STREAMLINING PER D.RENAUD/D.SINISI

5 OBSOLETE

4

OBSOLETE

OBSOLETE

4	284072-1	7,62	12,5			3
2	284071-1	2,54	7,4			
22	280636	53,34	58,2			
15	280635	35,56	40,4			
12	280634	27,94	32,8			
10	280633	22,86	27,7			
9	5 280632	20,32	25,1			
8	280631	17,78	22,6			
6	280630	12,70	17,5			
4	280629	7,62	12,5			
2	280628	2,54	7,4			1
N ^o Pos.	Part. Number	Dim. "A "	Dim. " B "			

o (Black Colour).

tiva.

nce.)

rizzato Rosso

rized - RED)

OLETE CIS

ENAUD/D.SINISI

				FINITURA / COLORE (FINISH / COLOUR)		MATERIALE (MATERIAL)		NUMERO (PART NUMBER)	
				CUSTOMER DWG. FOR REFERENCE ONLY			DISEGNO PER CLIENTE SOLO PER RIFERIMENTO		
				THIS DRAWING IS UNPUBLISHED		RELEASE FOR PUBLICATION		19	
				© COPYRIGHT 19 BY TE INCORPORATED, HARRISBURG, PA ALL INTERNATIONAL RIGHT RESERVED TE PRODUCTS MAY BE COVERED BY U.S. AND FOREIGN PATENT AND/OR PATENT PENDING					
				TOLLERANZE: SE NON DIVERSAMENTE SPECIFICATO (TOLERANCES UNLESS OTHERWISE SPECIFIED)		DIAM. ISOLANTE (INS. DIA. RANGE)		RANGO FILO (WIRE RANGE)	
				± 0,3				SCALA (SCALE) 5:1	
				ANGOLI (ANGLES) ± 2°		 TE Connectivity			
				RELEASED FOR PRODUCTION P/N 284071-1 & 284072-1 ETD 01/11/86 APPROV. P/N 284071-1 & 284072-1 ETD 01/11/86 APPROV. P/N 284071-1 & 284072-1 ETD 01/11/86		DESCRIZIONE (DESCRIPTION): AMP MODU II Pin Housing, Single Row, Crimp Snap-In.			
				DIS. Bassano 29 th 9-86 CONT. (CHK) APP.		LOC. SIZE NUMERO (DWG NO) 280628		REV. FOGLIO (SHEET) DI 1 OF 1	
				2 Revised note 1 Revised and Redrawn		10. 31 29. 9-86 APP.		H4 1	
				REV. REVISIONI (REV LTR) (REVISION RECORD) DIS. DATA (DR) (DATE)					