



0496




0496-0-15-XX-23-XX-10-0
Press-fit in .106 mounting hole

0368




0368-0-33-XX-13-XX-10-0
#16A Crimp Barrel

8067




8067-0-19-XX-13-XX-10-0
Wire Termination

1105




1105-0-15-XX-13-XX-04-0
Press-fit in .080 mounting hole

8730




8730-0-19-XX-23-XX-10-0
Wire Termination

3667




3667-0-19-XX-23-XX-10-0
Wire Termination

9372




9372-0-15-XX-23-XX-10-0
Solder mount in .102 min. mounting hole

4582




4582-0-15-XX-23-XX-10-0
Square press-fit in .040 plated thru hole

5834




5834-0-15-XX-23-XX-10-0
Press-fit in .107 mounting hole

9401




9401-0-15-XX-23-XX-10-0
Solder mount in .102 min. mounting hole
Also available on 24mm wide carrier tape: 1,100 parts per 13" reel.
Order as: 9401-0-57-XX-23-XX-10-0

9801



9801-0-15-XX-23-XX-10-0
Solder mount in .102 min. mounting hole
Also available on 16mm wide carrier tape: 1,200 parts per 13" reel.
Order as: 9801-0-57-XX-23-XX-10-0

8829



8829-0-15-XX-23-XX-10-0
Solder mount in .102 min. mounting hole

SPECIFICATIONS

SHELL MATERIAL:
Brass Alloy 360, 1/2 Hard

CONTACT MATERIAL:
Beryllium Copper Alloy 172, HT

DIMENSION IN INCHES
TOLERANCES ON:
LENGTHS: ±.005
DIAMETERS: ±.002
ANGLES: ± 2°

ORDER CODE: XXXX - X - XX - XX - X3 - XX - XX - 0

BASIC PART #

SPECIFY SHELL FINISH:
01 200μ" TIN/LEAD OVER NICKEL
80 200μ" TIN OVER NICKEL
15 10μ" GOLD OVER NICKEL

SPECIFY CONTACT FINISH:
01 200μ" TIN/LEAD OVER NICKEL
80 200μ" TIN OVER NICKEL
27 30μ" GOLD OVER NICKEL



SELECT CONTACT

#13 or #23 CONTACT (DATA ON PAGES 224 & 225)