










RECOMMENDED PCB LAYOUT



NOTES:

1. MATERIAL:

HSG: LCP, GLASS-FILLED, UL94V-0,
COLOR: BLACK
PIN: 0.64MM SQ PIN, COPPER ALLOY

2. PLATING TYPE:

- (1) : 0.381 μ m MIN. GOLD PLATE ON CONTACT AND 1.905 μ m MIN. TIN ON SOLDERTAIL OVER 1.270 μ m MIN. NICKEL OVERALL.
- (2) : 0.762 μ m MIN. GOLD PLATE ON CONTACT AND 1.905 μ m MIN. TIN ON SOLDERTAIL OVER 1.270 μ m MIN. NICKEL OVERALL.
- (3) : 2.540 μ m MIN. TIN IN SELECTED AREA OVER 1.270 μ m MIN. NICKEL OVERALL.

- 3. THE ABOVE 10 CKT IS FOR ILLUSTRATION PURPOSE ONLY.
- 4. FOR PACKAGING OPTION PLEASE REFER TO THE TABLE.
- 5. RECOMMENDED PCB THICKNESS 1.60MM.
- 6. PRODUCT SPECIFICATION: PS-87920-019
- 7. WAFER TO BE FLAT WITHIN 0.003mm/mm
- 8. IRREGULAR CIRCUIT CUTOFF WITHIN BREAKAWAY SECTION IS PERMISSIBLE. CUTTING OR CHIPPING OF THE MAIN BODY IS NOT ACCEPTABLE.
- 9. PARTS ARE NOT STACKABLE ON 2.54 CENTER
- 10. PACKAGING SPECIFICATION:
TRAY: PK-89990-489
BULK: PK-89990-491

EWR# 1010 & 1021 EC NO: S2007-0182 DRWN:SKL IM01 2006/09/11 CHKD:CWLAM 2006/09/12 APPR:KWLEE 2006/09/13	DESCRIPTION REV A	QUALITY SYMBOLS ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE NTS	DESIGN UNITS METRIC	 THIRD ANGLE PROJECTION
			4 PLACES 3 PLACES 2 PLACES 1 PLACE	mm	INCH	DRAWN BY SKL IM01	DATE 2006/08/21	TITLE CUSTOM HEADER C-GRID,SINGLE WAFER HDR, THROU HOLE,VERTICAL, LF MOLEX INCORPORATED	
				± ---	± ---	CHECKED BY CWLAM	DATE 2006/09/04		
				± 0.2	± ---	APPROVED BY KWLEE	DATE 2006/09/04		
				± ---	± ---	MATERIAL NO. SEE TABLE	DOCUMENT NO. SD-87914-059		
ANGULAR ± 3 °		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION					

	10		9		8		7		6		5		4		3		2		1		
F	PART NO FOR TRAY PACKAGING	PART NO FOR BULK PACKAGING	CKT SIZE	PLATING TYPE	DIMENSION					PART NO FOR TRAY PACKAGING	PART NO FOR BULK PACKAGING	CKT SIZE	PLATING TYPE	DIMENSION							
								MATING END	SOLDER TAIL								MATING END	SOLDER TAIL			
					A	B	F	M	P					A	B	F	M	P			
	87914-0401	-----	4	1	5.08	2.54	13.21	8.13	2.79		87914-0404	-----	4	1	5.08	2.54	11.11	6.10	2.72		
	87914-0402	-----	4	2	5.08	2.54	13.21	8.13	2.79		87914-0405	-----	4	2	5.08	2.54	11.11	6.10	2.72		
E		87914-0403	-----	4	3	5.08	2.54	13.21	8.13	2.79		87914-0406	-----	4	3	5.08	2.54	11.11	6.10	2.72	
	87914-0601	-----	6	1	7.62	5.08	13.21	8.13	2.79		87914-0604	-----	6	1	7.62	5.08	11.11	6.10	2.72		
	87914-0602	-----	6	2	7.62	5.08	13.21	8.13	2.79		87914-0605	-----	6	2	7.62	5.08	11.11	6.10	2.72		
	87914-0603	-----	6	3	7.62	5.08	13.21	8.13	2.79		87914-0606	-----	6	3	7.62	5.08	11.11	6.10	2.72		
D		87914-0801	-----	8	1	10.16	7.62	13.21	8.13	2.79		87914-0804	-----	8	1	10.16	7.62	11.11	6.10	2.72	
		87914-0802	-----	8	2	10.16	7.62	13.21	8.13	2.79		87914-0805	-----	8	2	10.16	7.62	11.11	6.10	2.72	
		87914-0803	-----	8	3	10.16	7.62	13.21	8.13	2.79		87914-0806	-----	8	3	10.16	7.62	11.11	6.10	2.72	
	87914-1001	-----	10	1	12.70	10.16	13.21	8.13	2.79		87914-1004	-----	10	1	12.70	10.16	11.11	6.10	2.72		
	87914-1002	-----	10	2	12.70	10.16	13.21	8.13	2.79		87914-1005	-----	10	2	12.70	10.16	11.11	6.10	2.72		
C		87914-1003	-----	10	3	12.70	10.16	13.21	8.13	2.79		87914-1006	-----	10	3	12.70	10.16	11.11	6.10	2.72	

	10		9		8		7		6		5		4		3		2		1					
F	PART NO FOR TRAY PACKAGING	PART NO FOR BULK PACKAGING	CKT SIZE	PLATING TYPE	DIMENSION						PART NO FOR TRAY PACKAGING	PART NO FOR BULK PACKAGING	CKT SIZE	PLATING TYPE	DIMENSION									
								MATING END	SOLDER TAIL									MATING END	SOLDER TAIL					
					A	B	F	M	P						A	B	F	M	P					
	87914-2201	-----	22	1	27.94	25.40	13.21	8.13	2.79		87914-2204	-----	22	1	27.94	25.40	11.11	6.10	2.72	F				
	87914-2202	-----	22	2	27.94	25.40	13.21	8.13	2.79		87914-2205	-----	22	2	27.94	25.40	11.11	6.10	2.72					
	87914-2203	-----	22	3	27.94	25.40	13.21	8.13	2.79		87914-2206	-----	22	3	27.94	25.40	11.11	6.10	2.72					
E	87914-2401	-----	24	1	30.48	27.94	13.21	8.13	2.79		87914-2404	-----	24	1	30.48	27.94	11.11	6.10	2.72					
	87914-2402	-----	24	2	30.48	27.94	13.21	8.13	2.79		87914-2405	-----	24	2	30.48	27.94	11.11	6.10	2.72					
	87914-2403	-----	24	3	30.48	27.94	13.21	8.13	2.79		87914-2406	-----	24	3	30.48	27.94	11.11	6.10	2.72	E				
D	87914-2601	-----	26	1	33.02	30.48	13.21	8.13	2.79		87914-2604	-----	26	1	33.02	30.48	11.11	6.10	2.72					
	87914-2602	-----	26	2	33.02	30.48	13.21	8.13	2.79		87914-2605	-----	26	2	33.02	30.48	11.11	6.10	2.72					
	87914-2603	-----	26	3	33.02	30.48	13.21	8.13	2.79		87914-2606	-----	26	3	33.02	30.48	11.11	6.10	2.72					
C	87914-2801	-----	28	1	35.56	33.02	13.21	8.13	2.79		87914-2804	-----	28	1	35.56	33.02	11.11	6.10	2.72	D				
	87914-2802	-----	28	2	35.56	33.02	13.21	8.13	2.79		87914-2805	-----	28	2	35.56	33.02	11.11	6.10	2.72					
	87914-2803	-----	28	3	35.56	33.02	13.21	8.13	2.79		87914-2806	-----	28	3	35.56	33.02	11.11	6.10	2.72					
B	87914-3001	-----	30	1	38.10	35.56	13.21	8.13	2.79		87914-3004	-----	30	1	38.10	35.56	11.11	6.10	2.72					
	87914-3002	-----	30	2	38.10	35.56	13.21	8.13	2.79		87914-3005	-----	30	2	38.10	35.56	11.11	6.10	2.72					
	87914-3003	-----	30	3	38.10	35.56	13.21	8.13	2.79		87914-3006	-----	30	3	38.10	35.56	11.11	6.10	2.72	C				
A																								
										QUALITY SYMBOLS ▽=0 ▽C=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE NTS	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION			CUSTOM HEADER C-GRID,SINGLE WAFER HDR, THROU HOLE,VERTICAL, LF MOLEX INCORPORATED				
											4 PLACES ± ---	mm	INCH	DRAWN BY SKL IM01	DATE 2006/08/21	TITLE								
											3 PLACES ± ---	± 0.2	± ---	CHECKED BY CWLAM	DATE 2006/09/04									
											2 PLACES ± 0.2	± ---	± ---	APPROVED BY KYLEE	DATE 2006/09/04	SD-87914-059								
											1 PLACE ± ---	± ---	± ---	MATERIAL NO.		DOCUMENT NO.					SHEET NO.			
											ANGULAR ± 3 °		SEE TABLE		SD-87914-059					4 OF 9				
											DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SIZE A3		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION									
tb_frame_A3_P_AM_T Rev. D 2004/06/28										9	8	7	6	5	4	3	2	1						

tb_frame_A3_P_AM_T
Rev. D 2004/06/28

10										9										8										7										6										5										4										3										2										1									
PART NO FOR TRAY PACKAGING	PART NO FOR BULK PACKAGING	CKT SIZE	PLATING TYPE	DIMENSION					MATING END	SOLDER TAIL	PART NO FOR TRAY PACKAGING	PART NO FOR BULK PACKAGING	CKT SIZE	PLATING TYPE	DIMENSION					MATING END	SOLDER TAIL																																																																														
				A	B	F	M	P							A	B	F	M	P																																																																																
87914-4201	-----	42	1	53.34	50.80	13.21	8.13	2.79			87914-4204	-----	42	1	53.34	50.80	11.11	6.10	2.72																																																																																
87914-4202	-----	42	2	53.34	50.80	13.21	8.13	2.79			87914-4205	-----	42	2	53.34	50.80	11.11	6.10	2.72																																																																																
87914-4203	-----	42	3	53.34	50.80	13.21	8.13	2.79			87914-4206	-----	42	3	53.34	50.80	11.11	6.10	2.72																																																																																
87914-4401	-----	44	1	55.88	53.34	13.21	8.13	2.79			87914-4404	-----	44	1	55.88	53.34	11.11	6.10	2.72																																																																																
87914-4402	-----	44	2	55.88	53.34	13.21	8.13	2.79			87914-4405	-----	44	2	55.88	53.34	11.11	6.10	2.72																																																																																
87914-4403	-----	44	3	55.88	53.34	13.21	8.13	2.79			87914-4406	-----	44	3	55.88	53.34	11.11	6.10	2.72																																																																																
87914-4601	-----	46	1	58.42	55.88	13.21	8.13	2.79			87914-4604	-----	46	1	58.42	55.88	11.11	6.10	2.72																																																																																
87914-4602	-----	46	2	58.42	55.88	13.21	8.13	2.79			87914-4605	-----	46	2	58.42	55.88	11.11	6.10	2.72																																																																																
87914-4603	-----	46	3	58.42	55.88	13.21	8.13	2.79			87914-4606	-----	46	3	58.42	55.88	11.11	6.10	2.72																																																																																
87914-4801	-----	48	1	60.96	58.42	13.21	8.13	2.79			87914-4804	-----	48	1	60.96	58.42	11.11	6.10	2.72																																																																																
87914-4802	-----	48	2	60.96	58.42	13.21	8.13	2.79			87914-4805	-----	48	2	60.96	58.42	11.11	6.10	2.72																																																																																
87914-4803	-----	48	3	60.96	58.42	13.21	8.13	2.79			87914-4806	-----	48	3	60.96	58.42	11.11	6.10	2.72																																																																																
87914-5001	-----	50	1	63.50	60.96	13.21	8.13	2.79			87914-5004	-----	50	1	63.50	60.96	11.11	6.10	2.72																																																																																
87914-5002	-----	50	2	63.50	60.96	13.21	8.13	2.79			87914-5005	-----	50	2	63.50	60.96	11.11	6.10	2.72																																																																																
87914-5003	-----	50	3	63.50	60.96	13.21	8.13	2.79			87914-5006	-----	50	3	63.50	60.96	11.11	6.10	2.72																																																																																
B																																																																																																			
A																																																																																																			
tb_frame_A3_P_AM_T Rev. D 2004/06/28																																																																																																			

EWR# 1010 & 1021 EC NO: S2007-0182 DRWN:SKL IM01 2006/09/11 CHKD:CWLAM 2006/09/12 APPR:KWLEE 2006/09/13 A	DESCRIPTION REV	QUALITY SYMBOLS ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)	DIMENSION STYLE MM ONLY		SCALE NTS	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION		
			mm	INCH	DRAWN BY SKL IM01	DATE 2006/08/21	CUSTOM HEADER C-GRID,SINGLE WAFER HDR, THROU HOLE,VERTICAL, LF MOLEX INCORPORATED			
		4 PLACES	± ---	± ---	CHECKED BY CWLAM	DATE 2006/09/04				
		3 PLACES	± ---	± ---	APPROVED BY KWLEE	DATE 2006/09/04				
		2 PLACES	± 0.2	± ---	ANGULAR ± 3 °		MATERIAL NO.	DOCUMENT NO.	SHEET NO.	
1 PLACE	± ---	± ---	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE TABLE	SD-87914-059	6 OF 9			
SIZE A3		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION								

	10		9		8		7		6		5		4		3		2		1																																																												
F	PART NO FOR TRAY PACKAGING	PART NO FOR BULK PACKAGING	CKT SIZE	PLATING TYPE	DIMENSION						PART NO FOR TRAY PACKAGING	PART NO FOR BULK PACKAGING	CKT SIZE	PLATING TYPE	DIMENSION																																																																
					A	B	F	MATING END	SOLDER TAIL						A	B	F	MATING END	SOLDER TAIL																																																												
																					M	P	M	P																																																							
	-----	87914-5201	52	1	66.04	63.50	13.21	8.13	2.79	-----	87914-5204	52	1	66.04	63.50	11.11	6.10	2.72																																																													
	-----	87914-5202	52	2	66.04	63.50	13.21	8.13	2.79	-----	87914-5205	52	2	66.04	63.50	11.11	6.10	2.72																																																													
	-----	87914-5203	52	3	66.04	63.50	13.21	8.13	2.79	-----	87914-5206	52	3	66.04	63.50	11.11	6.10	2.72																																																													
E	-----	87914-5401	54	1	68.58	66.04	13.21	8.13	2.79	-----	87914-5404	54	1	68.58	66.04	11.11	6.10	2.72																																																													
	-----	87914-5402	54	2	68.58	66.04	13.21	8.13	2.79	-----	87914-5405	54	2	68.58	66.04	11.11	6.10	2.72																																																													
	-----	87914-5403	54	3	68.58	66.04	13.21	8.13	2.79	-----	87914-5406	54	3	68.58	66.04	11.11	6.10	2.72																																																													
D	-----	87914-5601	56	1	71.12	68.58	13.21	8.13	2.79	-----	87914-5604	56	1	71.12	68.58	11.11	6.10	2.72																																																													
	-----	87914-5602	56	2	71.12	68.58	13.21	8.13	2.79	-----	87914-5605	56	2	71.12	68.58	11.11	6.10	2.72																																																													
	-----	87914-5603	56	3	71.12	68.58	13.21	8.13	2.79	-----	87914-5606	56	3	71.12	68.58	11.11	6.10	2.72																																																													
C	-----	87914-5801	58	1	73.66	71.12	13.21	8.13	2.79	-----	87914-5804	58	1	73.66	71.12	11.11	6.10	2.72																																																													
	-----	87914-5802	58	2	73.66	71.12	13.21	8.13	2.79	-----	87914-5805	58	2	73.66	71.12	11.11	6.10	2.72																																																													
	-----	87914-5803	58	3	73.66	71.12	13.21	8.13	2.79	-----	87914-5806	58	3	73.66	71.12	11.11	6.10	2.72																																																													
B	-----	87914-6001	60	1	76.20	73.66	13.21	8.13	2.79	-----	87914-6004	60	1	76.20	73.66	11.11	6.10	2.72																																																													
	-----	87914-6002	60	2	76.20	73.66	13.21	8.13	2.79	-----	87914-6005	60	2	76.20	73.66	11.11	6.10	2.72																																																													
	-----	87914-6003	60	3	76.20	73.66	13.21	8.13	2.79	-----	87914-6006	60	3	76.20	73.66	11.11	6.10	2.72																																																													
A																																																																															
<table><tr><td rowspan="5">EWR# 1010 & 1021 EC NO: S2007-0182 DRWN:SKL IM01 2006/09/11 CHKD:CWLAM 2006/09/12 APPR:KWLEE 2006/09/13 A</td><td rowspan="5">REV</td><td rowspan="5">DESCRIPTION</td><td rowspan="5">QUALITY SYMBOLS ▽=0 ▽=0</td><td colspan="2">GENERAL TOLERANCES (UNLESS SPECIFIED)</td><td colspan="2">DIMENSION STYLE MM ONLY</td><td>SCALE NTS</td><td>DESIGN UNITS METRIC</td><td colspan="2">THIRD ANGLE PROJECTION</td></tr><tr><td></td><td></td><td></td><td></td><td></td><td></td></tr><tr><td>4 PLACES</td><td>± ---</td><td>± ---</td><td>DRAWN BY SKL IM01</td><td>DATE 2006/08/21</td><td colspan="3" rowspan="2">CUSTOM HEADER C-GRID,SINGLE WAFER HDR, THROU HOLE,VERTICAL, LF</td></tr><tr><td>3 PLACES</td><td>± ---</td><td>± ---</td><td>CHECKED BY CWLAM</td><td>DATE 2006/09/04</td></tr><tr><td>2 PLACES</td><td>± 0.2</td><td>± ---</td><td>APPROVED BY KWLEE</td><td>DATE 2006/09/04</td><td colspan="3">MOLEX INCORPORATED</td></tr><tr><td>1 PLACE</td><td>± ---</td><td>± ---</td><td colspan="2">MATERIAL NO.</td><td colspan="2">DOCUMENT NO. SD-87914-059</td><td colspan="2">SHEET NO. 7 OF 9</td></tr><tr><td colspan="4">DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS</td><td colspan="2">SEE TABLE</td><td colspan="6">THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION</td></tr></table>																				EWR# 1010 & 1021 EC NO: S2007-0182 DRWN:SKL IM01 2006/09/11 CHKD:CWLAM 2006/09/12 APPR:KWLEE 2006/09/13 A	REV	DESCRIPTION	QUALITY SYMBOLS ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE NTS	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION								4 PLACES	± ---	± ---	DRAWN BY SKL IM01	DATE 2006/08/21	CUSTOM HEADER C-GRID,SINGLE WAFER HDR, THROU HOLE,VERTICAL, LF			3 PLACES	± ---	± ---	CHECKED BY CWLAM	DATE 2006/09/04	2 PLACES	± 0.2	± ---	APPROVED BY KWLEE	DATE 2006/09/04	MOLEX INCORPORATED			1 PLACE	± ---	± ---	MATERIAL NO.		DOCUMENT NO. SD-87914-059		SHEET NO. 7 OF 9		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				SEE TABLE		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION					
EWR# 1010 & 1021 EC NO: S2007-0182 DRWN:SKL IM01 2006/09/11 CHKD:CWLAM 2006/09/12 APPR:KWLEE 2006/09/13 A	REV	DESCRIPTION	QUALITY SYMBOLS ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE NTS	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION																																																																					
				4 PLACES	± ---	± ---	DRAWN BY SKL IM01	DATE 2006/08/21	CUSTOM HEADER C-GRID,SINGLE WAFER HDR, THROU HOLE,VERTICAL, LF																																																																						
				3 PLACES	± ---	± ---	CHECKED BY CWLAM	DATE 2006/09/04																																																																							
				2 PLACES	± 0.2	± ---	APPROVED BY KWLEE	DATE 2006/09/04	MOLEX INCORPORATED																																																																						
1 PLACE	± ---	± ---	MATERIAL NO.		DOCUMENT NO. SD-87914-059		SHEET NO. 7 OF 9																																																																								
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				SEE TABLE		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																																																																									
tb_frame_A3_P_AM_T Rev. D 2004/06/28		9	8	7	6	5	4	3	2	1																																																																					

	10		9		8		7		6		5		4		3		2		1		
F	PART NO FOR TRAY PACKAGING	PART NO FOR BULK PACKAGING	CKT SIZE	PLATING TYPE	DIMENSION						PART NO FOR TRAY PACKAGING	PART NO FOR BULK PACKAGING	CKT SIZE	PLATING TYPE	DIMENSION						
								MATING END	SOLDER TAIL									MATING END	SOLDER TAIL		
					A	B	F	M	P						A	B	F	M	P		
	-----	87914-6201	62	1	78.74	76.20	13.21	8.13	2.79		-----	87914-6204	62	1	78.74	76.20	11.11	6.10	2.72		
	-----	87914-6202	62	2	78.74	76.20	13.21	8.13	2.79		-----	87914-6205	62	2	78.74	76.20	11.11	6.10	2.72		
	-----	87914-6203	62	3	78.74	76.20	13.21	8.13	2.79		-----	87914-6206	62	3	78.74	76.20	11.11	6.10	2.72		
E	-----	87914-6401	64	1	81.28	78.74	13.21	8.13	2.79		-----	87914-6404	64	1	81.28	78.74	11.11	6.10	2.72		
	-----	87914-6402	64	2	81.28	78.74	13.21	8.13	2.79		-----	87914-6405	64	2	81.28	78.74	11.11	6.10	2.72		
	-----	87914-6403	64	3	81.28	78.74	13.21	8.13	2.79		-----	87914-6406	64	3	81.28	78.74	11.11	6.10	2.72		
	-----	87914-6601	66	1	83.82	81.28	13.21	8.13	2.79		-----	87914-6604	66	1	83.82	81.28	11.11	6.10	2.72		
	-----	87914-6602	66	2	83.82	81.28	13.21	8.13	2.79		-----	87914-6605	66	2	83.82	81.28	11.11	6.10	2.72		
	-----	87914-6603	66	3	83.82	81.28	13.21	8.13	2.79		-----	87914-6606	66	3	83.82	81.28	11.11	6.10	2.72		
D	-----	87914-6801	68	1	86.36	83.82	13.21	8.13	2.79		-----	87914-6804	68	1	86.36	83.82	11.11	6.10	2.72		
	-----	87914-6802	68	2	86.36	83.82	13.21	8.13	2.79		-----	87914-6805	68	2	86.36	83.82	11.11	6.10	2.72		
	-----	87914-6803	68	3	86.36	83.82	13.21	8.13	2.79		-----	87914-6806	68	3	86.36	83.82	11.11	6.10	2.72		
C	-----	87914-7001	70	1	88.90	86.36	13.21	8.13	2.79		-----	87914-7004	70	1	88.90	86.36	11.11	6.10	2.72		
	-----	87914-7002	70	2	88.90	86.36	13.21	8.13	2.79		-----	87914-7005	70	2	88.90	86.36	11.11	6.10	2.72		
	-----	87914-7003	70	3	88.90	86.36	13.21	8.13	2.79		-----	87914-7006	70	3	88.90	86.36	11.11	6.10	2.72		

