




THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
 © COPYRIGHT - By - ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
AJ	16		C	REVISED PER ECO-11-022150	26MAR12	KH	FB



- 1 ZINC PER QQ-Z-363
- 2 BERYLLIUM COPPER PER QQ-C-530.
- 3 POLYMETHYLPENTENE, GENERAL PURPOSE.
- 4 NICKEL PLATE PER QQ-N-290, 3.81µm [.000150] MINIMUM THICK.
- 5 GOLD PLATE PER ASTM-B-488, 0.76µm [.000030] MINIMUM THICK.
- 6 INTERFACE PER MIL-C-39012.
- 7 BRASS PER ASTM-B-16.
- 8 TIN PLATE PER ASTM-B-545, 3.81µm [.000150] MINIMUM THICK.



PCB CONFIGURATION

5414974-1
PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J. ALCORTA - 27APR2005	TE Connectivity	
DIMENSIONS: mm [INCHES]		CHK J. HAVENER - 27APR2005		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD J. LIPPERT - 27APR2005	NAME JACK, RIGHT ANGLE PCB, 50 OHM, SERIES BNC	
0 PLC ± -	1 PLC ± -	PRODUCT SPEC 108-12078	SIZE A2	CAGE CODE 00779
2 PLC ± 0.08 [.003]	3 PLC ± -	APPLICATION SPEC	DRAWING NO C=5414974	RESTRICTED TO
4 PLC ± -	ANGLES ± -	MATERIAL SEE NOTES 1,2,3,7	WEIGHT -	SCALE 2:1
FINISH SEE NOTES 4,5,8		CUSTOMER DRAWING	SHEET 1 of 1	REV C