

DEA1X3A561JA3B

“ # ” indicates a package specification code.

Recommended

Available

General


125℃

Flow OK

RoHS

< List of part numbers with package codes >
DEA1X3A561JA3B

Shape



Lead Code	Coating Extension e	ø d	Style
A2, A3	Up to the end of crimp	0.6±0.05	Fig. 1
C1, CD	3.0 max.	0.5±0.05	Fig. 2
C3	3.0 max.	0.6±0.05	Fig. 2



L size or outer diameter D (mm)	12.0 mm max.
T size	4.0 mm max.
Lead spacing F	7.5 ±1.0mm
Lead diameter d	0.6 ±0.05mm
Paint dripping e	Up to the end of crimp

References

Packaging	Specifications	Minimum quantity
B	Packing in bulk	200

Specifications

Capacitance	560pF ±5%
Rated voltage	1000Vdc
Temperature characteristics (complied standard)	SL(JIS)
Temperature coefficient	+350 to -1000ppm/℃
Temperature range of temperature characteristics	20 to 85℃
Operating temperature range	-25 to 125℃

⚠ Attention

- 1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it ’ s specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- 2.This datasheet has only typical specifications because there is no space for detailed specifications.
Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.