






RECOMMEND P.C.B. LAYOUT

NOTES:

1. ALL DIMENSIONS IN MM
2. GENERAL TOLERANCE: 0.0=±0.4
0.00=±0.25
3. TERM. NOS. FOR REF. ONLY
4. RATING: 50mA, @12V DC
5. TRAVEL: 0.25±0.1mm
6. OPERATING FORCE: 250±50gf
7. CONTACT RESISTANCE: 100m ohms Max.
8. ELECTRICAL LIFE: 100,000 CYCLES MIN.
9. INSULATION RESISTANCE: 100M ohms min.
10. DIELECTRIC STRENGTH: 250V RMS MIN.
11. OPERATING TEMP.: -20°C to -70°C
12. DESIGNATE MAJOR DIMENSIONS.
13. 2002/95/EC (ROHS) COMPLIANT



CIRCUIT: SPST

CONTACT CONFIGURATION



FIXED DRAWING, NOTES				5/8/07		TN	
RELEASED FOR PRODUCTION							
DESCRIPTION				DATE		CHKD	
THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED							
TITLE				SCALE		DATE	
TL1105LF250Q				4:1		5/8/07	
				DR		TN	
				DWG		P010025	
						REV	
						B	