


HAND REAMERS**Straight Shank**

BS 328 DIN 206 ISO 236/1



	Range	Finish
73 060 HSS	1/16" - 2" 1.5mm - 40mm	Bright Bright

Hand Reamers are supplied with Left-Hand Helical Flutes and Taper Lead unless otherwise ordered.

Hand Reamers without Lead are non-standard and will be priced in accordance with the quantity ordered

Dia	Cutting Edge Length	Overall Length	Availability
in d	mm l ₂	mm l ₁	

1.50	20	41	•
1/16	21	44	•
5/64	25	50	•
2.00	25	50	•
3/32	29	58	•
2.50	29	58	•
7/64	31	62	•
3.00	31	62	•
1/8	33	66	•
3.50	35	71	•
9/64	35	71	•
5/32	38	76	•
4.00	38	76	•
11/64	41	81	•
4.50	41	81	•
3/16	44	87	•
5.00	44	87	•
13/64	44	87	•
5.50	47	93	•
7/32	47	93	•
15/64	47	93	•
6.00	47	93	•
1/4	50	100	•
6.50	50	100	•
17/64	54	107	•
7.00	54	107	•
9/32	54	107	•
7.50	54	107	•
19/64	58	115	•
5/16	58	115	•
8.00	58	115	•
21/64	58	115	•
8.50	58	115	•
11/32	62	124	•
9.00	62	124	•
23/64	62	124	•
9.50	62	124	•
3/8	66	133	•
25/64	66	133	•
10.00	66	133	•
13/32	66	133	•
10.50	66	133	•
27/64	71	142	•
11.00	71	142	•
7/16	71	142	•
11.50	71	142	•
29/64	71	142	•
15/32	76	152	•

Dia	Cutting Edge Length	Overall Length	Availability
in d	mm l ₂	mm l ₁	

12.00	76	152	•
31/64	76	152	•
12.50	76	152	•
1/2	76	152	•
13.00	76	152	•
33/64	76	152	•
17/32	81	163	•
13.50	81	163	•
14.00	81	163	•
9/16	81	163	•
14.50	81	163	•
15.00	81	163	•
19/32	87	175	•
5/8	87	175	•
16.00	87	175	•
16.50	87	175	•
21/32	87	175	•
17.00	87	175	•
11/16	93	188	•
18.00	93	188	•
23/32	93	188	•
19.00	93	188	•
3/4	100	201	•
25/32	100	201	•
20.00	100	201	•
13/16	100	201	•
21.00	100	201	•
27/32	107	215	•
22.00	107	215	•
7/8	107	215	•
23.00	107	215	•
29/32	107	215	•
15/16	115	231	•
24.00	115	231	•
31/32	115	231	•
25.00	115	231	•
1	115	231	•
26.00	115	231	•
1.1/32	115	231	•
1.1/16	124	247	•
27.00	124	247	•
28.00	124	247	•
1.1/8	124	247	•
29.00	124	247	•
30.00	124	247	•
1.3/16	133	265	•
31.00	133	265	•
1.1/4	133	265	•

Dia	Cutting Edge Length	Overall Length	Availability
in d	mm l ₂	mm l ₁	

32.00	133	265	•
33.00	133	265	•
1.5/16	133	265	•
34.00	142	284	•
1.3/8	142	284	•
35.00	142	284	•
36.00	142	284	•
1.7/16	142	284	•
37.00	142	284	•
38.00	152	305	•
1.1/2	152	305	•
40.00	152	305	•
1.5/8	152	305	•
1.3/4	163	326	•
1.7/8	174	347	•
2	174	347	•