MARKETING SALES DRAWING

DIMENSIONS IN INCHES - DO NOT SCALE THIS DRAWING
DIMENSIONS IN METRIC - [ ]

Electrical Testing per Tusonix standard test plans and Mil-Std-202 Test Methods.







NOTES:
1. SUPPLIED WITH HEX NUT AND INTERNAL TOOTH LOCK WASHER.
2. PARTS WILL BE MARKED M15733/61.

2000	500 VDC / 350 VAC	25 AC	I.R. MIN. @ 100 (VDC.)	DWV	----	55	70	70
	125 °C				10 MHz	100 MHz	1 GHz	10 GHz
MIN. CAP. (pF)	WORKING VOLTAGE	CURRENT (A)	10 G Ω	1250 VDC	MINIMUM NO LOAD INSERTION LOSS (dB) AT 25°C PER MIL-STD -220			

REVISION RECORD		
Original Release C.O. **19990713-1-01**	0	
ADDED DWV, IR & DIM. .050. DIM .437 ±.010 WAS .436 ±.046 & .250±.010 WAS .250 ±.015. S.M. 11-10-03 **20031110-4-01**	1	

TOLERANCES unless otherwise specified	
2 PLC. DECIMAL ±	N/A
3 PLC. DECIMAL ±	.031 [0.79]
ANGLES ±	N/A

TUSONIX
TUCSON, ARIZONA

Title **MIL-15733/61-0003 BUSHING STYLE FILTER**

Drawn S.M. 07-15-99	Scale 2 X
Approved E.F. 07-15-99	
A	**4206-502**

X-2015 Rev-0