

Dual monostable multivibrator

BU4528B / BU4528BF

The BU4528B and BU4528BF are monostable multivibrators with trigger and reset functions that can be activated. Each chip has two built-in circuits.


Triggers can initiate both rising and falling in response to Input A and Input B. As the output monostable pulse width is determined by the time constant of the external resistance (R_x) and the capacitor (C_x), a wide range of output pulse widths can be set.

Setting the $\overline{\text{RESET}}$ input to "L" enables external asynchronous resetting and this $\overline{\text{RESET}}$ input can be utilized to reduce the time from the trigger disable input or the power on until the BU4528B and BU4528BF are ready for monostable operation.

●Features

- 1) Low power dissipation.
- 2) Wide range of operating power supply voltages.
- 3) High input impedance.
- 4) High fan-out.
- 5) Direct drive of 2 L-TTL inputs and 1 LS-TTL input.


●Block diagram



●Truth table

INPUT			OUTPUT	
$\overline{\text{RESET}}$	A	B	Q	$\overline{Q}$
H		H		
H	L			
H		L	Not Triggered	
H	H		Not Triggered	
H	L, H,	H	Not Triggered	
H	L	L, H,	Not Triggered	
L	X	X	L	H
	X	X	Not Triggered	

●Logic circuit diagram



●Absolute maximum ratings (Ta = 25°C, V_{SS} = 0V)

Parameter	Symbol	Limits	Unit
Power supply voltage	V _{DD}	− 0.3 ~ + 18	V
Power dissipation	P _d	1000 (DIP), 500 (SOP)	mW
Operating temperature	T _{opr}	− 40 ~ + 85	°C
Storage temperature	T _{stg}	− 55 ~ + 150	°C
Input voltage	V _{IN}	− 0.3 ~ V _{DD} + 0.3	V

●Electrical characteristics

DC characteristics (unless otherwise noted, Ta = 25°C, V_{SS} = 0V)

Parameter	Symbol	Min.	Typ.	Max.	Unit	V _{DD} (V)	Conditions
Input high level voltage	V _{IH}	3.5	—	—	V	5	—
		7.0	—	—		10	
		11.0	—	—		15	
Input low level voltage	V _{IL}	—	—	1.5	V	5	—
		—	—	3.0		10	
		—	—	4.0		15	
Input high level current	I _{IH}	—	—	0.3	μA	15	V _{IH} = 15V
Input low level current	I _{IL}	—	—	− 0.3	μA	15	V _{IL} = 0V
Output high level voltage	V _{OH}	4.95	—	—	V	5	I _O = 0mA
		9.95	—	—		10	
		14.95	—	—		15	
Output low level voltage	V _{OL}	—	—	0.05	V	5	I _O = 0mA
		—	—	0.05		10	
		—	—	0.05		15	
Output high level current	I _{OH}	− 0.16	—	—	mA	5	V _{OH} = 4.6V
		− 0.4	—	—		10	V _{OH} = 9.5V
		− 1.2	—	—		15	V _{OH} = 13.5V
Output low level current	I _{OL}	0.44	—	—	mA	5	V _{OL} = 0.4V
		1.1	—	—		10	V _{OL} = 0.5V
		3.0	—	—		15	V _{OL} = 1.5V
Static current dissipation	I _{DD}	—	—	20	μA	5	V _I = V _{DD} or GND
		—	—	40		10	
		—	—	80		15	

Switching characteristics (Ta = 25°C, CL = 50pF, VSS = 0V)

Parameter	Symbol	Min.	Typ.	Max.	Unit	VDD (V)	Conditions
Output rise time	t _{TLH}	—	100	—	ns	5	—
		—	50	—	ns	10	
		—	40	—	ns	15	
Output fall time	t _{THL}	—	100	—	ns	5	—
		—	50	—	ns	10	
		—	40	—	ns	15	
Propagation delay time, A or B to Q or $\bar{Q}$	t _{PLH} t _{PHL}	—	325	—	ns	5	Cx = 15pF, Rx = 5kΩ
		—	120	—	ns	10	
		—	90	—	ns	15	
Propagation delay time, A or B to Q or $\bar{Q}$	t _{PLH} t _{PHL}	—	705	—	ns	5	Cx = 1000pF, Rx = 10kΩ
		—	290	—	ns	10	
		—	210	—	ns	15	
Propagation delay, Reset to Q or $\bar{Q}$	t _{PLH} t _{PHL}	—	325	—	ns	5	Cx = 15pF, Rx = 5kΩ
		—	90	—	ns	10	
		—	60	—	ns	15	
		—	1000	—	ns	5	Cx = 1000pF, Rx = 10kΩ
		—	300	—	ns	10	
		—	250	—	ns	15	
Minimum input pulse width	t _{WIN}	—	70	—	ns	5	Cx = 1000pF, Rx = 10kΩ Cx = 15pF, Rx = 5kΩ
		—	30	—	ns	10	
		—	30	—	ns	15	
Output pulse width	t _{WOUT1}	—	550	—	ns	5	Cx = 15pF, Rx = 5kΩ
		—	350	—	ns	10	
		—	300	—	ns	15	
Output pulse width	t _{WOUT2}	25	40	55	μs	5	Cx = 1000pF, Rx = 10kΩ
		10	50	90	μs	10	
		15	55	95	μs	15	
Minimum trigger time	t _{tr}	—	0	—	ns	5	Cx = 1000pF, Rx = 10kΩ Cx = 15pF, Rx = 5kΩ
		—	0	—	ns	10	
		—	0	—	ns	15	
Input capacitance	C _{IN}	—	5	—	pF	—	—

● Measurement circuits




Fig. 1 Switching time measurement circuit




Fig. 2 Switching time waveform

●Timing chart





Fig. 3


●Electrical characteristic curve

Fig. 4 Power dissipation vs. T_a


●External dimensions (Units: mm)

BU4528B

BU4528BF



DIP16



SOP16

Notes

- No technical content pages of this document may be reproduced in any form or transmitted by any means without prior permission of ROHM CO.,LTD.
- The contents described herein are subject to change without notice. The specifications for the product described in this document are for reference only. Upon actual use, therefore, please request that specifications to be separately delivered.
- Application circuit diagrams and circuit constants contained herein are shown as examples of standard use and operation. Please pay careful attention to the peripheral conditions when designing circuits and deciding upon circuit constants in the set.
- Any data, including, but not limited to application circuit diagrams information, described herein are intended only as illustrations of such devices and not as the specifications for such devices. ROHM CO.,LTD. disclaims any warranty that any use of such devices shall be free from infringement of any third party's intellectual property rights or other proprietary rights, and further, assumes no liability of whatsoever nature in the event of any such infringement, or arising from or connected with or related to the use of such devices.
- Upon the sale of any such devices, other than for buyer's right to use such devices itself, resell or otherwise dispose of the same, no express or implied right or license to practice or commercially exploit any intellectual property rights or other proprietary rights owned or controlled by
- ROHM CO., LTD. is granted to any such buyer.
- Products listed in this document use silicon as a basic material.
Products listed in this document are no antiradiation design.

The products listed in this document are designed to be used with ordinary electronic equipment or devices (such as audio visual equipment, office-automation equipment, communications devices, electrical appliances and electronic toys).

Should you intend to use these products with equipment or devices which require an extremely high level of reliability and the malfunction of which would directly endanger human life (such as medical instruments, transportation equipment, aerospace machinery, nuclear-reactor controllers, fuel controllers and other safety devices), please be sure to consult with our sales representative in advance.

About Export Control Order in Japan

Products described herein are the objects of controlled goods in Annex 1 (Item 16) of Export Trade Control Order in Japan.

In case of export from Japan, please confirm if it applies to "objective" criteria or an "informed" (by MITI clause) on the basis of "catch all controls for Non-Proliferation of Weapons of Mass Destruction.