

10

9

8

7

6

5

4

3

2

1

F




E

D


C

B

A



SECT. B-B



SECT. A-A

NOTES.

1. 適合ハウジング: 501330-**** / 501939-****
APPLICABLE HOUSING: 501330-**** / 501939-****

2. メッキ仕様
PLATING
錫メッキ: 1.0μmMIN. リフロー処理 (前メッキ)
Sn: 1.0μmMIN. REFLOW TREATMENT (PRE-PLATED)

3. 刻印は裏面から実施
PUNCH SIDE: OTHER SIDE

MXJ

金型番号 (番号無しの製品もあります。)
Die No. (There is Non-Mark Item)

TREAD MARK

501334-0100	バラ状 LOOSE
501334-0000	連鎖状 CHAIN
MATERIAL NO.	端子形状 FORM

MATERIAL	REVISED EC NO.: J2009-0651 DRW: RAKATA 2008/09/16 CHKD: MATSUMOTO 2008/09/16 APPR: NUKITA 2008/09/16	DESCRIPTION	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE 20:1	DESIGN UNITS METRIC	 THIRD ANGLE PROJECTION
リン青銅 PHOSPHOR BRONZE t=0.12			10 UNDER	±0.2	DRAWN BY DATE	TITLE	1.0 WIRE TO BOARD CONN. CRIMP REC TERMINAL (SN) -LEAD FREE-		
FINISH SEE NOTE			10 OVER 30 UNDER	±0.25	CHECKED BY DATE	MOLEX MOLEX INCORPORATED			
WIRE RANGE AWG #28-32			30 OVER	±0.3	APPROVED BY DATE				
INS. RANGE Ø0.4-0.8			ANGULAR ±3 °		MATERIAL NO.	DOCUMENT NO.	SHEET NO.		
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			SEE TABLE		SD-501334-001	1 OF 1			
						THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION			

9

8

7

6

5

4

3

2