


RLS4148 / RLS4150 / RLS4448

● Applications

● Features

- External dimensions (Units : mm)



●Construction

●Absolute maximum ratings (Ta = 25°C)

Type	V _{RM} (V)	V _R (V)	I _{FM} (mA)	I _O (mA)	I _F (mA)	I _{FSM} 1μS (A)	P (mW)	T _J (°C)	Topr (°C)	Tstg (°C)
RLS4148	100	75	450	150	200	2	500	200	-65~+200	-65~+200
RLS4150	50	50	600	200	250	4	500	200	-65~+200	-65~+200
RLS4448	100	75	450	150	200	2	500	200	-65~+200	-65~+200

●Electrical characteristics (Ta = 25°C)

Type	V _F (V)						B _V (V)Min.		I _R (μA)Max.				Cr (pF)	t _{rr} (ns)
	@	@	@	@	@	@	@	@	@25°C		@150°C		V _R =0 f=1MHz	V _R =6V I _F =10mA R _L =100Ω
	1mA	5mA	10mA	50mA	100mA	200mA	5μA	100μA	V _R (V)		V _R (V)			
RLS4148			1.0				75	100	0.025 5.0	20 75	50.0	20	4	4
RLS4150	0.54 0.62		0.66 0.74	0.76 0.86	0.82 0.92	0.87 1.0	—	50	0.1 5.0	50 75	100.0	50	2.5	4
RLS4448		0.62 0.72					—	100	0.025 5.0	20 75	50.0	20	4	4

The upper figure is the minimum V_F and the lower figure is the maximum V_F value.

Diodes

●Electrical characteristic curves (Ta = 25°C)




Fig.1 Forward characteristics




Fig.2 Reverse characteristics




Fig.3 Capacitance between terminals characteristics




Fig.4 Reverse recovery time characteristics




Fig.5 Surge current characteristics




Fig.6 Reverse recovery time (t_{rr}) measurement circuit