

256 - Precision centre punches | 256.4



Standards

NF E 71-211, DIN 7250, ASME B107.410

Description

- Chrome-vanadium steel forged, hardened to 52 to 58 HRc.
- Presentation: knurled body.
- Zinc-plated finish.

Specifications

Reference	256.4
[g]	35
L [mm]	105
d [mm]	8
A [mm]	4
[kg]	0,035

